

DO NOT
SCALE FROM
THIS PRINT

PCMS-1XX-XX-XX-D

NO. OF POSITIONS

20, 25, 30, 34, 40, 50
(PER ROW)

LEAD STYLE

-01: FOR .031" BOARD
(USE C-61-07-XX)
(USE PCMS-XX-D-01)
-02: FOR .062" BOARD
(USE C-61-08-XX)
(USE PCMS-XX-D-02)



-02: FOR .062" BOARD
(USE C-61-08-XX)

PLATING


- S: 30µ" SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL
- F: 3µ" FLASH SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL
- L: 10µ" LIGHT SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL
- LM: 10µ" LIGHT SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL
- FM: 3µ" FLASH SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL
- SM: 30µ" SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL

ROW SPECIFICATION

-D: DOUBLE ROW
(USE PCMS-XX-D-XX)



SECTION "A"-"A"




SECTION "B"-"B"

NOTES:

1.  REPRESENTS A CRITICAL DIMENSION.
2. NOTE DELETED.
3. NOTE DELETED.
4. MINIMUM PUSHOUT FORCE: .5 LB.
5. MAXIMUM ALLOWABLE BOW: .002 INCH/INCH AFTER ASSEMBLY.
6. ALL POSITIONS ARE TO BE PACKAGED IN PT-1-24-19-09 TUBES WITH TWO TP-09 PLUGS PER TUBE.

PACKAGING
(SEE NOTE 6)



-PT-1-24-19-09

TABLE 1

LEAD STYLE	"A"	"B"	"C"
-01	.036 [.91]	.070 [1.78]	.118 [3.00]
-02	.070 [1.78]	.110 [2.79]	.105 [2.67]

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS	ANGLES
.XX: $\pm .01$ [.3]	2°

.XXX: $\pm .005$ [.13]
.XXXX: $\pm .0020$ [.05]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL:

INSULATOR: BLACK VECTRA E130
CONTACT: BeCu

DO NOT SCALE DRAWING

SHEET SCALE: 2.5:1

	DESCRIPTION:
--	--------------

.050 x .050 EDGE MOUNT SOCKET ASSEMBLY

DWG. NO.

PCMS-1XX-XX-XX-D

BY: BRATCHER 2/12/99

SHEET 1 OF 1

F:\DWG\MISC\MKTG\PCMS-1XX-XX-XX-D-MKT.SLDDRW