


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D3	REVISED PER ECO-12-002699	13FEB12	KH	DR
	D4	REVISED PER ECR-16-018115	03JAN2017	RS	DR



AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
4/0 AWG SOLID OR STRANDED	4/0 AWG SOLID OR STRANDED	4/0 AWG SOLID OR STRANDED

- 1

STAMP AMP 4/0W* 200 APPROX AS SHOWN
- 2

MATERIAL THK: 2.59±0.08 [.102±.003]
- 3

COPPER PER ASTM B-152, ANNEALED
- 4


TIN PLATE 0.00254 [.000100] MIN EXT THK PER ASTM B545
- 5

MEETS MS20659-157, CLASS 2
- 6

NICKEL PLATE 0.00762[.000300] MIN EXT THK PER SAE AMS QQ-N-290
- 7

PART IS NOT UL LISTED OR CSA CERTIFIED

7 6	343°C [650°F]	321271-1
4	170°C [338°F]	5 321271
RECOMMENDED OPERATING TEMP.		PART NUMBER

CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHRUM 15MAY96		 TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	RECOMMENDED OPERATING TEMPERATURE: SEE TABLE	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		CHK DM SWARTZ 01JUL96	NAME TERMINAL, RING TONGUE, SOLISTRAND				
						APVD JL MECKLEY 01JUL96					
		VOLTAGE RATING: NOT APPLICABLE		FINISH SEE TABLE	PRODUCT SPEC —	SIZE A3					CAGE CODE 00779
		WIRE CROSS SECTIONAL AREA RANGE: 96.3-117.0mm² [190,000-231,100] CIR MILS STRANDED			APPLICATION SPEC —	CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV D4
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111										
FOR ORDER ENTRY	1-800-526-5142										