


PowerBLOC

Solid State Switches



Engineering Specifications	JT(*) 1205-(X)	JT(*) 2405-(X)	JT(*) 1210-(X)	JT(*) 2410-(X)	JT(*) 2415-(X)	MX1	MX100	MX200
Output Characteristics								
Peak Blocking (V)	400	500	400	500	500	40	400	500
Output Rating (A/V_{RMS})	5/120	5/240	10/120	10/240	15/240	1.5/24	1.5/120	1.5/240
Max Off-State Leakage Current at Full Rated Load Voltage (mA)	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
Max On-State Voltage Drop (V_{RMS})	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
Critical Rate of Rise Voltage dv/dt (V/μsec @ 60°C tab temperature)								
Minimum	75	75	75	75	75	75	75	75
Max Holding Current (mA)	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
Typical Response Time (msec @ 60Hz)	32	32	32	32	32	32	32	32
Applied Load Voltage Before Turn-on (VAC)								
MX1	5	5	5	5	5	5	5	5
Other than MX1	25	25	25	25	25	25	25	25
Operating Frequency (Hz)								
Minimum	20	20	20	20	20	20	20	20
Maximum	500	500	500	500	500	500	500	500
Input Characteristics								
Control Voltage (DC)								
Minimum (JTA)	4	4	4	4	4	2 ⁽¹⁾	2 ⁽¹⁾	2 ⁽¹⁾
(JTB)	9	9	9	9	9			
(JTC)	20	20	20	20	20			
Typical (JTA)	5	5	5	5	5	—	—	—
(JTB)	12	12	12	12	12			
(JTC)	24	24	24	24	24			
Maximum (JTA)	8	8	8	8	8	48 ⁽¹⁾	48 ⁽¹⁾	48 ⁽¹⁾
(JTB)	16	16	16	16	16			
(JTC)	28	28	28	28	28			
Max Control Current to Operate (mA)	15	15	15	15	15	15	15	15
Min Dropout Voltage (VDC)	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8

¹External limiting resistor required to maintain control current between 15 mA (min) and 50 mA (max).

(*) "A" designates 4-8VDC Control
 "B" designates 9-16VDC Control
 "C" designates 20-26VDC Control

(X) "1" specifies 0.3" pins
 "2" specifies Quick Connect
 "3" specifies 0.175" pins

High Voltage Option Available (H Suffix)

Features:

- Random turn-on
- Ratings to 600V, 10A
- UL recognized
- CSA approved
- DC control, AC output
- Optically isolated
- TTL and CMOS compatible

Surge and Overload Current Maximum

Duration	Load Current
1 Second	3 Times Continuous Rating
16 Milliseconds	10 Times Continuous Rating
1 Millisecond	20 Times Continuous Rating

Absolute Maximum Ratings

Parameter	Min	Max	Units
Isolation Voltage:			
Input-to-Output	2500	—	V _{RMS}
Terminals-to-Tab/Case	2500	—	V _{RMS}
Thermal Resistance:			
Junction-to-Ambient	—	41.0	°C/Watt ¹
Junction-to-Tab	—	5.9	°C/Watt ²
Input to Output Capacitance	—	4	pF
Continuous Control Current	—	100	mA
Peak Control Current (100 μsec)	—	1	A
Reverse Control Voltage	—	5	VDC
Operating Temperature	-25	75	°C
Storage Temperature	-25	75	°C
Soldering Temperature (10 seconds on leads)	—	260	°C

¹MX Series T_A = 40°C


²JT Series T_{TAB} = 65°C

All characteristics at 25°C


*For a complete listing of CP Clare Solid State Products ask for our SSP15 catalog.

2144904 0000494 369


6 Pin Through Hole (Standard)




6 Pin PC Board Pattern (Bottom View)




6 Pin Surface Mount ("S" Suffix)




6 Pin Mounting Pad (Top View)




8 Pin Through Hole (Standard)




8 Pin PC Board Pattern (Bottom View)



8 Pin Surface Mount ("S" Suffix)




8 Pin Mounting Pad (Top View)




DIMENSIONS
mm
(Inches)


8 Pin Flatpack ("P" Suffix)




8 Pin Flatpack Mounting Pad (Top View)




16 Pin SOIC ("P" Suffix)




16 Pin SOIC Mounting Pad (Top View)




16 Pin Through Hole (Standard)



16 Pin PC Board Pattern (Bottom View)




8 Pin SIP




DIMENSIONS
mm
(Inches)


16 Pin DIP




Thermal Clip




OptoFILM® 10A Series, Pins




OptoFILM® 10A Series, Quick Connect




Tape and Reel Packaging for 6 Pin Surface Mount Package



Tape and Reel Packaging for 8 Pin Surface Mount Package



Tape and Reel Packaging for 8 Pin Flatpack Package



Tape and Reel Packaging for 16 Pin SOIC Package

