




PRINT DIST

DIMENSIONS IN INCHES. DO NOT SCALE PRINT

C" DIM	NO 60
60	.013
.013	.017



METHOD OF GAGING CRIMP DIMENSIONS
THE CRIMP DIMS APPLY ONLY TO THE ABOVE
COMBINATIONS, ON A CRIMPED PRODUCT.

SUPERSEDED BY 1.5. 2024-3

14	REVISED	PL	11/24
13	REVISED	PL	11/24
12	REVISED	PL	11/24
11	REVISED	PL	11/24
10	REVISED	PL	11/24
9	REVISED	PL	11/24
8	REVISED	PL	11/24
7	REVISED	PL	11/24
6	REVISED	PL	11/24
5	REVISED	PL	11/24
4	REVISED	PL	11/24
3	REVISED	PL	11/24
2	REVISED	PL	11/24
1	REVISED	PL	11/24

ITEM NO	REMARKS	NAME	NUMBER	DWG SIZE
14		EJECTOR	306493-2	1
13		SCREW-SPECIAL	1-306593-4	1
12		INDENTER-INSULATION	306740-2	1
11		SPACER-LOWER	306192-7	1
10		INDENTER-BRAID	306742	1
9		BARREL-BLOCK	306543-1	1
8		SPRING	305182	2
7		INSERT-BARREL-LOWER	306544-8	1
6		RING-RETAINING	1-21046-3	2
5		INSERT-BARREL-UPPER	306738-2	1
4		ANVIL-BRAID	306741	1
3		SPACER-UPPER	1-306191-0	1
2		ANVIL-INSULATION	306739-2	1
1		SCREW-SPECIAL	7-306131-2	1

NUMBER	69690-2
DESCRIPTION	

DR	B. Mangell	2-1-66
CHK	J. J. J.	2-2-66

MATERIAL AND FINISH		CLASS	
WIRE - RANGE - INSULATION		SUB MIN. COAX	
RG 196		M B	
TOLERANCE EXCEPT AS NOTED ± .015		SCALE 4-1	
NAME		DIE ASSEMBLY	



CUSTOMER COPY
REFERENCE ONLY