


4

3



2

1

REVISIONS			
ZONE	LTR	DESCRIPTION	DATE
—	A	CHG'D PER DCO# T-02582	W.J. 4-23-81



Raychem
PART NO.
MTC100-JBI-SII-T08
DATE CODE



5 WEIGHT (MAX.) : $\frac{\text{LBS.}}{.0054}$ $\frac{\text{GRAMS}}{2.46}$

4 SOCKET ONE: SOCKET NUMBER ONE MARKED IN CONTRASTING COLOR.

3. WAFER : WAFER MEETS THE REQUIREMENTS OF RAYCHEM SPECIFICATION D-6012.
2. FINISH :
- 2-A SOCKET WAFER ; FINISH TO BE AS MOLDED.
 - 2-B SOCKET CONTACT ; GOLD PLATE PER MIL-G-45204 CLASS I.
 - 2-C CONTACT TAIL ; COATED WITH SOLDER PER QQ-S-571.
1. MATERIAL :
- 1-A SOCKET WAFER ; HIGH GRADE POLYARYLENE THERMO-PLASTIC.
 - 1-B SOCKET CONTACT ; COPPER ALLOY PER QQ-B-750 (A).
 - 1-C SOLDERPAK® TERMINATORS ASSY ; REFER TO RAYCHEM DWG. CTA-0035 FOR DATA.

NOTES

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

DO NOT SCALE THIS DRAWING

SPECIFICATION CONTROL DRAWING

© Raychem Corporation 1981

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES BRACKETED DIMENSIONS () ARE METRIC AND TOLERANCES ARE:				DRAWN	W.V.J.	I-15-81	Raychem RAYCHEM CORPORATION 300 CONSTITUTION DR., MENLO PARK, CALIFORNIA 94025	
.XXX: ± .005 (0.13 M.M.)				CHECKED			TITLE KIT, 1 " SOCKET WAFER "B" WITH SOLDERPAK® TERMINATORS, FOR ROUND WIRE (20-26 AWG), 125 °C TEMPERATURE RATING MTC 100 SERIES	
.XX: ± .02 (0.51 M.M.)				APPROVED				
.X: ± .04 (1.02 M.M.)				APPROVED				
.A: ± .01 (0.25 M.M.)				APPROVED				
							SIZE C	CODE IDENT NO. 06090
							DWG. NO. MTC100-JBI-SII-T08	
							WEIGHT $\frac{\Delta}{5}$	SHEET 1 OF 1