






14.4	15.6	16.42	15.0	16.95	503566-5100	51
12.6	13.8	14.62	13.2	15.15	503566-4500	45
12.0	13.2	14.02	12.6	14.55	503566-4300	43
11.4	12.6	13.42	12.0	13.95	503566-4100	41
10.8	12.0	12.82	11.4	13.35	503566-3900	39
10.2	11.4	12.22	10.8	12.75	503566-3700	37
9.6	10.8	11.62	10.2	12.15	503566-3500	35
9.0	10.2	11.02	9.6	11.55	503566-3300	33
8.4	9.6	10.42	9.0	10.95	503566-3100	31
7.2	8.4	9.22	7.8	9.75	503566-2700	27
6.6	7.8	8.62	7.2	9.15	503566-2500	25
6.0	7.2	8.02	6.6	8.55	503566-2300	23
5.4	6.6	7.42	6.0	7.95	503566-2100	21
4.8	6.0	6.82	5.4	7.35	503566-1900	19
4.2	5.4	6.22	4.8	6.75	503566-1700	17
3.6	4.8	5.62	4.2	6.15	503566-1500	15
3.0	4.2	5.02	3.6	5.55	503566-1300	13
2.4	3.6	4.42	3.0	4.95	503566-1100	11
1.8	3.0	3.82	2.4	4.35	503566-0900	9
E	D	C	B	A	EMBOSSED PACKAGE オーダー番号 ORDER NO.	極数 CIRCUITS
CONNECTOR SERIES NO. 503566-***8						


REVISED EC NO: J2011-1637 TDRWN: H. YAMOTO CHKD: H. IJIMA APPR: K. MORIKAWA REV	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		10 UNDER	± ---	DRAWN BY HIJIMA	DATE 2010/05/20	TITLE 0.3 FPC CONN E/O BTM CONTACT TYPE HGT=0.95MM MOLEX INCORPORATED			
		10 OVER 30 UNDER	± ---	CHECKED BY NMATSUURA	DATE 2010/05/20				
		30 OVER	± ---	APPROVED BY KMORIKAWA	DATE 2010/06/11				
		ANGULAR	± 1 °	MATERIAL NO. 503566-***8		DOCUMENT NO. SD-503566-001	SHEET NO. 1 OF 2		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					





14.4	15.6	16.42	15.0	16.95	503566-5100	51
12.6	13.8	14.62	13.2	15.15	503566-4500	45
12.0	13.2	14.02	12.6	14.55	503566-4300	43
11.4	12.6	13.42	12.0	13.95	503566-4100	41
10.8	12.0	12.82	11.4	13.35	503566-3900	39
10.2	11.4	12.22	10.8	12.75	503566-3700	37
9.6	10.8	11.62	10.2	12.15	503566-3500	35
9.0	10.2	11.02	9.6	11.55	503566-3300	33
8.4	9.6	10.42	9.0	10.95	503566-3100	31
7.2	8.4	9.22	7.8	9.75	503566-2700	27
6.6	7.8	8.62	7.2	9.15	503566-2500	25
6.0	7.2	8.02	6.6	8.55	503566-2300	23
5.4	6.6	7.42	6.0	7.95	503566-2100	21
4.8	6.0	6.82	5.4	7.35	503566-1900	19
4.2	5.4	6.22	4.8	6.75	503566-1700	17
3.6	4.8	5.62	4.2	6.15	503566-1500	15
3.0	4.2	5.02	3.6	5.55	503566-1300	13
2.4	3.6	4.42	3.0	4.95	503566-1100	11
1.8	3.0	3.82	2.4	4.35	503566-0900	9
E	D	C	B	A	EMBOSSED PACKAGE オーダー番号 ORDER NO.	極数 CIRCUITS
CONNECTOR SERIES NO. 503566-***8						

REVISED EC NO: J2011-1637 DRWN: H. YAMOTO CHKD: H. IJIMA APPR: K. MORIKAWA REV		DESCRIPTION 2011/05/31 2011/05/31 2011/06/02		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION	
10 UNDER		± ---		DRAWN BY HIJIMA		DATE 2010/05/20		TITLE		0.3 FPC CONN E/O BTM CONTACT TYPE HGT=0.95MM		MOLEX INCORPORATED	
10 OVER 30 UNDER		± ---		CHECKED BY NMATSUURA		DATE 2010/05/20		MATERIAL NO.		503566-***8		SD-503566-001	
30 OVER		± ---		APPROVED BY KMORIKAWA		DATE 2010/06/11		DOCUMENT NO.		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 1 OF 2	
ANGULAR		± 1 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3							



10

9

8

7

6

5

4

3

2

1

F



E

D


C

B

A




DETAIL "C"



注記 NOTES

- 製品詳細寸法については図面 SD-503566-001 を参照下さい。
RE DETAILED DIMENSION, SEE SD-503566-001
- 梱包数量 : 3000個/リール
NUMBER OF CONNECTORS : 3000 PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH



- 材料 MATERIAL
キャリアテープ (CARRIER TAPE) : ポリスチレン (POLYSTYRENE)
トップテープ (TOP TAPE) : PET , PE , PEF
リール (REEL) : ポリスチレン (PS) <リサイクル材を含む>
POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>
- トップテープの剥離強度については、IEC60286-3に準拠
TOP TAPE PEEL FORCE IS DEFINED BY IEC60286-3.

REVISED		EC NO. J2011-1637		2011/05/31		DRWN: HMIYAMOTO		2011/05/31		CHKD: HIJIMA		2011/06/02		APPR: KMORIKAWA		REV	
DESCRIPTION		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---		DESIGN UNITS METRIC		MODEL NO.		503566-**00		THIRD ANGLE PROJECTION		SHEET NO.	
10 UNDER		± 0.2		DRAWN BY		DATE		TITLE		0.3 FPC CONN. E/O TAPING PACKAGE (503566-**08 SERIES)		MOLEX INCORPORATED		DOCUMENT NO.		SD-503566-002	
10 OVER 30 UNDER		± 0.25		CHECKED BY		DATE		MATERIAL NO.		SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		1 OF 2		EN-02JA(021)	
30 OVER		± 0.3		APPROVED BY		DATE		ANGULAR $\pm 3^\circ$		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		3		2	

9

8

7

6

5

4

3

2

EN-02JA(021)

10

9

8

7

6

5

4

3

2

1

F




E

D

C


B

A



注記 NOTES

- 製品詳細寸法については図面 SD-503566-001 を参照下さい。
RE DETAILED DIMENSION, SEE SD-503566-001
- 梱包数量 : 3000個/リール
NUMBER OF CONNECTORS : 3000 PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH



- 材料 MATERIAL
キャリアテープ (CARRIER TAPE) : ポリスチレン (POLYSTYRENE)
トップテープ (TOP TAPE) : PET , PE , PEF
リール (REEL) : ポリスチレン (PS) <リサイクル材を含む>
POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>
- トップテープの剥離強度については、IEC60286-3に準拠
TOP TAPE PEEL FORCE IS DEFINED BY IEC60286-3.

9

8

7

6

5

4

3

2

EN-02JA(021)

REVISED EC NO: J2011-1637 DRWN:HMIYAMOTO CHKD:HIJIMA APPR:KMORIKAWA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
		10 UNDER	± 0.2	DRAWN BY HIJIMA	DATE 2010/05/20	TITLE 0.3 FPC CONN. E/O TAPING PACKAGE (503566-**08 SERIES)		
		10 OVER 30 UNDER	± 0.25	CHECKED BY NMATSUURA	DATE 2010/05/20			
		30 OVER	± 0.3	APPROVED BY KMORIKAWA	DATE 2010/06/11			
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-503566-002		1 OF 2	
	REV			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

F

E

D

C

B

A

F




E

D

C

B

A



SECTION Y-Y

32±0.3	28.4	14.2	33.4	17.25	503566-5100	51
24±0.3	≡	11.5	25.4	15.45	503566-4500	45
				14.85	503566-4300	43
				14.25	503566-4100	41
				13.65	503566-3900	39
				13.05	503566-3700	37
				12.45	503566-3500	35
				11.85	503566-3300	33
				11.25	503566-3100	31
				10.05	503566-2700	27
				9.45	503566-2500	25
16±0.3	≡	7.5	17.4	8.85	503566-2300	23
				8.25	503566-2100	21
				7.65	503566-1900	19
				7.05	503566-1700	17
				6.45	503566-1500	15
				5.85	503566-1300	13
				5.25	503566-1100	11
				4.65	503566-0900	9
E キャリアテープ幅 EMBOSSED TAPE WIDTH	D	C	B	A	EMBOSSD TAPE PACKAGE オーダー番号 ORDER NO.	極 数 CIRCUITS

SEE SHEET 1 OF 2
EC NO: J2011-1637
DRAWN: HMI YAMOTO 2011/05/31
CHKD: H I J I M A 2011/05/31
APPR: KMORIKAWA 2011/06/02

DESCRIPTION
GENERAL TOLERANCES (UNLESS SPECIFIED)
10 UNDER ±0.2
10 OVER 30 UNDER ±0.25
30 OVER ±0.3
ANGULAR ±3 °
DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY
DRAWN BY DATE
H I J I M A 2010/05/20
CHECKED BY DATE
NMATSUURA 2010/05/20
APPROVED BY DATE
KMORIKAWA 2010/06/11
MATERIAL NO.
SEE CHART
SIZE
A3

SCALE

DESIGN UNITS
METRIC
THIRD ANGLE PROJECTION
TITLE
0.3 FPC CONN. E/O
TAPING PACKAGE
(503566-**08 SERIES)
MOLEX INCORPORATED
DOCUMENT NO.
SD-503566-002
SHEET NO.
2 OF 2

F

E

D

C

B

A

F




E

D

C

B

A



32±0.3	28.4	14.2	33.4	17.25	503566-5100	51
24±0.3	≡	11.5	25.4	15.45	503566-4500	45
				14.85	503566-4300	43
				14.25	503566-4100	41
				13.65	503566-3900	39
				13.05	503566-3700	37
				12.45	503566-3500	35
				11.85	503566-3300	33
				11.25	503566-3100	31
				10.05	503566-2700	27
				9.45	503566-2500	25
16±0.3	≡	7.5	17.4	8.85	503566-2300	23
				8.25	503566-2100	21
				7.65	503566-1900	19
				7.05	503566-1700	17
				6.45	503566-1500	15
				5.85	503566-1300	13
				5.25	503566-1100	11
				4.65	503566-0900	9
E キャリアテープ幅 EMBOSSED TAPE WIDTH	D	C	B	A	EMBOSSD TAPE PACKAGE オーダー番号 ORDER NO.	極 数 CIRCUITS

SECTION Y-Y

SEE SHEET 1 OF 2
EC NO: J2011-1637
DRAWN: H. IYAMOTO 2011/05/31
CHECKED: H. IYAMA 2011/05/31
APPR: K. MORIKAWA 2011/06/02

GENERAL TOLERANCES
(UNLESS SPECIFIED)

10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGULAR	±3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE
MM ONLY

DRAWN BY H. IYAMA	DATE 2010/05/20
CHECKED BY NMATSUURA	DATE 2010/05/20
APPROVED BY KMORIKAWA	DATE 2010/06/11
MATERIAL NO.	

SCALE

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
0.3 FPC CONN. E/O
TAPING PACKAGE
(503566-**08 SERIES)

MOLEX INCORPORATED

DOCUMENT NO.
SD-503566-002

SHEET NO.
2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION