

SA5.0A Series

500 Watt Peak Power MiniMOSORB™ Zener Transient Voltage Suppressors

Unidirectional

The SA5.0A series is designed to protect voltage sensitive components from high voltage, high energy transients. They have excellent clamping capability, high surge capability, low zener impedance and fast response time. The SA5.0A series is supplied in ON Semiconductor's exclusive, cost-effective, highly reliable Surmetic™ axial leaded package and is ideally-suited for use in communication systems, numerical controls, process controls, medical equipment, business machines, power supplies and many other industrial/consumer applications.

Features

- Working Peak Reverse Voltage Range – 5.0 to 170 V
- Peak Power – 500 Watts @ 1.0 ms
- ESD Rating of Class 3 (>16 kV) per Human Body Model
- Maximum Clamp Voltage @ Peak Pulse Current
- Low Leakage < 1 μ A above 8.5 V
- UL 497B for Isolated Loop Circuit Protection
- Maximum Temperature Coefficient Specified
- Response Time is typically < 1.0 ns
- Pb-Free Packages are Available*

Mechanical Characteristics:

CASE: Void-free, Transfer-molded, Thermosetting Plastic

FINISH: All external surfaces are corrosion resistant and leads are readily solderable

MAXIMUM LEAD TEMPERATURE FOR SOLDERING:

260°C, 1/16 in. from the case for 10 seconds



POLARITY: Cathode indicated by polarity band

MOUNTING POSITION: Any




ON Semiconductor®

<http://onsemi.com>



MARKING DIAGRAM



A = Assembly Location
SAxxxA = Device Number
(Refer to Table on Page 3)
YY = Year
WW = Work Week
▪ = Pb-Free Package
(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping†
SAxxxAG	Axial Lead (Pb-Free)	1000 Units / Box
SAxxxARLG	Axial Lead (Pb-Free)	5000 / Tape & Reel
SAxxxALFG**	Axial Lead (Pb-Free)	2000 Units / Box

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

**Lead formed device.

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

SA5.0A Series

MAXIMUM RATINGS


Rating	Symbol	Value	Unit
Peak Power Dissipation (Note 1) @ $T_L \leq 25^\circ\text{C}$	P_{PK}	500	W
Steady State Power Dissipation @ $T_L \leq 25^\circ\text{C}$, Lead Length = 3/8 in Derated above $T_L = 50^\circ\text{C}$	P_D	3.0 30	W mW/ $^\circ\text{C}$
Thermal Resistance, Junction-to-Lead	$R_{\theta JL}$	33.3	$^\circ\text{C/W}$
Forward Surge Current (Note 2) @ $T_A = 25^\circ\text{C}$	I_{FSM}	70	A
Operating and Storage Temperature Range	T_J, T_{stg}	- 55 to +150	$^\circ\text{C}$

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Nonrepetitive current pulse per Figure 4 and derated above $T_A = 25^\circ\text{C}$ per Figure 5.
2. 1/2 sine wave (or equivalent square wave), $PW = 8.3$ ms, duty cycle = 4 pulses per minute.

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted, $V_F = 3.5$ V Max. @ I_F (Note 6) = 35 A)

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
ΔV_{BR}	Maximum Temperature Variation of V_{BR}
I_F	Forward Current
V_F	Forward Voltage @ I_F



SA5.0A Series

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted, $V_F = 3.5\text{ V Max. @ } I_F$ (Note 6) = 35 A)

Device*	Device Marking	V _{RWM} (Note 3)	I _R @ V _{RWM}	Breakdown Voltage				V _C @ I _{PP} (Note 5)		ΘV _{BR}
				V _{BR} (Note 4) (Volts)			@ I _T	V _C	I _{PP}	
		Volts	μA	Min	Nom	Max	mA	Volts	A	mV/°C
SA5.0A, G	SA5.0A	5	600	6.4	6.7	7	10	9.2	54.3	5
SA6.0AG	SA6.0A	6	600	6.67	7.02	7.37	10	10.3	48.5	5
SA7.0ARLG	SA7.0A	7	150	7.78	8.19	8.6	10	12	41.7	6
SA10AG	SA10A	10	1	11.1	11.7	12.3	1	17	29.4	10
SA12AG	SA12A	12	1	13.3	14	14.7	1	19.9	25.1	12
SA13AG	SA13A	13	1	14.4	15.15	15.9	1	21.5	23.2	13
SA15AG	SA15A	15	1	16.7	17.6	18.5	1	24.4	20.6	16
SA16AG	SA16A	16	1	17.8	18.75	19.7	1	26	19.2	17
SA17ARLG	SA17A	17	1	18.9	19.9	20.9	1	27.6	18.1	19
SA18ARLG	SA18A	18	1	20	21.05	22.1	1	29.2	17.2	20
SA20ARLG	SA20A	20	1	22.2	23.35	24.5	1	32.4	15.4	23
SA24AG	SA24A	24	1	26.7	28.1	29.5	1	38.9	12.8	28
SA26ARLG	SA26A	26	1	28.9	30.4	31.9	1	42.1	11.9	30
SA28ARLG	SA28A	28	1	31.1	32.75	34.4	1	45.4	11	31
SA30ARLG	SA30A	30	1	33.3	35.05	36.8	1	48.4	10.3	36
SA33ARLG	SA33A	33	1	36.7	38.65	40.6	1	53.3	9.4	39
SA36AG	SA36A	36	1	40	42.1	44.2	1	58.1	8.6	41
SA51AG	SA51A	51	1	56.7	59.7	62.7	1	82.4	6.1	61
SA64ALFG	SA64A	64	1	71.1	74.85	78.6	1	103	4.9	76
SA100AG	SA100A	100	1	111	117	123	1	162	3.1	123
SA170ARLG	SA170A	170	1	189	199	209	1	275	1.8	208

3. MiniMOSORB™ transients suppressor is normally selected according to the maximum working peak reverse voltage (V_{RWM}), which should be equal to or greater than the dc or continuous peak operating voltage level.

4. V_{BR} measured at pulse test current I_T at an ambient temperature of 25°C .

5. Surge current waveform per Figure 4 and derate per Figures 1 and 2.

6. 1/2 sine wave (or equivalent square wave), $PW = 8.3\text{ ms}$, duty cycle = 4 pulses per minute

*The "G" suffix indicates Pb-Free package or Pb-Free Packages available.




Figure 1. Pulse Rating Curve




Figure 2. Pulse Derating Curve

SA5.0A Series




Figure 3. Capacitance versus Breakdown Voltage




Figure 4. Pulse Waveform




Figure 5. Steady State Power Derating

UL RECOGNITION*

The entire series including the bidirectional CA suffix has *Underwriters Laboratory Recognition* for the classification of protectors (QVGQ2) under the UL standard for safety 497B and File #E210057. Many competitors only have one or two devices recognized or have recognition in a non-protective category. Some competitors have no recognition at all. With the UL497B recognition, our parts successfully passed several tests including Strike Voltage

Breakdown test, Endurance Conditioning, Temperature test, Dielectric Voltage-Withstand test, Discharge test and several more.


Whereas, some competitors have only passed a flammability test for the package material, we have been recognized for much more to be included in their protector category.

*Applies to SA5.0A – SA170A.

SA5.0A Series

PACKAGE DIMENSIONS

AXIAL LEAD CASE 59AA-01 ISSUE A



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. ALL RULES AND NOTES ASSOCIATED WITH JEDEC DO-41 OUTLINE SHALL APPLY.
4. POLARITY DENOTED BY CATHODE BAND.
5. LEAD DIAMETER NOT CONTROLLED WITHIN F DIMENSION.
6. REPLACES CASE 59-09.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.228	0.299	5.80	7.60
B	0.102	0.142	2.60	3.60
D	0.028	0.034	0.71	0.86
K	1.000	---	25.44	---

MiniMOSORB and Surmetic are trademarks of Semiconductor Components Industries, LLC.

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada

Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local
Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor:

[SA10ARLG](#) [SA12AG](#) [SA12ARLG](#) [SA13ARLG](#) [SA15AG](#) [SA15ARLG](#) [SA16ARLG](#) [SA17ARLG](#) [SA18ARLG](#)
[SA20ARLG](#) [SA24AG](#) [SA24ARLG](#) [SA26ARLG](#) [SA28ARLG](#) [SA30ARLG](#) [SA33ARLG](#) [SA36AG](#) [SA36ARLG](#)
[SA5.0AG](#) [SA5.0ARLG](#) [SA6.0AG](#) [SA6.0ARLG](#) [SA7.0ARLG](#)