


REV.	DATE	DESCRIPTION
A	01/25/04	UPDATE DRAWING FORMAT



NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .255"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex																																																						
8						DRAWN	G.R.S.	01/25/04																																																								
7						CHECKED																																																										
6						ISSUED				PART DESCRIPTION																																																						
5	FERRULE	COPPER	GOLD	1		SHEET	1 OF 1			SMA R/A CRIMP PLUG (FOR RG-8X, LMR-240)																																																						
4	COVER	BRASS	GOLD	1									PART NO.																																																			
3	CONTACT PIN	BRASS	GOLD	1									132239																																																			
2	INSULATOR	TEFLON	NATURAL	1									DWG. NO.																																																			
1	BODY	BRASS	GOLD	1								SCALE																																																				
DESCRIPTION					MATERIAL					FINISH					QTY					C:/132/132239.DWG					DWG. NO.					132239.DWG					REV.					A					SIZE					A					SCALE					NA				