


MLF2012DR82JT000

Applications		Commercial Grade
Feature	<div style="display: flex; justify-content: space-around;"> <div>Multilayer</div> <div>Shield</div> <div>Ferrite Core</div> </div>	<div style="display: flex; justify-content: space-around;"> <div>Multilayer</div> <div>Magnetic Shield</div> <div>Ferrite Core</div> </div>
Series	MLF Series / MLF2012 Type	
Status	PROD	




Size	
Length(L)	2.00mm +/-0.20mm
Width(W)	1.25mm +/-0.20mm
Thickness(T)	1.25mm +/-0.20mm
Recommended Land Pattern (A)	0.80mm Nom.
Recommended Land Pattern (B)	1.00mm Nom.
Recommended Land Pattern (C)	1.20mm Nom.

Electrical Characteristics	
Inductance	820nH +/-5% at 25MHz
Rated Current	150mA
Self-Resonant Frequency [Min.]	130MHz
Self-Resonant Frequency [Typ.]	170MHz
Q [Min.]	25 at 25MHz
Q [Typ.]	35 at 25MHz
DC Resistance [Nom.]	400mΩ
DC Resistance [Max.]	650mΩ


Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Blister (Plastic)Taping [180mm Reel]
Package Quantity	2000Pcs Min.
Weight	0.014g

MLF2012DR82JT000

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




MLF2012DR82JT000



MLF2012DR82JT000



MLF2012DR82JT000



MLF2012DR82JT000

•This PDF document was created based on the data listed on the TDK Corporation website.

•All specifications are subject to change without notice.

MLF2012DR82JT000

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)

DC Bias Characteristic

no data available

Temperature Characteristic

no data available

Temperature Rise by DC

no data available