




(22.40)
PROTECTIVE CAP WIDTH

(16.45)


VIEWS SHOWN WITH
PROTECTIVE COVER INSTALLED
10122770-1*1LF

NOTE 12

NOTE 13





Copyright FCI.

spec ref -				dr Sander Soe		2012/09/12		projection		MM		size A2		scale 5:1							
tolerance std				eng Tao Zhan		2014/10/23						ecn no		ELX-DG-18510-1							
ASME Y14.5				chr -		-						rel level		Released							
				appr Collins Lu		2014/10/23						product family		AIRMAX VS							
surface 		linear		0.X		±0.3				title		AIRMAX VS2 VERTICAL HEADER		dwg no		10122770		rev		C	
		0.XX		±0.10																	
		0.XXX		±0.050																	
ASME Y14.5		angular		0°		±2°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 2 of 4					

PDS: Rev :C

STATUS:Released

Printed: Oct 24, 2014



RECOMMENDED PCB LAYOUT
FOR DIFFERENTIAL APPLICATIONS,
COMPONENT SIDE
(TWO ADJACENT FOOTPRINTS SHOWN)
NOTES 6, AND 8

spec ref	-	dr	Sander Soe	2012/09/12	projection	MM	size	A2	scale	3:1
tolerance std	ASME Y14.5	eng	Tao Zhan	2014/10/23	chr	-	ecn no	ELX-DG-18510-1	rel level	Released
surface	✓	appr	Collins Lu	2014/10/23	product family	AIRMAX VS	cat. no.	10122770	rev	C
ASME Y14.5	linear	angular	0°	±2°	www.fci.com	Product - Customer Drw	sheet 3 of 4			

