

5

4

3




2

1


D

C


B



vorverrastet
pre assembled
preassemble



verrastet
fitted
assemble



1) Markierung erster Kontakt, Ader 1 des Flachkabels
1) Contact no.1, 1st contact wire of flat cable
1) Contact no.1, repère 1 du câble

A

0918 514 5803 58U	0,76 μ m Au	Bulk packaging MOQ = 5000 pcs		All Dimensions in mm Original Size DIN A 4			Techn. Character.				Nicht tolerierte Masse/ <i>Free size tolerances</i>		
0918 514 6803 58U	2							Dat.	Name	Massstab/Scale 2:1	SEK 18 Female Connector 14 poles with central polarisation cover without cable stop		
0918 514 7803 58U	3												
0918 514 5803	0,76 μ m Au	N.A.					Detail.	01-FEB-00	Th				
0918 514 6803	2	N.A.				Insp.							
0918 514 7803	3	N.A.	33797	10/08/06	PK	Stand.							
Bestell-Nr. Part-No. Reference	Anforderungsstufe Performance level Niveau de qualite	Index Designation	33788	24/07/06	PK	HARTING EURL F-95972 Paris				TB 09 18 514 X803			Blatt/ page 1 1
			26570	01-FEB-00	JB								
						Mod.	Dat.	Name		Sub.			