



DO NOT
SCALE FROM
THIS PRINT



IPS1-1XX-XX-XX-D-XXX

No OF POS PER ROW

-02 THRU -25

OPTION

-POL: POSITION #1 REMOVED
(USE IPS1-XX-D-P)
-FL: FRICTION LOCK
(USE IPS1-XX-D-FL-X)
[POSITIONS -05 THRU -25]

LEAD STYLE


-01: STANDARD INSERTION
(USE C-08-01-XXX)
-L1: LOW INSERTION
(USE C-17-01-XXX)

ROW SPECIFICATION

-D: DOUBLE (USE IPST-XX-D)

PLATING SPECIFICATION

-H: HEAVY GOLD
(USE C-XX-01-H)
-S: SELECTIVE GOLD, MATTE TIN TAIL
(USE C-XX-01-S)
-T: TIN (AVAILABLE FOR EXISTING CUSTOMERS ONLY.)
(USE C-XX-01-T)
-SM: HEAVY SELECTIVE GOLD, MATTE TIN TAIL
(USE C-XX-01-S)
-L: LIGHT SELECTIVE GOLD, MATTE TIN TAIL
(USE C-XX-01-L)




SECTION "A"-"A"


NOTES:

1. $\odot$ REPRESENTS A CRITICAL DIMENSION.
2. MAXIMUM ALLOWABLE CUT FLASH: .010[.25].
3. MINIMUM CONTACT PUSH OUT FORCE: 1.5 lbs.
4. MAXIMUM ALLOWABLE BOW: .003[.08] INCH/INCH AFTER ASSEMBLY.
5. MAXIMUM VARIATION BETWEEN PIN ROWS: .010[.25].
6. "END WALLS" AFTER CUTTING SHOULD BE .015+/- .003[.38+/- .08].
7. PARTS TO BE BULK PACKAGED.
8. -T PLATING AVAILABLE FOR EXISTING CUSTOMERS ONLY.
9. AFTER REVISION N OF THE COMPONENT PRINT IPS1-XX-D-XX-X, SAMTEC LOGO TO APPEAR ON THE #1 POSITIONS.

-FL: FRICTION LOCK OPTION
IPS1-110-01-X-D-FL SHOWN



-POL: POLARIZED OPTION
IPS1-110-01-X-D-POL SHOWN



UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES

.XX: $\pm .01[.3]$ $\pm 2^\circ$

.XXX: $\pm .005[.13]$

.XXXX: $\pm .0020[.051]$

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

MATERIAL:

DO NOT SCALE DRAWING

SHEET SCALE: 2.5:1

INSULATOR: VECTRA E130i, COLOR: BLACK
CONTACT: PHOS BRONZE, 510 SPRING TEMPER

DESCRIPTION:

.100[2.54] DOUBLE ROW SHROUDED SOCKET ASSEMBLY

DWG. NO.

IPS1-1XX-XX-XX-D-XXX

BY: DEAN P

10-30-2002

SHEET 1 OF 1