

Linear and Switching Wall Plug Power Supplies



Features

- Alternative Output Connectors and Other Output Connectors Available on Special Order
- Approved by CSA, NRTL(UL)

General Specifications

A/C Input: 108-132 VAC 60 Hz.  
Regulation: ±6%.  
Overload Protection: Output Protected Against Overload and Short Circuit. Automatic Recovery Upon Removal of Overload Condition.

Linear Regulated Wallmount Units — Single Output

| Stock No. | Mfr.'s Type    | Output Connector Type | Output #1 |      | Max. Watts (W) | Dimensions H×W×L (In.) | EACH  |       |
|-----------|----------------|-----------------------|-----------|------|----------------|------------------------|-------|-------|
|           |                |                       | VDC       | Amps |                |                        | 1-4   | 5-9   |
| 879-0075  | WM025-760      | A                     | 5         | 0.50 | 2.5            | 2.20×1.90×3.30         | 30.60 | 27.82 |
| 879-2050  | WM050-1950-760 | A                     | 5         | 1.20 | 6.0            | 3.21×2.18×1.89         | 16.03 | 14.69 |
| 879-2075  | WM075-1950-760 | A                     | 5         | 1.50 | 7.5            | 4.70×2.60×1.90         | 32.30 | 29.82 |
| 879-0090  | WM075-1950-D5  | B                     | 5         | 1.50 | 7.5            | 4.70×2.60×1.90         | 34.00 | 31.38 |
| 879-2101  | WM101-1950-760 | A                     | 5         | 2.00 | 10.0           | 4.70×3.10×2.30         | 32.30 | 29.82 |
| 879-1805  | WM1805/3-760   | A                     | 5         | 3.00 | 18.0           | 3.07×2.13×1.26         | 42.80 | 39.69 |
| 879-1060  | WM060-1950-760 | A                     | 12        | 0.50 | 6.0            | 3.20×2.20×1.90         | 18.03 | 16.52 |
| 879-1444  | WM144-1950-S   | *                     | 12        | 1.20 | 14.4           | 4.70×3.10×2.20         | 44.00 | 40.80 |
| 879-2144  | WM144-1950-760 | A                     | 12        | 1.20 | 14.4           | 4.70×3.10×2.30         | 37.09 | 34.00 |
| 879-1812  | WM1812/1.5-760 | A                     | 12        | 1.40 | 18.0           | 3.07×2.13×1.26         | 40.66 | 37.70 |
| 879-1061  | WM061-1950-760 | A                     | 15        | 0.40 | 6.0            | 3.20×2.20×1.90         | 23.54 | 21.86 |
| 879-1824  | WM1824/.75-760 | A                     | 18        | 0.75 | 18.0           | 3.07×2.13×1.26         | 40.66 | 37.70 |
| 879-1818  | WM1818/1-760   | A                     | 18        | 1.00 | 18.0           | 3.07×2.13×1.26         | 40.66 | 37.70 |
| 879-1080  | WM080-1950-760 | A                     | 24        | 0.33 | 42.0           | 3.21×2.18×1.57         | 25.96 | 23.80 |

Switching Regulated Wallmount Units — Single Output

|          |            |   |    |      |      |                |       |       |
|----------|------------|---|----|------|------|----------------|-------|-------|
| 879-5050 | WP0505-760 | A | 5  | 1.00 | 5.0  | 2.25×1.88×1.03 | 27.82 | 25.80 |
| 879-1105 | WP1105-760 | A | 5  | 1.60 | 8.0  | 2.20×1.80×1.10 | 31.04 | 28.78 |
| 879-1205 | WP1205-760 | A | 5  | 2.40 | 12.0 | 3.00×2.00×1.00 | 33.00 | 30.14 |
| 879-0605 | WP0605-760 | A | 6  | 1.00 | 6.0  | 2.25×1.88×1.03 | 29.96 | 27.78 |
| 879-0612 | WP0612-760 | A | 12 | 0.50 | 6.0  | 2.25×1.88×1.03 | 31.03 | 28.78 |
| 879-1112 | WP1112-760 | A | 12 | 0.80 | 10.0 | 2.20×1.80×1.10 | 32.10 | 29.77 |
| 879-1212 | WP1212-760 | A | 12 | 1.00 | 12.0 | 3.00×2.00×1.00 | 33.00 | 30.14 |
| 879-0615 | WP0615-760 | A | 15 | 0.40 | 6.0  | 2.25×1.88×1.03 | 31.03 | 28.78 |
| 879-1115 | WP1115-760 | A | 15 | 0.60 | 10.0 | 2.20×1.80×1.10 | 36.00 | 33.38 |
| 879-1215 | WP1215-760 | A | 15 | 0.80 | 12.0 | 3.00×2.00×1.00 | 33.00 | 30.14 |
| 879-1218 | WP1218-760 | A | 18 | 0.67 | 12.0 | 3.00×2.00×1.00 | 33.00 | 30.14 |
| 879-1224 | WP1224-760 | A | 24 | 0.50 | 12.0 | 3.00×2.00×1.00 | 33.00 | 30.14 |

\*-S indicates shielded DC output cable.

Linear Regulated Wallmount Units — Dual Output

| Stock No. | Mfr.'s Type   | Output #1 |      | Output #2 |      | Max. Watts (W) | Dimensions H×W×L (In.) | EACH  |       |
|-----------|---------------|-----------|------|-----------|------|----------------|------------------------|-------|-------|
|           |               | VDC       | Amps | VDC       | Amps |                |                        | 1-4   | 5-9   |
| 879-1070  | WM070-1950-D5 | 5         | 0.60 | 12.0      | 0.33 | 7.0            | 4.50×2.60×1.90         | 26.23 | 24.48 |
| 879-1090  | WM090-1950-D5 | 5         | 0.70 | −5.0      | 0.70 | 7.0            | 4.50×2.60×1.90         | 35.70 | 32.95 |
| 879-0115  | WM100-S†      | 5         | 1.00 | −5.0      | 1.00 | 10.0           | 4.77×3.12×2.31         | 53.04 | 48.22 |
| 879-1071  | WM071-1950-D5 | 15        | 0.24 | −15.0     | 0.24 | 7.5            | 4.50×2.60×1.90         | 32.27 | 30.18 |
| 879-1072  | WM072-1950-D5 | 12        | 0.30 | −12.0     | 0.30 | 7.2            | 4.50×2.60×1.90         | 28.41 | 27.25 |

†-S indicates shielded DC output cable.

Linear Regulated Units — Triple Output

| Stock No. | Mfr.'s Type   | Output #1 |      | Output #2 |      | Output #3 |      | Max. Watts (W) | Dimensions H×W×L (In.) | EACH  |       |
|-----------|---------------|-----------|------|-----------|------|-----------|------|----------------|------------------------|-------|-------|
|           |               | VDC       | Amps | VDC       | Amps | VDC       | Amps |                |                        | 1-4   | 5-9   |
| 879-0080  | WM053         | 5         | 0.38 | 12.0      | 0.18 | −5        | 0.18 | 5.3            | 2.20×2.75×3.50         | 43.86 | 39.87 |
| 879-1063  | WM063-1950-D5 | 5         | 0.60 | 12.0      | 0.16 | −12       | 0.16 | 6.3            | 4.33×2.44×2.00         | 38.02 | 34.85 |
| 879-0105  | WM113         | 5         | 0.86 | 12.0      | 0.30 | −12       | 0.30 | 11.3           | 2.28×3.10×4.36         | 37.27 | 34.85 |
| 879-0125  | WM113TT       | 5         | 0.86 | 12.0      | 0.30 | −12       | 0.30 | 11.3           | 6.50×3.85×2.60         | 53.04 | 48.22 |
| 879-0135  | WM220-1       | 5         | 2.00 | 12.0      | 0.50 | −12       | 0.50 | 22.0           | 6.50×3.85×2.60         | 79.75 | 73.10 |
| 879-1220  | WM220-1950-D5 | 5         | 2.00 | 12.0      | 0.50 | −12       | 0.50 | 22.0           | 6.50×3.85×2.60         | 97.92 | 89.02 |

**Connector Type A**  
Output Connector Female

ID = 2.5 mm; OD = 5.5 mm  
Barrel Length = 10.0 mm

**Connector Type B**  
5 Pin DIN  
Male Connector

Alternative Output Connectors and Other Output Connectors Available on Special Order.

D15  
15 Pin Sub “D”

D9  
9 Pin Sub “D”

M6  
6 Pin Molex

760  
Phone Plug

M4  
4 Pin Molex