



# LET19060C

## RF POWER TRANSISTORS

### *Ldmos Enhanced Technology*



TARGET DATA

#### N-CHANNEL ENHANCEMENT-MODE LATERAL MOSFETs

- IS-97 CDMA PERFORMANCES  
 $P_{OUT} = 7.5 \text{ W}$   
 $EFF. = 18 \%$
- EDGE PERFORMANCES  
 $P_{OUT} = 30 \text{ W}$   
 $EFF. = 25 \%$
- GSM PERFORMANCES  
 $P_{OUT} = 65 \text{ W}$   
 $EFF. = 45 \%$
- EXCELLENT THERMAL STABILITY
- BeO FREE PACKAGE
- INTERNAL INPUT/OUTPUT MATCHING
- ESD PROTECTION

#### DESCRIPTION

The LET19060C is a common source N-Channel enhancement-mode lateral Field-Effect RF power transistor designed for broadband commercial and industrial applications at frequencies up to 1.0 GHz. The LET19060C is designed for high gain and broadband performance operating in common source mode at 26 V. Its internal matching makes it ideal for base station applications requiring high linearity.



#### ABSOLUTE MAXIMUM RATINGS ( $T_{CASE} = 25 \text{ }^{\circ}\text{C}$ )

| Symbol        | Parameter  | Value       | Unit               |
|---------------|--|-------------|--------------------|
| $V_{(BR)DSS}$ | Drain-Source Voltage                                       | 65          | V                  |
| $V_{GS}$      | Gate-Source Voltage  | -0.5 to +15 | V                  |
| $I_D$         | Drain Current  | 7           | A                  |
| $P_{DISS}$    | Power Dissipation (@ $T_c = 70 \text{ }^{\circ}\text{C}$ ) | 130         | W                  |
| $T_j$         | Max. Operating Junction Temperature                        | 200         | $^{\circ}\text{C}$ |
| $T_{STG}$     | Storage Temperature  | -65 to +150 | $^{\circ}\text{C}$ |

#### THERMAL DATA

|               |                                   |     |                      |
|---------------|-----------------------------------|-----|----------------------|
| $R_{th(j-c)}$ | Junction -Case Thermal Resistance | 1.0 | $^{\circ}\text{C/W}$ |
|---------------|-----------------------------------|-----|----------------------|

**LET19060C****ELECTRICAL SPECIFICATION** ( $T_{CASE} = 25^{\circ}C$ )**STATIC** (Per Section)

| Symbol        | Test Conditions   | Min. | Typ. | Max. | Unit          |
|---------------|---|------|------|------|---------------|
| $V_{(BR)DSS}$ | $V_{GS} = 0\text{ V}$ $I_D = 10\text{ }\mu\text{A}$             | 65   |      |      | V             |
| $I_{DSS}$     | $V_{GS} = 0\text{ V}$ $V_{DS} = 26\text{ V}$                    |      |      | 6    | $\mu\text{A}$ |
| $I_{GSS}$     | $V_{GS} = 5\text{ V}$ $V_{DS} = 0\text{ V}$                     |      |      | 1    | $\mu\text{A}$ |
| $V_{GS(Q)}$   | $V_{DS} = 26\text{ V}$ $I_D = \text{TBD}$                       | 2.5  |      | 4.5  | V             |
| $V_{DS(ON)}$  | $V_{GS} = 10\text{ V}$ $I_D = 2\text{ A}$                       |      | 0.27 |      | V             |
| $G_{FS}$      | $V_{DS} = 10\text{ V}$ $I_D = 2\text{ A}$                       |      | 4.7  |      | mho           |
| $C_{ISS}^*$   | $V_{GS} = 0\text{ V}$ $V_{DS} = 26\text{ V}$ $f = 1\text{ MHz}$ |      | TBD  |      | pF            |
| $C_{OSS}^*$   | $V_{GS} = 0\text{ V}$ $V_{DS} = 26\text{ V}$ $f = 1\text{ MHz}$ |      | TBD  |      | pF            |
| $C_{RSS}$     | $V_{GS} = 0\text{ V}$ $V_{DS} = 26\text{ V}$ $f = 1\text{ MHz}$ |      | TBD  |      | pF            |

\* Includes Internal Matching

| Symbol  | Test Conditions  | Min. | Typ. | Max. | Unit |
|---|--|------|------|------|------|
| <b>DYNAMIC</b> ( $f = 2000\text{ MHz}$ )        |  |      |      |      |      |
| $P_{1dB}$                                       | $V_{DD} = 26\text{ V}$ $I_{DQ} = \text{TBD}$   | 70   | 75   |      | W    |
| $\eta_D^{(1)}$                                  | $V_{DD} = 26\text{ V}$ $I_{DQ} = \text{TBD}$   | 45   | 50   |      | %    |
| Load mismatch                                   | $V_{DD} = 26\text{ V}$ $I_{DQ} = \text{TBD}$ $P_{OUT} = 60\text{ W}$<br>ALL PHASE ANGLES |      |      | 10:1 | VSWR |
| <b>DYNAMIC</b> ( $f = 1930 - 1990\text{ MHz}$ ) |  |      |      |      |      |
| $P_{1dB}$                                       | $V_{DD} = 26\text{ V}$ $I_{DQ} = \text{TBD}$   | 60   | 65   |      | W    |
| $G_P$   | $V_{DD} = 26\text{ V}$ $I_{DQ} = \text{TBD}$ $P_{OUT} = 60\text{ W}$                     | 11   | 13   |      | dB   |
| $\eta_D^{(1)}$                                  | $V_{DD} = 26\text{ V}$ $I_{DQ} = \text{TBD}$   | 40   | 45   |      | %    |
| $P_{OUT(CDMA)}^{(2)}$                           | 885 KHz < -47 dBc<br>1.25 MHz < -55 dBc<br>2.25 MHz < -55 dBc                            |      | 7.5  |      | W    |
| $\eta_{D(CDMA)}^{(2)}$                          | 885 KHz < -47 dBc<br>1.25 MHz < -55 dBc<br>2.25 MHz < -55 dBc                            |      | 18   |      | %    |
| <b>DYNAMIC</b> ( $f = 1805 - 1880\text{ MHz}$ ) |  |      |      |      |      |
| $P_{1dB}$                                       | $V_{DD} = 26\text{ V}$ $I_{DQ} = \text{TBD}$   | 60   | 65   |      | W    |
| $G_P$   | $V_{DD} = 26\text{ V}$ $I_{DQ} = \text{TBD}$ $P_{OUT} = 60\text{ W}$                     | 11   | 13   |      | dB   |
| $\eta_D^{(1)}$                                  | $V_{DD} = 26\text{ V}$ $I_{DQ} = \text{TBD}$   | 45   |      |      | %    |
| $P_{OUT(EDGE)}$                                 | 400 KHz < -60 dBc<br>600 KHz < -70 dBc $EVM < 3\%$                                       |      | 30   |      | W    |
| $\eta_{D(EDGE)}$                                | 400 KHz < -60 dBc<br>600 KHz < -70 dBc $EVM < 3\%$                                       |      | 25   |      | %    |


(1) 1 dB Compression point (2) IS-97 CDMA Pilot, Sync, Paging, Traffic, Codes 8 Thru 13

**ESD PROTECTION CHARACTERISTICS**

| Test Conditions  | Class |
|------------------|-------|
| Human Body Model | 2     |
| Machine Model    | M3    |

## M265 (.370 x .780 WIDE 2/L N/HERM W/FLG) MECHANICAL DATA

| DIM. | mm    |      |       | Inch  |      |       |
|------|-------|------|-------|-------|------|-------|
|      | MIN.  | TYP. | MAX   | MIN.  | TYP. | MAX   |
| A    | 12.57 |      | 12.83 | .495  |      | .505  |
| B    | 4.32  |      | 5.33  | .170  |      | .210  |
| C    | 9.65  |      | 9.91  | .380  |      | .390  |
| D    | 19.61 |      | 20.02 | .772  |      | .788  |
| E    | 33.91 |      | 34.16 | 1.335 |      | 1.345 |
| F    | 0.08  |      | 0.15  | .003  |      | .006  |
| G    | 0.89  |      | 1.14  | .035  |      | .045  |
| H    | 1.45  |      | 1.70  | .057  |      | .067  |
| I    | 3.18  |      | 4.32  | .125  |      | .170  |
| J    | 9.27  |      | 9.53  | .365  |      | .375  |
| K    | 27.69 |      | 28.19 | 1.090 |      | 1.110 |
| L    | 3.00  |      | 3.51  | .118  |      | .138  |



Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is registered trademark of STMicroelectronics  
© 2003 STMicroelectronics - All Rights Reserved

All other names are the property of their respective owners.

Australia - Brazil - Canada - China - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -  
Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - U.S.A.

<http://www.st.com>