





| | | | | |
|--------|--------------|--------|-------------|--|
| △ | | | Engineering | |
| △ | | | 1 | |
| △ | | | 2 | |
| △ | | | 3 | |
| Symbol | Modify annal | Design | 4 | |
| | | | 5 | |
| | | | 6 | |
| | | | 7 | |
| | | | 8 | |
| | | | 9 | |
| | | | 10 | |
| | | | 11 | |
| | | | 12 | |
| | | | 13 | |
| | | | 14 | |
| | | | 15 | |
| | | | 16 | |
| | | | 17 | |
| | | | 18 | |
| | | | 19 | |
| | | | 20 | |



Specification:

P/N:53100.9

- 1.all size is for after heat-shrinking
- 2.heat-shrink temperature: 120° C
- 3.heat shrink time:90S

| | | | | |
|--|----------|---------|---|--|
| <p><GENERAL TOLERANCE>DIMENSIONS IN mm</p> <p>0.5~3= ±0.1 3~6 ±0.1 6~30 ±0.2</p> <p>Angel: ±0.5°</p> | | |  | |
| | | | <p>Product name</p> <p>Heat-shrinking</p> | |
|  | Approved | Drawing | <p>mateial</p> | |
| <p>Unit.</p> <p>mm</p> | | | <p>Drawing no.</p> <p>53100.9</p> | |