

NOTES:

1. MAXIMUM PERMISSIBLE OUT OF SQUARE OF PIN TO MOULDING TO BE 0.10mm IN ANY DIRECTION.
2. CONTACT LEG VARIATION ON COMPLETE ASSEMBLY NOT TO EXCEED 0.10mm.

**THIS SKETCH IS FOR
QUOTATION PURPOSES
ONLY**

SPECIFICATION:

MATERIAL:

MOULDING = HIGH TEMPERATURE
NYLON 6T, UL94V-0, BLACK

PINS = BRASS

FINISH:

PINS: SEE BOX BELOW

ELECTRICAL:

CURRENT RATING = 1A MAX

CONTACT RESISTANCE = 30 mΩ MAX

INSULATION RESISTANCE = 5,000 MΩ MIN

DIELECTRIC STRENGTH = 500V AC/DC

ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +105°C

PACKING:

BAG

FINISH

(TICK APPLICABLE):



100% TIN




GOLD

DATE OF SKETCH:

REQUESTED BY:

No. OF CONTACTS
PER ROW:



HARWIN

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

TITLE:

1.27 x 2.54mm PITCH DIL VERTICAL
PC TAIL PIN HEADER VARIANT

DRAWING No.:

M52-

W

SHT
1
OF
1

HARWIN INC
U.S.A.
TEL: (812) 542 2540
FAX: (812) 542 2541

HARWIN PLC
U.K.
TEL: 023 9231 4545
FAX: 023 9231 4590

HARWIN PTE
SINGAPORE
TEL: 65 6779 4909
FAX: 65 6779 3868