







2 CIRCUIT RECEPTACLE BRIDGED POLARIZATION OPTION A



2 CIRCUIT RECEPTACLE BRIDGED POLARIZATION OPTION B



2 CIRCUIT RECEPTACLE BRIDGED POLARIZATION OPTION C



2 CIRCUIT RECEPTACLE BRIDGED POLARIZATION OPTION D

NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:

- a. APPLICATION SPECIFICATION SEE: AS-34791-020
- b. PRODUCT SPECIFICATION SEE: PS-34971-020
- c. PACKAGING SPECIFICATION PER MOLEX DRAWING: PK-31301-538
- d. PARTS MUST BE IN COMPLIANCE TO MOLEX CHEMICAL SUBSTANCES FOR PRODUCTS AND PACKAGING SPECIFICATION: QEHS-699000-301
- e. DATA MUST BE SUBMITTED UNDER THE MOLEX PART NUMBER TO IMDS (COMPANY ID#13255)
- f. FLAMMABILITY REQUIREMENT: PER ISO3795 OR GM3191
 - 1. BURN RATE 100 mm/MIN MAXIMUM
 - 2. MATERIAL MUST BE SELF EXTINGUISHING
- g. VISUAL DEFECTS SHALL MEET COSMETIC STANDARD PS-45499-002 (Class B)
- h. FOR TERMINAL USAGE, REFER TO MOLEX SALES DRAWING SD-560023-002 (PLAN OBSOLESCENCE IN 2024) AND 5600230800.

2. DESIGN - MATERIALS:


- a. MATERIAL: UNFILLED PBT

3. DESIGN - GEOMETRY:


- a. THIS IS A 100% CAD GENERATED PART. THE CAD MATHEMATICAL DATA IS THE MASTER FOR THIS PART. FOR DIMENSIONAL OR ANY INFORMATION NOT SHOWN ON THIS DRAWING, ANALYZE THE CAD MODEL.
- b. GEOMETRIC DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994
- c. GENERAL TOLERANCES:
 LINEAR: PER DIN 16901 CODE B FOR PRECISION ENGINEERING
 ANGULAR: $\pm 3^\circ$
- d. EDGES AND UNDIMENSIONED DETAILS PER ISO13715
- e. CORNERS SHOWN AS SHARP TO BE R 0.2 MAX
- f. LETTERING SHALL BE 0.1 MAX RAISED IN 0.15 MAX RECESS PAD AND NOT PROTRUDE THE SURFACE. THIS INCLUDES RECYCLING CODE, PLANT AND CAVITY ID, VENDOR ID, CIRCUIT ID, AND PART SERIES NUMBER.

4. DESIGN - FUNCTIONALITY


- a. HINGE DOES NOT AFFECT FUNCTION OF THE PART.




4 CIRCUIT RECEPTACLE NO BRIDGE POLARIZATION OPTION A




4 CIRCUIT RECEPTACLE NO BRIDGE POLARIZATION OPTION B




4 CIRCUIT RECEPTACLE NO BRIDGE
POLARIZATION OPTION C




4 CIRCUIT RECEPTACLE NO BRIDGE POLARIZATION OPTION D




4 CIRCUIT RECEPTACLE BRIDGED POLARIZATION OPTION A



4 CIRCUIT RECEPTACLE BRIDGED POLARIZATION OPTION B



4 CIRCUIT RECEPTACLE BRIDGED POLARIZATION OPTION C




4 CIRCUIT RECEPTACLE BRIDGED POLARIZATION OPTION D


L8	SHEET 1: ADDED TERMINAL SD-DRAWING 5600230800 IN NOTES 1-H SHEET 4: UPDATED CTX50 UNSEALED RCPT TERMINAL PART NUMBER AND STATUS
L7	MODELS UPDATED, NO GEOMETRY CHANGE SHEET 4: UPDATED SMALL TERMINAL PN ON TERMINAL BOM SHEET 4: ADDED TAPE AND REEL MATING PNs TO BOM
L3	DRAWING REMASTERED SHEET 3: ADDED DIM A FOR PASS THRU SHEET 4: ADDED DIM A TO BOM
L2	NX REMASTERING
REV	DESCRIPTION

FUNCTIONAL SYMBOLS = 0 = 0 = 0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC:										
	MM		6:1												
	GENERAL TOLERANCES (UNLESS SPECIFIED)														
	ANGULAR TOL ± 0.5°														
	4 PLACES		±												
	3 PLACES		±												
2 PLACES		±													
1 PLACE		±													
0 PLACES		±													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
				D-SIZE		34791				GENERAL MARKET		1 OF 4			
molex															
MINI50 SINGLE ROW RECEPTACLE SALES DWG															
PRODUCT SALES DRAWING															
DOCUMENT NUMBER										DOC TYPE		DOC PART		REVISION	
SD-34791-001										PSD		000		L8	
2023-10-20															
2023-10-25															
2023-10-30															
STATUS: Production															
DRWN: Yann Chen															
CHK'D: Gang Li															
APPR: Colin Zhang															


INSPECTION BALLON NUMBER LOG
PER DRAWING REVISION: L8
LAST BALLOON USED: 16
ADDED BALLOON NUMBERS:
REMOVED BALLOON NUMBERS:




8 CIRCUIT RECEPTACLE NO BRIDGE
POLARIZATION OPTION A




8 CIRCUIT RECEPTACLE NO BRIDGE
POLARIZATION OPTION B




8 CIRCUIT RECEPTACLE NO BRIDGE
POLARIZATION OPTION C




8 CIRCUIT RECEPTACLE BRIDGED
POLARIZATION OPTION A



8 CIRCUIT RECEPTACLE BRIDGED
POLARIZATION OPTION B




8 CIRCUIT RECEPTACLE BRIDGED
POLARIZATION OPTION C



2 CIRCUIT RECEPTACLE SHOWN
(AS SHIPPED)

POLARIZATION
FEATURE
LOCATION


POLARIZATION
FEATURE
LOCATION



4 CIRCUIT RECEPTACLE SHOWN
(AS SHIPPED)


MINI50 WITH BRIDGE OPTION
COMES WITH CPA TRAY
REFER TO SD-34824-003 FOR
CPA-RECEPTACLE ASSEMBLIES

RECYCLING CODE




SCALE 7:1

CIRCUIT ID



PART SERIES NUMBER



PLANT CODE & CAVITY ID

SCALE 7:1













FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:				molex			
	DIMENSION UNITS	SCALE								
$\frac{F}{A} = 0$	MM	5:1	GENERAL TOLERANCES (UNLESS SPECIFIED)				MINI50 SINGLE ROW RECEPTACLE SALES DWG			
$\frac{F}{C} = 0$										
$\frac{F}{P} = 0$			ANGULAR TOL $\pm$ 0.5°				PRODUCT SALES DRAWING			
DIVISIONAL SYMBOLS	4 PLACES	$\pm$	STATUS: Production DRWN: Yann Chen CHK'D: Gang Li APPR: Colin Zhang				DOCUMENT NUMBER SD-34791-001			
	3 PLACES	$\pm$					DOC TYPE PSD			
	2 PLACES	$\pm$					DOC PART 000			
	1 PLACE	$\pm$					REVISION L8			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	0 PLACES	$\pm$	2023-10-20 2023-10-25 2023-10-30				MATERIAL NUMBER D-SIZE			
							CUSTOMER GENERAL MARKET			
			THIRD ANGLE PROJECTION		SERIES 34791				SHEET NUMBER 2 OF 4	

8 CIRCUIT

4 CIRCUIT

2 CIRCUIT

NOTE: KEY A SHOWN AS REFERENCE



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
FUNCTIONAL SYMBOLS F A = 0 F C = 0 F P = 0 DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex MINI50 SINGLE ROW RECEPTACLE SALES DWG						
		MM		7:1											
		GENERAL TOLERANCES (UNLESS SPECIFIED)													
		ANGULAR TOL ± 0.5°													
		4 PLACES		±											
3 PLACES		±		STATUS: Production DRWN: Yann Chen CHK'D: Gang Li APPR: Colin Zhang			2023-10-20 2023-10-25 2023-10-30			PRODUCT SALES DRAWING					
2 PLACES		±								DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION
1 PLACE		±								SD-34791-001		PSD		000	L8
0 PLACES		±													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION								DRAWING		SERIES		MATERIAL NUMBER	
						D-SIZE		34791				GENERAL MARKET		3 OF 4	




MINI50 RECEPTACLES

MATERIAL NUMBER BULK PACKAGING PK-31301-538	LOCK BRIDGE OPTION	CONFIGURATION	CIRCUIT	POL	COLOR	DIM A	MATING COMPONENT									
							SURFACE MOUNT TECHNOLOGY (SMT) HEADER-TIN		SURFACE MOUNT TECHNOLOGY (SMT) HEADER-GOLD		VERTICAL THRU HOLE HEADER			RIGHT ANGLE THRU HOLE HEADERS		
							TAPE AND REEL PACKAGING PK-31301-786	TUBE PACKAGING PK-31301-688	TAPE AND REEL PACKAGING PK-31301-786	TUBE PACKAGING PK-31301-688	TRAY PACKAGING PK-31301-440	TUBE PACKAGING PK-31301-688	TAPE AND REEL PACKAGING PK-47799-0001	TRAY PACKAGING PK-31301-440	TUBE PACKAGING PK-31301-688	TAPE AND REEL PACKAGING PK-47799-0001
34791-0040	NO	USCAR COMPATIBLE	4	A	BLACK	15.26	34912-8040	34912-9040	34912-6040	34912-5040	34792-0040	34792-9040	34792-8040	34793-0040	34793-9040	34793-8040
34791-0041	NO	USCAR COMPATIBLE	4	B	GRAY		34912-8041	34912-9041	34912-6041	34912-5041	34792-0041	34792-9041	34792-8041	34793-0041	34793-9041	34793-8041
34791-0042	NO	USCAR COMPATIBLE	4	C	DARK GRAY		34912-8042	34912-9042	34912-6042	34912-5042	34792-0042	34792-9042	34792-8042	34793-0042	34793-9042	34793-8042
34791-0043	NO	USCAR COMPATIBLE	4	D	GREEN		34912-8043	34912-9043	34912-6043	34912-5043	34792-0043	34792-9043	34792-8043	34793-0043	34793-9043	34793-8043
34791-0080	NO	USCAR COMPATIBLE	8	A	BLACK	22.52	34912-8080	34912-9080	34912-6080	34912-5080	34792-0080	34792-9080	34792-8080	34793-0080	34793-9080	34793-8080
34791-0081	NO	USCAR COMPATIBLE	8	B	GRAY		34912-8081	34912-9081	34912-6081	34912-5081	34792-0081	34792-9081	34792-8081	34793-0081	34793-9081	34793-8081
34791-0082	NO	USCAR COMPATIBLE	8	C	DARK GRAY		34912-8082	34912-9082	34912-6082	34912-5082	34792-0082	34792-9082	34792-8082	34793-0082	34793-9082	34793-8082
34791-0140	YES	USCAR COMPATIBLE	4	A	BLACK	16.09	34912-8040	34912-9040	34912-6040	34912-5040	34792-0040	34792-9040	34792-8040	34793-0040	34793-9040	34793-8040
34791-0141	YES	USCAR COMPATIBLE	4	B	GRAY		34912-8041	34912-9041	34912-6041	34912-5041	34792-0041	34792-9041	34792-8041	34793-0041	34793-9041	34793-8041
34791-0142	YES	USCAR COMPATIBLE	4	C	DARK GRAY		34912-8042	34912-9042	34912-6042	34912-5042	34792-0042	34792-9042	34792-8042	34793-0042	34793-9042	34793-8042
34791-0143	YES	USCAR COMPATIBLE	4	D	GREEN		34912-8043	34912-9043	34912-6043	34912-5043	34792-0043	34792-9043	34792-8043	34793-0043	34793-9043	34793-8043
34791-0180	YES	USCAR COMPATIBLE	8	A	BLACK	22.52	34912-8080	34912-9080	34912-6080	34912-5080	34792-0080	34792-9080	34792-8080	34793-0080	34793-9080	34793-8080
34791-0181	YES	USCAR COMPATIBLE	8	B	GRAY		34912-8081	34912-9081	34912-6081	34912-5081	34792-0081	34792-9081	34792-8081	34793-0081	34793-9081	34793-8081
34791-0182	YES	USCAR COMPATIBLE	8	C	DARK GRAY		34912-8082	34912-9082	34912-6082	34912-5082	34792-0082	34792-9082	34792-8082	34793-0082	34793-9082	34793-8082
34791-0020	YES	MOLEX	2	A	BLACK		34912-8020	34912-9020	34912-6020	34912-5020	N/A	N/A	N/A	N/A	N/A	N/A
34791-0021	YES	MOLEX	2	B	GRAY	13.33	34912-8021	34912-9021	34912-6021	34912-5021	N/A	N/A	N/A	N/A	N/A	N/A
34791-0022	YES	MOLEX	2	C	DARK GRAY		34912-8022	34912-9022	34912-6022	34912-5022	N/A	N/A	N/A	N/A	N/A	N/A
34791-0023	YES	MOLEX	2	D	GREEN		34912-8023	34912-9023	34912-6023	34912-5023	N/A	N/A	N/A	N/A	N/A	N/A

CTX50 UNSEALED RECEPTACLE TERMINALS

PART NUMBER		MATERIAL	WIRE GAGE (mm ²)	GRIP	STATUS
D-WIND (LEFT PAYOFF)	B-WIND (RIGHT PAYOFF)				
560023-0448	560023-0450	COPPER ALLOY	0.35	LARGE	PLAN OBSOLESCENCE IN 2024
560023-0421	560023-0423	COPPER ALLOY	0.22	MEDIUM	PLAN OBSOLESCENCE IN 2024
560023-0444	560023-0445	COPPER ALLOY	0.13	SMALL	PLAN OBSOLESCENCE IN 2024
560023-0748	560023-0750	COPPER ALLOY	0.35	LARGE	SALEABLE
560023-0721	560023-0723	COPPER ALLOY	0.22	MEDIUM	SALEABLE
560023-0744	560023-0745	COPPER ALLOY	0.13	SMALL	SALEABLE

L8

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	= 0	DIMENSION UNITS	SCALE
	= 0	MM	7:1
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)	
		ANGULAR TOL	± 0.5°
DIVISIONAL SYMBOLS		4 PLACES	±
		3 PLACES	±
		2 PLACES	±
		1 PLACE	±
		0 PLACES	±
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
		THIRD ANGLE PROJECTION	
			
		D-SIZE	34791
		SERIES	
		MATERIAL NUMBER	
		CUSTOMER	
		SHEET NUMBER	
		STATUS: Production	
		DRWN: Yann Chen	2023-10-20
		CHK'D: Gang Li	2023-10-25
		APPR: Colin Zhang	2023-10-30
		DOCUMENT NUMBER	
		DOC TYPE	
		DOC PART	
		REVISION	
		SD-34791-001	
		PSD	
		000	
		L8	
		GENERAL MARKET	
		4 OF 4	