

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


0676430930

Status:

Active - Custom

Description:

Universal Serial Bus (USB) Shielded I/O Receptacle, Right Angle, Type A, High-Temperature Black Nylon, Gold (Au) Flash, PCB Thickness 1.20mm (.047"), without Upper Flange, for IR Reflow Process, Lead Free



Documents:

Drawing (PDF)

Product Specification PS-67643-002 (PDF)

Test Summary TS-67643-002 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	I/O Connectors
Series	67643
Application	Wire-to-Board
Comments	Without Upper Flange For IR Reflow Process
Component Type	Receptacle
Product Name	USB
Type	A
Physical	
Circuits (Loaded)	4
Circuits (maximum)	4
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.00mm (.079")
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.20mm (.047")
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	2.50mm (.098")
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole

Electrical	
Current - Maximum per Contact	1.5A
Shielded	Yes
Voltage - Maximum	30V

Solder Process Data	
Lead-free Process Capability	SMC & Wave Capable (TH only)
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers	
Product Specification	PS-67643-002
Sales Drawing	SD-67643-003
Test Summary	TS-67643-002

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

67643Series

Mates With

USB Type A Plug

This document was generated on 02/23/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION