

# FAN21SV04 — TinyBuck™ 4A, 24V Single-Input Integrated Synchronous Buck Regulator

## Features

- Single-Supply Operation with 4A Output Current
- Wide Input Range with Dual Supply: 3.0V to 24V
- Wide Output Voltage Range: 0.8V to 80%  $V_{IN}$
- Over 94% Peak Efficiency
- 1% Reference Accuracy Over Temperature
- Fully Synchronous Operation with Integrated Schottky Diode on Low-Side MOSFET Boosts Efficiency
- Single Supply Device for  $V_{IN} > 6.5V - 24V$
- Programmable Frequency Operation (200-600KHz)
- Synchronizable to External Clock with Master/Slave Provisions
- Power-Good Signal
- Accepts Ceramic Capacitors on Output
- External Compensation for Flexible Design
- Starts on Pre-Bias Outputs
- Integrated Bootstrap Diode
- Programmable Over-Current Protection
- Under-Voltage, Over-Voltage, and Thermal-Shutdown Protections
- 5x6mm, 25-Pin, 3-Pad MLP Package

## Applications

- Servers & Telecom
- Graphics Cards & Displays
- Computing Systems
- Set-Top Boxes & Game Consoles
- Point-of-Load Regulation

## Description

The FAN21SV04 TinyBuck™ is a highly efficient, small-footprint, programmable-frequency, 4A, integrated synchronous buck regulator.

FAN21SV04 contains both synchronous MOSFETs and a controller/driver with optimized interconnects in one package, which enables designers to solve high-current requirements in a small area with minimal external components, thereby reducing cost. On-board internal 5V regulator enables single-supply operation for input voltages  $>6.5V$ .

The FAN21SV04 can be configured to drive multiple slave devices OR synchronize to an external system clock. In slave mode, FAN21SV04 may be set up to be free-running in the absence of a master clock signal.

External compensation, programmable switching frequency, and current-limit features allow for design optimization and flexibility. High-frequency operation allows for all-ceramic solutions.

Fairchild's advanced BiCMOS power process, combined with low- $R_{DS(ON)}$  internal MOSFETs and a thermally efficient MLP package, provide the ability to dissipate high power in a small package. Integration helps minimize critical inductances, making layout simpler and more efficient compared to discrete solutions.

Output over-voltage, under-voltage, over-current, and thermal-shutdown protections help protect the device from damage during fault conditions. FAN21SV04 prevents pre-biased output discharge during startup in point-of-load applications.

## Related Application Notes

[AN-8022 — TinyCalc™ Calculator](#)

## Ordering Information

| Part Number   | Operating Temperature Range |  Eco Status | Package                             | Packing Method |
|---------------|-----------------------------|------------------------------------------------------------------------------------------------|-------------------------------------|----------------|
| FAN21SV04MPX  | -10°C to 85°C               | Green                                                                                          | Molded Leadless Package (MLP) 5x6mm | Tape and Reel  |
| FAN21SV04EMPX | -40°C to 85°C               | Green                                                                                          | Molded Leadless Package (MLP) 5x6mm | Tape and Reel  |

 For Fairchild's definition of Eco Status, please visit: [http://www.fairchildsemi.com/company/green/rohs\\_green.html](http://www.fairchildsemi.com/company/green/rohs_green.html).



## Pin Configuration




Figure 3. MLP 5x6mm Pin Configuration (Bottom View)

## Pad / Pin Definitions

| Pad / Pin | Name           | Description                                                                                                                                                                                                                                                                                                             |
|-----------|----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| P1, 6-12  | SW             | <b>Switching Node.</b> Junction of high-side and low-side MOSFETs.                                                                                                                                                                                                                                                      |
| P2, 3-5   | VIN            | <b>Power Conversion Input Voltage.</b> Connect to the main input power source.                                                                                                                                                                                                                                          |
| P3, 21-23 | PGND           | <b>Power Ground.</b> Power return and Q2 source.                                                                                                                                                                                                                                                                        |
| 1         | BOOT           | <b>High-Side Drive BOOT Voltage.</b> Connect through capacitor ( $C_{BOOT}$ ) to SW. The IC has an internal synchronous bootstrap diode to recharge the capacitor on this pin to 5V_Reg when SW is LOW.                                                                                                                 |
| 2         | VIN_Reg        | <b>Regulator Input Voltage.</b> Input voltage to the internal regulator. Connect to input voltage >6.5V with 10 $\Omega$ resistor and a 1 $\mu$ F bypass capacitor at the pin (see Figure 10).                                                                                                                          |
| 13        | PGOOD          | <b>Power-Good.</b> An open-drain output that pulls LOW when the voltage on the FB pin is outside the specified limits. PGOOD does not assert HIGH until the fault latch is enabled (see Figure 31).                                                                                                                     |
| 14        | EN             | <b>ENABLE.</b> Enables operation when pulled to logic HIGH or left open. Toggling EN resets the regulator after a latched-fault condition. This input has an internal pull-up. When a latched fault occurs, EN is discharged by a current sink.                                                                         |
| 15        | 5V_Reg         | <b>5V Regulator Output.</b> Internal regulator output that provides power for the IC's logic and analog circuitry. This pin should be connected to AGND through a >2.2 $\mu$ F X5R/X7R capacitor.                                                                                                                       |
| 16        | AGND           | <b>Analog Ground.</b> The signal ground for the IC. All internal control voltages are referred to this pin. Tie this pin to the ground island/plane through the lowest impedance connection.                                                                                                                            |
| 17        | ILIM           | <b>Current Limit.</b> A resistor ( $R_{ILIM}$ ) from this pin to AGND can be used to program the current-limit trip threshold lower than the internal default setting.                                                                                                                                                  |
| 18        | R <sub>T</sub> | <b>Switching Frequency and Master/Slave Set.</b> Connecting a resistor ( $R_T$ ) to AGND sets the switching frequency and configures the CLK pin as an output (master). Tying this pin to 5V_Reg through a resistor configures the CLK signal as an input (slave) and establishes the free-running switching frequency. |
| 19        | FB             | <b>Output Voltage Feedback.</b> Connect through a resistor divider to the output voltage.                                                                                                                                                                                                                               |
| 20        | COMP           | <b>Compensation.</b> Error amplifier output. Connect the external compensation network between this pin and FB.                                                                                                                                                                                                         |
| 24        | CLK            | <b>Clock.</b> Bi-directional signal pin, depending on master/slave configuration. When configured as a master, this pin represents the clock output that connects directly to the slave(s) for synchronizing with 180° phase shift.                                                                                     |
| 25        | RAMP           | <b>Ramp Amplitude.</b> A resistor ( $R_{RAMP}$ ) connected from this pin to VIN sets the internal ramp amplitude and also provides voltage feedforward functionality.                                                                                                                                                   |

## Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

| Parameter            | Conditions                                               | Min.                              | Max. | Units |
|----------------------|----------------------------------------------------------|-----------------------------------|------|-------|
| VIN, VIN_Reg to AGND | AGND=PGND                                                |                                   | 28   | V     |
| 5V_Reg to AGND       | AGND=PGND                                                |                                   | 6    | V     |
| BOOT to PGND         |                                                          |                                   | 35   | V     |
| BOOT to SW           |                                                          | -0.5                              | 6.0  | V     |
| SW to PGND           | Continuous                                               | -0.5                              | 24.0 | V     |
|                      | Transient ( $t < 20\text{ns}$ , $f \leq 600\text{KHz}$ ) | -5                                | 30   |       |
| All other pins       |                                                          | -0.3                              | 6.0  | V     |
| ESD                  | Electrostatic Discharge Protection Level                 | Human Body Model, JESD22-A114     | 1.5  | kV    |
|                      |                                                          | Charged Device Model, JESD22-C101 | 2.5  |       |

## Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

| Symbol                                    | Parameter                         | Conditions      | Min. | Typ. | Max  | Units |
|-------------------------------------------|-----------------------------------|-----------------|------|------|------|-------|
| $f_{\text{SW}}$                           | Switching Frequency               |                 | 200  | 500  | 600  | KHz   |
| $V_{\text{IN}}$ ,<br>$V_{\text{IN\_Reg}}$ | Supply Voltage for Power and Bias | VIN to PGND     | 3.0  |      | 24.0 | V     |
|                                           |                                   | VIN_Reg to AGND | 6.5  |      | 24.0 |       |
| $T_{\text{A}}$                            | Ambient Temperature               | FAN21SV04MPX    | -10  |      | +85  | °C    |
|                                           |                                   | FAN21SV04EMPX   | -40  |      | +85  |       |
| $T_{\text{J}}$                            | Junction Temperature              |                 |      |      | +125 | °C    |

## Thermal Information

| Symbol                  | Parameter                                                                       | Min.    | Typ. | Max. | Units |
|-------------------------|---------------------------------------------------------------------------------|---------|------|------|-------|
| $T_{\text{STG}}$        | Storage Temperature                                                             | -65     |      | +150 | °C    |
| $T_{\text{L}}$          | Lead Soldering Temperature, 30 Seconds                                          |         |      | +300 | °C    |
| $\theta_{\text{JC}}$    | Thermal Resistance: Junction-to-Case                                            | P1 (Q2) | 4    |      | °C/W  |
|                         |                                                                                 | P2 (Q1) | 7    |      |       |
|                         |                                                                                 | P3      | 4    |      |       |
| $\theta_{\text{J-PCB}}$ | Thermal Resistance: Junction-to-Mounting Surface <sup>(1)</sup>                 |         | 35   |      | °C/W  |
| $P_{\text{D}}$          | Total Power Dissipation in the package, $T_{\text{A}}=25^{\circ}\text{C}^{(1)}$ |         |      | 2.8  | W     |

### Note:

1. Typical thermal resistance when mounted on a four-layer, two-ounce PCB, as shown in Figure 38. Actual results are dependent upon mounting method and surface related to the design.

## Electrical Characteristics

Recommended operating conditions and using the circuit shown in Figure 1, with  $V_{IN}$ ,  $V_{IN\_Reg}=12V$ , unless otherwise noted.

| Parameter                                                                   | Conditions                                          | Min. | Typ. | Max. | Units |
|-----------------------------------------------------------------------------|-----------------------------------------------------|------|------|------|-------|
| Power Supplies                                                              |                                                     |      |      |      |       |
| Operating Current (VIN+VIN_Reg)                                             | VIN=12V, 5V_Reg Open, CLK Open, fSW=500KHz, No Load |      | 22   | 30   | mA    |
| VIN_Reg Operating Current                                                   | EN=High, 5V_Reg Open, CLK Open, fSW=500KHz          |      | 11   |      | mA    |
| VIN_Reg Quiescent Current                                                   | EN=High, FB=0.9V                                    |      | 4    | 5    | mA    |
| VIN_Reg Standby Current                                                     | EN=0, VIN=12V                                       |      |      | 1    | mA    |
| 5V_Reg Output Voltage                                                       | Internal VCC Regulator, No Load, 6.5V<VIN_Reg<24V   | 4.7  | 5.0  | 5.3  | V     |
| 5V_Reg Max. Current Load                                                    | VIN_Reg=12V                                         |      |      | 5    | mA    |
| VIN_Reg UVLO Threshold                                                      | Rising VIN, VIN=VIN_Reg                             |      | 5.6  | 6.3  | V     |
|                                                                             | Falling VIN, VIN=VIN_Reg                            |      |      | 5    | V     |
| Reference                                                                   |                                                     |      |      |      |       |
| Reference Voltage measured at FB (See Figure 4 for Temperature Coefficient) | FAN21SV04MPX, TA=25°C                               | 794  | 800  | 806  | mV    |
|                                                                             | FAN21SV04EMPX, TA=25°C                              | 795  | 800  | 805  |       |
| Oscillator                                                                  |                                                     |      |      |      |       |
| Frequency                                                                   | RT=50kΩ to GND (Master Mode)                        | 255  | 300  | 345  | KHz   |
|                                                                             | RT=24kΩ to GND (Master Mode)                        | 540  | 600  | 660  |       |
| Frequency in Slave Mode Compared to Master Mode                             | RT=24 kΩ to 50kΩ to 5V_Reg (Slave Mode)             | -15  |      | +15  | %     |
| Minimum On Time <sup>(2)</sup>                                              |                                                     |      | 40   | 65   | ns    |
| Duty Cycle                                                                  | VIN=6.5V, fSW=600KHz                                |      | 80   | 85   | %     |
| Ramp Amplitude, Peak-to-Peak <sup>(2)</sup>                                 | VIN=16V, 1.8VOUT, RT=30kΩ, RRAMP=200kΩ              |      | 0.5  |      | V     |
| Minimum Off Time <sup>(2)</sup>                                             |                                                     |      | 100  | 150  | ns    |
| Synchronization                                                             |                                                     |      |      |      |       |
| CLK Output Pulse Width                                                      | Master (RT to GND)                                  | 70   | 85   | 100  | ns    |
| CLK Output Sink Current                                                     | Master, VCLK=0.4V                                   | 0.25 |      | 0.35 | mA    |
| CLK Output Source Current                                                   | Master, VCLK=2V                                     | -2.5 |      | -2.0 | mA    |
| CLK Input Pulse Width                                                       | Slave: VCLK ≥ 2V                                    | 50   |      |      | ns    |
| CLK Input Source Current                                                    | Slave: VCLK=1V                                      | -230 | -200 | -170 | μA    |
| CLK Input Threshold, Rising                                                 | Slave                                               | 1.73 | 1.83 | 1.93 | V     |
| Soft-Start                                                                  |                                                     |      |      |      |       |
| VOUT to Regulation (T0.8)                                                   | Frequency=500KHz                                    |      | 2.5  |      | ms    |
| Fault Enable/SSOK (T1.0)                                                    |                                                     |      | 3.1  |      | ms    |
| Error Amplifier                                                             |                                                     |      |      |      |       |
| DC Gain <sup>(2)</sup>                                                      | VIN_Reg > 6.5V                                      | 80   | 85   |      | dB    |
| Gain Bandwidth Product <sup>(2)</sup>                                       |                                                     | 12   | 15   |      | MHz   |
| Output Voltage Swing (VCOMP)                                                |                                                     | 0.4  |      | 4.0  | V     |
| Output Current, Sourcing                                                    | 5V_Reg=5V, VCOMP=2.2V                               | 1.5  | 2.2  | 2.5  | mA    |
| Output Current, Sinking                                                     | 5V_Reg=5V, VCOMP=1.2V                               | 0.8  | 1.2  | 1.5  | mA    |
| FB Bias Current                                                             | VFB=0.8V, TA=25°C                                   | -850 | -650 | -450 | nA    |

### Note:

- Specifications guaranteed by design and characterization; not production tested.

**Electrical Characteristics** (Continued)

Recommended operating conditions and using the circuit shown in Figure 1 with  $V_{IN}$ ,  $V_{IN\_Reg}=12V$ , unless otherwise noted.


| Parameter                      | Conditions                                                                                                             | Min.  | Typ.  | Max.  | Units       |
|--------------------------------|------------------------------------------------------------------------------------------------------------------------|-------|-------|-------|-------------|
| <b>Control Functions</b>       |                                                                                                                        |       |       |       |             |
| EN Threshold, Rising           |                                                                                                                        |       | 1.35  | 2.00  | V           |
| EN Hysteresis                  |                                                                                                                        |       | 250   |       | mV          |
| EN Pull-Up Resistance          | $V_{IN\_Reg} > 6.5V$                                                                                                   |       | 800   |       | $K\Omega$   |
| EN Discharge Current           | Auto-Restart Mode, $V_{IN\_Reg} > 6.5V$                                                                                |       | 1     |       | $\mu A$     |
| FB OK Drive Resistance         |                                                                                                                        |       | 800   | 1000  | $K\Omega$   |
| PGOOD Low Threshold            | $FB < V_{REF}$ , 2 Consecutive Clock Cycles <sup>(3)</sup>                                                             | -14.0 | -11.0 | -8.0  | % $V_{REF}$ |
|                                | $FB > V_{REF}$ , 2 Consecutive Clock Cycles <sup>(3)</sup>                                                             | +7.0  | +10.0 | +13.5 |             |
| PGOOD Low Voltage              | $I_{OUT} \leq 2mA$                                                                                                     |       |       | 0.4   | V           |
| PGOOD Leakage Current          | $V_{PGOOD}=5V$                                                                                                         |       | 0.2   | 1.0   | $\mu A$     |
| <b>Protection and Shutdown</b> |                                                                                                                        |       |       |       |             |
| Current Limit                  | $R_{ILIM}$ open, $f_{SW}=500KHz$ , $V_{OUT}=1.8V$ , $R_{RAMP}=200k\Omega$ , 16 Consecutive Clock Cycles <sup>(3)</sup> | 5.5   | 6.5   | 7.5   | A           |
| $I_{LIM}$ Current              | $V_{IN\_Reg} > 6.5V$ , $T_A=25^\circ C$                                                                                | -11   | -10   | -9    | $\mu A$     |
| Over-Temperature Shutdown      | Internal Temperature                                                                                                   |       | +155  |       | $^\circ C$  |
| Over-Temperature Hysteresis    |                                                                                                                        |       | +30   |       | $^\circ C$  |
| Over-Voltage Threshold         | 2 Consecutive Clock Cycles <sup>(3)</sup>                                                                              | 110   | 115   | 120   | % $V_{OUT}$ |
| Under-Voltage Shutdown         | 16 Consecutive Clock Cycles <sup>(3)</sup>                                                                             | 68    | 73    | 78    | % $V_{OUT}$ |
| Fault-Discharge Threshold      | Measured at FB pin                                                                                                     |       | 250   |       | mV          |
| Fault-Discharge Hysteresis     | Measured at FB pin ( $V_{FB} \sim 500mV$ )                                                                             |       | 250   |       | mV          |

**Note:**


3. Delay times are not tested in production. Guaranteed by design.

## Typical Characteristics


$V_{IN}=12V$ ,  $V_{CC}=5V$ ,  $T_A=25^{\circ}C$ , unless otherwise specified.




**Figure 4. Reference Voltage ( $V_{FB}$ ) vs. Temperature, Normalized**




**Figure 5. Reference Bias Current ( $I_{FB}$ ) vs. Temperature, Normalized**




**Figure 6. Frequency vs.  $R_T$  (Master)**



**Figure 7. Frequency vs. Temperature, Normalized**



**Figure 8.  $R_{DS}$  vs. Temperature, Normalized ( $5V_{Reg}=V_{GS}=5V$ )**



**Figure 9.  $I_{ILIM}$  Current ( $I_{ILIM}$ ) vs. Temperature, Normalized**

# Application Circuit




Figure 10. Single-Supply Application Circuit: 1.8V<sub>OUT</sub>, 500KHz, Master, 8V – 20V Input




Figure 11. Single-Supply Application Circuit: 1.2 V<sub>OUT</sub>, 500KHz, Master 8V – 20V Input

## Typical Performance Characteristics

Typical operating characteristics using the Figure 10 circuit;  $V_{IN}=12V$ ,  $V_{CC}=5V$ ,  $T_A=25^\circ C$ , unless otherwise specified.




Figure 12. 1.8 V<sub>OUT</sub> Efficiency Over  $V_{IN}$  vs. Load




Figure 13. 3.3 V<sub>OUT</sub> Efficiency, 500KHz<sup>(4)</sup>




Figure 14. 1.8 V<sub>OUT</sub> Efficiency, 300KHz<sup>(4)</sup>




Figure 15. 3.3 V<sub>OUT</sub> Efficiency, 300KHz<sup>(4)</sup>




Figure 16. 1.2 V<sub>OUT</sub> Efficiency, 500KHz (Figure 11)




Figure 17. 5 V<sub>OUT</sub> Efficiency, 300KHz<sup>(4)</sup>

### Note:

4. Circuit values for this configuration change in Figure 10.

## Typical Performance Characteristics (Continued)

Typical operating characteristics using the Figure 10 circuit;  $V_{IN}=12V$ ,  $V_{CC}=5V$ ,  $T_A=25^{\circ}C$ , unless otherwise specified.




Figure 18. 1.8 V<sub>OUT</sub> Line Regulation




Figure 19. 1.8 V<sub>OUT</sub> Load Regulation




Figure 20. Peak MOSFET Temperatures  
3.3V Output, 12V and 24V Input (500KHz)<sup>(5)</sup>




Figure 21. Peak Case Temperature Over MOSFET  
Locations 5V Output (300KHz)




Figure 22. 1.8 V<sub>OUT</sub> Efficiency Over  $f_{sw}$




Figure 23. Typical Output Operating Area Based on  
Thermal Limitations

### Note:

5. Circuit values for this configuration change in Figure 10.

## Typical Performance Characteristics (Continued)

Typical operating characteristics using the Figure 10 circuit.  $V_{IN}=12V$  unless otherwise specified.




Figure 24. CLK and  $V_{OUT}$  at Startup




Figure 25. Transient Response, 2-4A Load




Figure 26. Startup on Pre-Bias




Figure 27. Restart on Fault




Figure 28. Shutdown, 1A Load




Figure 29. Slave (500KHz Free-Run to 600KHz Synchronization)

## Circuit Operation

### PWM Generation

Refer to Figure 2 for the PWM control mechanism. FAN21SV04 uses the summing-mode method of control to generate the PWM pulses. An amplified current-sense signal is summed with an internally generated ramp and the combined signal is compared with the output of the error amplifier to generate the pulse width to drive the high-side MOSFET. Sensed current from the previous cycle is used to modulate the output of the summing block. The output of the summing block is also compared against a voltage threshold set by the  $R_{LIM}$  resistor to limit the inductor current on a cycle-by-cycle basis.  $R_{RAMP}$  resistor helps set the charging current for the internal ramp and provides input voltage feed-forward function. The controller facilitates external compensation for enhanced flexibility.

### Initialization

Once  $V_{IN\_Reg}$  voltage exceeds the UVLO threshold and EN is HIGH, the IC checks for a shorted FB pin before releasing the internal soft-start ramp (SS).

If the parallel combination of  $R_1$  and  $R_{BIAS}$  is  $\leq 1k\Omega$ , the internal SS ramp is not released and the regulator does not start.

### Enable

FAN21SV04 has an internal pull-up to the enable (EN) pin so that the IC is enabled once  $V_{IN\_Reg}$  exceeds the UVLO threshold. Connecting a small capacitor across EN and AGND delays the rate of voltage rise on the EN pin. The EN pin also serves for the restart whenever a fault occurs (refer to the *Auto-Restart* section). If the regulator is enabled externally, the external EN signal should go HIGH only after  $5V_{Reg}$  is established. For applications where such sequencing is required, FAN21SV04 can be enabled (after the  $V_{CC}$  comes up) with external control, as shown in Figure 30.

If auto-restart is not desired, tie the EN pin HIGH with a logic gate to keep the  $1\mu A$  current sink from discharging EN to 1.1V. Figure 32 shows one method to pull up EN to  $V_{CC}$  for a latch configuration.




Figure 30. Enabling with External Control

### Internal Regulator

FAN21SV04 facilitates single-supply operation for input voltages  $>6.5V$ . At startup, the output of the internal regulator tracks the input voltage and comes into regulation (5V) when  $V_{IN\_Reg}$  exceeds the UVLO threshold. The EN pin is released at the same time. The output voltage of the internal regulator ( $5V_{Reg}$ ) is set to 5V. The internal regulator supplies power to all the control circuits including the drivers.

For applications with  $V_{IN} < 6.5V$ , FAN21SV04 can be used if  $V_{IN\_Reg}$  is provided with a separate low-power source  $>6.5V$ .  $V_{IN\_Reg}$  supply should come up after  $V_{IN}$  during dual-supply operation. The  $V_{IN\_Reg}$  pin should always be decoupled with at least a  $10\Omega$  resistor and a  $1\mu F$  ceramic capacitor (see Figure 10, Figure 11).

Since  $5V_{Reg}$  is used to drive the internal MOSFET gates, high peak currents are present on the  $5V_{Reg}$  pin. Connect a  $\geq 2.2\mu F$  X5R or X7R decoupling capacitor between the  $5V_{Reg}$  pin and AGND. For  $V_{IN} > 20V$  operation, use a  $3.3\Omega$  resistor in series with the boot capacitor to reduce noise into the regulator.

In addition to supplying power for the control circuits internally,  $5V_{Reg}$  output can be used as a reference voltage for other applications requiring low noise reference voltage.  $5V_{Reg}$  is capable of sourcing up to 5mA of output current.

When EN is pulled LOW externally,  $5V_{Reg}$  output is still present, but the IC is in standby mode with no switching.

### Soft-Start

FAN21SV04 uses an internal digital soft-start circuit to slowly ramp up the output voltage and limit inrush current during startup. When  $5V_{Reg}$  is in regulation and EN is HIGH, the circuit releases SS and enables the PWM regulator. Soft-start time is a function of the switching frequency (number of clock cycles).

Once internal SS ramp has charged to 0.8V ( $T_{0.8}$ ), the output voltage is in regulation. Until SS ramp reaches 1.0V ( $T_{1.0}$ ), only the over-current-protection circuit is active during soft-start and all other output protections are inhibited.

In dual-supply operation mode, it is necessary to apply  $V_{IN}$  before  $V_{IN\_Reg}$  reaches its UVLO threshold to avoid skipping the soft-start cycle.

$V_{IN\_Reg}$  UVLO or toggling the EN pin discharges the SS and resets the IC.




Figure 31. Typical Soft-Start Timing Diagram

### Startup on Pre-Bias

The regulator does not allow the low-side MOSFET to operate in full synchronous mode until SS reaches 95% of  $V_{REF}$  (~0.76V). This enables the regulator to startup on a pre-biased output and ensures that output is not discharged during the soft-start cycle.

### Protections

The converter output is monitored and protected against extreme overload, short-circuit, over-voltage, and under-voltage conditions.

#### Under-Voltage Protection

If FB remains below the under-voltage threshold for 16 consecutive clock cycles, the fault latch is set and the converter shuts down. This protection is not active until the internal SS ramp reaches 1.0V during soft-start.

#### Over-Voltage Protection

If FB exceeds  $115\% \cdot V_{REF}$  for two consecutive clock cycles, the fault latch is set and shutdown occurs.

A shorted high-side MOSFET condition is detected when SW voltage exceeds ~0.7V while the low-side MOSFET is fully enhanced. The fault latch is set immediately upon detection.

The OV/UV fault conditions are not allowed to set the fault latch during soft-start. They are active only after T1.0 (see Figure 31).

### Over-Temperature Protection

The chip incorporates an over-temperature protection circuit that sets the fault latch when a die temperature of about 155°C is reached. The IC is allowed to restart when the die temperature falls below 125°C.

### Auto-Restart

After a fault, the EN pin is discharged with 1μA current pull-down to a 1.1V threshold before the internal 800kΩ pull-up is restored. A new soft-start cycle begins when EN charges above 1.35V.

Depending on the external circuit, the FAN21SV04 can be configured to remain latched off or automatically restart after a fault, as listed in Table 1.

Table 1. Fault / Restart Configurations

| EN Pin                         | Controller / Restart State                                |
|--------------------------------|-----------------------------------------------------------|
| Pull to GND                    | OFF (Disabled)                                            |
| Connected to 5V_Reg with 100kΩ | No Restart – Latched OFF                                  |
| Open                           | Immediate Restart After Fault                             |
| Cap to GND                     | New Soft-Start Cycle After EN is HIGH (Auto Restart Mode) |

With EN left open, restart is immediate.

If auto-restart is not desired, tie the EN pin HIGH with a logic gate to keep the 1μA current sink from discharging EN to 1.1V. Figure 32 shows one method to pull up EN to  $V_{CC}$  for a latch configuration.




Figure 32. Enable Control with Latch Option

### Power Good (PGOOD) Signal

PGOOD is an open-drain output that asserts LOW when  $V_{OUT}$  is out of regulation, as measured at the FB pin. The thresholds are specified in the Electrical Specifications section. PGOOD does not assert HIGH until soft start is complete (T1.0) (see Figure 31).

## Application Information

### 5V\_Reg Output

The 5V\_Reg pin is the output of the internal regulator that supplies all power to the control circuit. It is important to keep this pin decoupled to AGND with a  $\geq 2.2\mu\text{f}$  X5R or X7R decoupling capacitor. In addition, for operation with  $V_{\text{IN}} > 20\text{V}$ , add a  $3.3\Omega$  resistor in series with the boot capacitor to reduce the switching noise into the regulator.

### Setting the Output Voltage

The output voltage of the regulator can be set from 0.8V to  $\sim 80\%$  of  $V_{\text{IN}}$  by an external resistor divider ( $R_1$  and  $R_{\text{BIAS}}$  in Figure 1). For output voltages  $> 3.3\text{V}$ , output current rating may need to be de-rated depending on the ambient temperature, power dissipated in the package, and the PCB layout (refer to *Thermal Information table on page 4, Figure 20, Figure 21, and Figure 23*).

The internal reference is set to 0.8V with 650nA sourced from the FB pin to ensure that the regulator does not start if the pin is left open.

The external resistor divider is calculated using:

$$\frac{0.8\text{V}}{R_{\text{BIAS}}} = \frac{V_{\text{OUT}} - 0.8\text{V}}{R_1} + 650\text{nA} \quad (1)$$

Connect  $R_{\text{BIAS}}$  between FB and AGND.

If  $R_1$  is open (see Figure 1), the output voltage is not regulated and a latched fault occurs after the SS is complete (T1.0).

If the parallel combination of  $R_1$  and  $R_{\text{BIAS}}$  is  $\leq 1\text{k}\Omega$ , the internal SS ramp is not released and the regulator does not start.

### Setting the Switching Frequency

Switching frequency is determined by a resistor,  $R_T$ , connected between the  $R_T$  pin and AGND (Master Mode) or 5V\_Reg (Slave Mode):

where  $R_T$  is expressed in  $\text{k}\Omega$ :

$$R_{T(\text{k}\Omega)} = \frac{(10^6 / f) - 135}{65} \quad (2)$$

where frequency (f) is expressed in KHz.

In Slave Mode, the switching frequency is about 10% slower for the same  $R_T$ . The regulator does not start if  $R_T$  is open in Master Mode.

### Calculating the Inductor Value

Typically the inductor value is chosen based on ripple current ( $\Delta I_L$ ), which is chosen between 10 to 35% of the maximum DC load. Regulator designs that require fast

transient response use a higher ripple-current setting while regulator designs that require higher efficiency keep ripple current on the low side and operate at a lower switching frequency. The inductor value is calculated by the following formula:

$$L = \frac{V_{\text{OUT}} \cdot (1 - \frac{V_{\text{OUT}}}{V_{\text{IN}}})}{\Delta I_L \cdot f} \quad (3)$$

where f is the switching frequency.

### Setting the Ramp Resistor Value

$R_{\text{RAMP}}$  resistor plays a critical role by providing charging current to the internal ramp capacitor and also serving as a means to provide input voltage feedforward.

$R_{\text{RAMP}}$  is calculated by the following formula:

$$R_{\text{RAMP}(\text{k}\Omega)} = \frac{(V_{\text{IN}} - 1.8) \cdot V_{\text{OUT}}}{(30.5 - 4.5 \cdot I_{\text{OUT}}) \cdot V_{\text{IN}} \cdot f \cdot 10^{-6}} - 2 \quad (4)$$

where frequency (f) is expressed in KHz.

For wide input operation, first calculate  $R_{\text{RAMP}}$  for the minimum and maximum input voltage conditions and use larger of the two values calculated.

In all applications, current through the  $R_{\text{RAMP}}$  pin must be greater than  $10\mu\text{A}$  from the equation below for proper operation:

$$\frac{V_{\text{IN}} - 1.8}{R_{\text{RAMP}} + 2} \geq 10\mu\text{A} \quad (5)$$

If the calculated  $R_{\text{RAMP}}$  values in Equation (4) result in a current less than  $10\mu\text{A}$ , use the  $R_{\text{RAMP}}$  value that satisfies Equation (5). In applications with large input ripple voltage, the  $R_{\text{RAMP}}$  resistor should be adequately decoupled from the input voltage to minimize ripple on the ramp pin.

### Setting the Current Limit

There are two levels of current-limit thresholds in FAN21SV04. The first level of protection is through an internal default limit set at the factory to provide cycle-by-cycle current limit and prevent output current beyond normal levels. The second level of protection is set at the ILIM pin by connecting a resistor ( $R_{\text{ILIM}}$ ) between ILIM and AGND. Current-limit protection is enabled whenever the lower of the two thresholds is reached (see Figure 33). The FAN21SV04 uses its internal low-side MOSFET as the current-sensing element. The current-limit threshold voltage ( $V_{\text{ILIM}}$ ) is compared to the voltage drop across the low-side MOSFET sampled at the end of each PWM off-time cycle. The internal default threshold ( $I_{\text{LIM}}$  open) is temperature compensated.




Figure 33. ILIM Network

The ILIM pin can source a 10µA current that can be used to establish a lower, temperature-dependent, current-limit threshold by connecting an external resistor ( $R_{ILIM}$ ) to AGND.  $R_{ILIM}$  can be approximated with the equation:

$$R_{ILIM}(K\Omega) = 95 + 15.1 \cdot I_{OUT} + \frac{(V_{IN} - 1.8) \cdot V_{OUT} \cdot 3.33 \cdot 10^6}{(R_{RAMP} + 2) \cdot V_{IN} \cdot f} \quad (6)$$

where:

- $I_{OUT}$  = Full load current in Amps;
- $V_{OUT}$  = Set output voltage;
- $V_{IN}$  = Input voltage;
- $R_{RAMP}$  = Ramp resistor used in KΩ; and
- $f$  = Selected switching frequency in KHz.

After 16 consecutive pulse-by-pulse current-limit cycles, the fault latch is set and the regulator shuts down. Cycling VIN\_Reg or EN restores operation after a normal soft-start cycle (refer to the Auto-Restart section).

The over-current protection fault latch is active during the soft-start cycle. Use a 1% resistor for  $R_{ILIM}$ . For a given  $R_{RAMP}$  and  $R_{ILIM}$  setting, the current-limit point varies slightly in an inverse relationship to  $V_{IN}$ . If  $R_{ILIM}$  is not connected, the IC uses the internal default current-limit threshold.

## Loop Compensation

The control loop is compensated using a feedback network around the error amplifier. Figure 34 shows a complete Type-3 compensation network. Type-2 compensation eliminates  $R_3$  and  $C_3$ .




Figure 34. Compensation Network

Since the FAN21SV04 employs summing current-mode architecture, Type-2 compensation can be used for many applications. For applications that require wide loop bandwidth and/or use very low-ESR output capacitors, Type-3 compensation may be required.

$R_{RAMP}$  provides feedforward compensation for changes in  $V_{IN}$ . With a fixed  $R_{RAMP}$  value, the modulator gain increases as  $V_{IN}$  is reduced, which can make it difficult to compensate the loop. For low-input-voltage-range designs (3V to 8V),  $R_{RAMP}$  and the compensation component values are different as compared to designs with  $V_{IN}$  between 8V and 24V.

## Master / Slave Configuration

When first enabled, the IC determines if it is configured as a master or slave for synchronization, depending on how  $R_T$  is connected.

Table 2. Master / Slave Configuration

| $R_T$ to: | Master / Slave      | CLK Pin |
|-----------|---------------------|---------|
| GND       | Master              | Output  |
| 5V_Reg    | Slave, free-running | Input   |

Slaves free-run in the absence of an external clock signal input when  $R_T$  is connected to 5V\_Reg, allowing regulation to be maintained. It is not recommended to leave  $R_T$  open when running in Slave Mode to avoid noise pick up on the clock pin.

Slave free-running frequency should be set at least 25% lower than the incoming synchronizing pulse frequency. Maximum synchronizing clock frequency is recommended to be below 600KHz.

## Synchronization

The synchronization method employed by the FAN21SV04 also provides the following features for maximum flexibility.

- Synchronization to an external system clock
- Multiple FAN21SV04s can be synchronized to a single master or system clock
- Independently programmable phase adjustment for one or multiple slaves
- Free-running capability in the absence of system clock or, if the master is disabled/faulted, the slaves can continue to regulate at a lower frequency

The FAN21SV04 master outputs an 85ns-wide clock (CLK) signal, delayed 180° from its leading PWM edge. This feature allows out-of-phase operation for the slaves, thereby reducing the input capacitance requirements when more than one converter is operating on the same input supply. The leading SW-node edge is delayed ~40ns from the rising PWM signal.

On a slave, synchronization is rising-edge triggered. The CLK input pin has a 1.8V threshold and a 200µA current source pull-up.

In Master Mode, the clock signals go out after power-good signal asserts HIGH. Likewise, in Slave Mode, synchronization to an external clock signal occurs after the power-good signal goes HIGH. Until then, the converter operates in free-run mode.




Figure 35. Synchronization Timing Diagram




Figure 36. Slave-CLK-Input Block Diagram

One or more slaves can be connected directly to a master or system clock to achieve a 180° phase shift.




Figure 37. Slaves with 180° Phase Shift

Since the synchronizing circuit utilizes a narrow reset pulse, the actual phase delay is slightly more than 180°.

The FAN21SV04 is not intended for use in single-output, multi-phase regulator applications.

## PCB Layout

Good PCB layout and careful attention to temperature rise is essential for reliable operation of the regulator. Four-layer PCB with two-ounce copper on the top and bottom side and thermal vias connecting the layers is recommended. Keep power traces wide and short to minimize losses and ringing. Do not connect AGND to PGND below the IC. Connect AGND pin to PGND at the output OR to the PGND plane.




Figure 38. Recommended PCB Layout

## Physical Dimensions




Figure 39. 5x6mm Molded Leadless Package (MLP)

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings:  
<http://www.fairchildsemi.com/packaging/>.



## TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

AccuPower™  
Auto-SPM™  
Build it Now™  
CorePLUS™  
CorePOWER™  
CROSSVOLT™  
CTL™  
Current Transfer Logic™  
EcoSPARK®  
EfficientMax™  
EZSWITCH™  
EZ™  
F®  
Fairchild®  
Fairchild Semiconductor®  
FACT Quiet Series™  
FACT®  
FAST®  
FastvCore™  
FETBench™  
FlashWriter®

FPS™  
F-PFST™  
FRFET®  
Global Power Resource™  
Green FPS™  
Green FPS™ e-Series™  
Gmax™  
GTO™  
IntelliMAX™  
ISOPLANAR™  
MegaBuck™  
MICROCOUPLER™  
MicroFET™  
MicroPak™  
MillerDrive™  
MotionMax™  
Motion-SPM™  
OPTOLOGIC®  
OPTOPLANAR®  
PDP SPM™  
Power-SPM™

PowerTrench®  
PowerXS™  
Programmable Active Droop™  
QFET®  
QS™  
Quiet Series™  
RapidConfigure™  
TM  
Saving our world, 1mW/W/kW at a time™  
SignalVise™  
SmartMax™  
SMART START™  
SPM®  
STEALTH™  
SuperFET™  
SuperSOT™.3  
SuperSOT™.6  
SuperSOT™.8  
SupreMOS™  
SyncFET™  
Sync-Lock™  
SYSTEM GENERAL

The Power Franchise®  
the power franchise  
TinyBoost™  
TinyBuck™  
TinyCalc™  
TinyLogic®  
TINYOPTO™  
TinyPower™  
TinyPWM™  
TinyWire™  
TriFault Detect™  
TRUECURRENT™  
µSerDes™  
µSerDes®  
UHC®  
Ultra FRFET™  
UniFET™  
VCX™  
VisualMax™  
XS™

\* Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, [www.fairchildsemi.com](http://www.fairchildsemi.com), under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status        | Definition                                                                                                                                                                                          |
|--------------------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Advance Information      | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.                                                                       |
| Preliminary              | First Production      | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production       | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.                                               |
| Obsolete                 | Not In Production     | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.                                                    |

Rev. I42