



- NOTES:
- 1. MATERIALS AND FINISHES;  
BODY & HEX NUT - BRASS, NICKEL PLATING  
CENTER PIN - BeCu, GOLD PLATING  
BUSHING & FERRULE - BRASS, SLIVER PLATING
  - 2. ELECTRICAL:  
A. IMPENDANCE: 50 OHM  
B. FREQUENCY RANGE: DC 0-4 GHz
  - 3. SHOW CABLE ENTRY DIMENSIONS.
  - 4. FERRULE HEX CRIMP SIZE .128"(3.25mm).
  - 5. CENTER CONTACT SOLDER TO CABLE.
  - 6. FOR ASSEMBLY INSTRUCTION SEE AMPHENOL SPEC. 349-50666.



THIRD ANGLE PROJ.		REVISIONS			
REV	DESCRIPTION	DATE	ECO	APPR	
A	RELEASE TO MFG.	24-Jul-00	43450		
E	SYNC ARFA AND DANBURY DRAWINGS	12-Jul-11	48628	D.HU	



RECOMMENDED  
CABLE STRIPPING DIMENSIONS



SCALE 2.000



**CUSTOMER OUTLINE DRAWING**  
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm    0.5 - 6mm    6 - 30mm    30 - 120mm    ANGLES ± 0.05mm    ±0.1mm    ±0.2mm    ± 0.3mm    ±1°	MATERIAL SEE NOTE	DRAWN I.XU	DATE 30-Jun-11	TITLE BNC BULKHEAD CRIMP JACK		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com
		ENGINEER RICHER	DATE 11-Dec-06			
	REFERENCE EAR 967150-1 & 967150-2 GEN# ASSYF11-BNC AGILENT# 1250-2169	APPROVED D.HU	DATE 12-Jul-11	SCALE: 5.0:1.0	SHEET 2 OF 2	
	FINISH	CAD FILE I: \BNC\31-6010	DWG SIZE B	REV E		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.						DRAWING NO. B6411G1-001-N/ST70G-50
						ITEM NO. 016411AADAIME5F
						PART NO.31-6010