




FEATURES

Dimensions are in inch [metric] units.

- TO-5, 5 pin header
- Windowless package


ELECTRO-OPTICAL CHARACTERISTICS AT 25°C (PER ELEMENT)

PARAMETERS	TEST CONDITIONS	MIN	TYP	MAX	UNITS
Active Area	Per Quadrant		1.25		mm ²
Responsivity, $\mathcal{R}$	@ 254nm		0.02		A/W
Dark Current, I_{dr}	$V_R = \pm 18V$		1	100	nA
Reverse Breakdown Voltage, V_R	$I_R = 1\mu A$	20			Volts
Capacitance, C	$V_R = 0V$			500	pF
Response Time	$V_R = 0V$		1		usec
Shunt Resistance	$V_f = \pm 10mV$	100			MOhms

THERMAL PARAMETERS

STORAGE AND OPERATING TEMPERATURE RANGE	
Ambient	-10° TO 40°C
Nitrogen or Vacuum	-20°C TO 80°C
Maximum Junction Temperature	70°C
Lead soldering temperature ¹	260°C

¹0.080" from case for 10 seconds.

**OPTO DIODE CORP.**

750 Mitchell Road, Newbury Park, California 91320
Phone: (805) 499-0335, Fax: (805) 499-8108
Email: sales@optodiode.com, Website: www.optodiode.com