

Super323™ SOT323 PNP SILICON POWER  
(SWITCHING) TRANSISTOR

ZUMT720


ISSUE 1 - SEPTEMBER 1998

FEATURES

- \* **500mW POWER DISSIPATION**
- \* 1A Peak Pulse Current
- \* Excellent  $H_{FE}$  Characteristics Up To 1A (pulsed)
- \* Low Saturation Voltage
- \* Low Equivalent On Resistance;  $R_{CE(sat)}$

APPLICATIONS

- \* Boost functions in DC-DC converters
- \* Motor driver functions



| DEVICE TYPE | COMPLEMENT | PARTMARKING | $R_{CE(sat)}$  |
|-------------|------------|-------------|----------------|
| ZUMT720     | ZUMT619    | T73         | 240mΩ at 750mA |

ABSOLUTE MAXIMUM RATINGS.

| PARAMETER                                                      | SYMBOL         | VALUE                  | UNIT |
|----------------------------------------------------------------|----------------|------------------------|------|
| Collector-Base Voltage                                         | $V_{CBO}$      | -40                    | V    |
| Collector-Emitter Voltage                                      | $V_{CEO}$      | -40                    | V    |
| Emitter-Base Voltage                                           | $V_{EBO}$      | -5                     | V    |
| Peak Pulse Current**                                           | $I_{CM}$       | -1                     | A    |
| <b>Continuous Collector Current</b>                            | $I_C$          | <b>-0.75</b>           | A    |
| Base Current                                                   | $I_B$          | -200                   | mA   |
| <b>Power Dissipation at <math>T_{amb}=25^{\circ}C^*</math></b> | $P_{tot}$      | <b>385 †<br/>500 ‡</b> | mW   |
| Operating and Storage Temperature Range                        | $T_J; T_{stg}$ | -55 to +150            | °C   |

† Recommended  $P_{tot}$  calculated using FR4 measuring 10 x 8 x 0.6mm (still air).

‡ Maximum power dissipation is calculated assuming that the device is mounted on FR4 size 25x25x0.6mm and using comparable measurement methods adopted by other suppliers.

# ZUMT720

## ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}\text{C}$ unless otherwise stated).

| PARAMETER                             | SYMBOL        | MIN.                         | TYP.                          | MAX.                        | UNIT                 | CONDITIONS.                                                                                                                                                                                                                            |
|---------------------------------------|---------------|------------------------------|-------------------------------|-----------------------------|----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Collector-Base Breakdown Voltage      | $V_{(BR)CBO}$ | -40                          |                               |                             | V                    | $I_C = -100\mu\text{A}$                                                                                                                                                                                                                |
| Collector-Emitter Breakdown Voltage   | $V_{(BR)CEO}$ | -40                          |                               |                             | V                    | $I_C = -10\text{mA}^*$                                                                                                                                                                                                                 |
| Emitter-Base Breakdown Voltage        | $V_{(BR)EBO}$ | -5                           |                               |                             | V                    | $I_E = -100\mu\text{A}$                                                                                                                                                                                                                |
| Collector Cut-Off Current             | $I_{CBO}$     |                              |                               | -10                         | nA                   | $V_{CB} = -35\text{V}$                                                                                                                                                                                                                 |
| Emitter Cut-Off Current               | $I_{EBO}$     |                              |                               | -10                         | nA                   | $V_{EB} = -4\text{V}$                                                                                                                                                                                                                  |
| Collector Emitter Cut-Off Current     | $I_{CES}$     |                              |                               | -10                         | nA                   | $V_{CES} = -35\text{V}$                                                                                                                                                                                                                |
| Collector-Emitter Saturation Voltage  | $V_{CE(sat)}$ |                              | -50<br>-90<br>-140<br>-180    | -65<br>-120<br>-200<br>-250 | mV<br>mV<br>mV<br>mV | $I_C = -0.1\text{A}, I_B = -10\text{mA}^*$<br>$I_C = -0.25\text{A}, I_B = -20\text{mA}^*$<br>$I_C = -0.5\text{A}, I_B = -50\text{mA}^*$<br>$I_C = -0.75\text{A}, I_B = -100\text{mA}^*$                                                |
| Base-Emitter Saturation Voltage       | $V_{BE(sat)}$ |                              | -1000                         | -1100                       | mV                   | $I_C = -0.75\text{A}, I_B = -100\text{mA}^*$                                                                                                                                                                                           |
| Base-Emitter Turn-On Voltage          | $V_{BE(on)}$  |                              | -890                          | -1100                       | mV                   | $I_C = -0.75\text{A}, V_{CE} = -2\text{V}^*$                                                                                                                                                                                           |
| Static Forward Current Transfer Ratio | $h_{FE}$      | 300<br>300<br>90<br>40<br>20 | 510<br>450<br>190<br>60<br>30 |                             |                      | $I_C = -10\text{mA}, V_{CE} = -2\text{V}^*$<br>$I_C = -0.1\text{A}, V_{CE} = -2\text{V}^*$<br>$I_C = -0.5\text{A}, V_{CE} = -2\text{V}^*$<br>$I_C = -0.75\text{A}, V_{CE} = -2\text{V}^*$<br>$I_C = -1\text{A}, V_{CE} = -2\text{V}^*$ |
| Transition Frequency                  | $f_T$         |                              | 220                           |                             | MHz                  | $I_C = -50\text{mA}, V_{CE} = -10\text{V}$<br>$f = 100\text{MHz}$                                                                                                                                                                      |
| Output Capacitance                    | $C_{obo}$     |                              | 8                             |                             | pF                   | $V_{CB} = -10\text{V}, f = 1\text{MHz}$                                                                                                                                                                                                |
| Turn-On Time                          | $t_{(on)}$    |                              | 75                            |                             | ns                   | $V_{CC} = -10\text{V}, I_C = -0.75\text{A}$<br>$I_{B1} = I_{B2} = -100\text{mA}$                                                                                                                                                       |
| Turn-Off Time                         | $t_{(off)}$   |                              | 315                           |                             | ns                   |                                                                                                                                                                                                                                        |

\*Measured under pulsed conditions. Pulse width=300 $\mu\text{s}$ . Duty cycle  $\leq 2\%$

TYPICAL CHARACTERISTICS

