


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 693679



FLEXO® PET

The **FLEXO PET** grade is used in electronics, marine and industrial wire harnessing applications where cost efficiency and durability are critical.

PET is the perfect solution for an infinite variety of applications. **FLEXO PET**'s unique braided construction and wide expandability allows quick and easy installation over large connectors and long runs.

FLEXO PET can be found in applications ranging from small office/home office (SOHO) to high tech wire and cable harnesses. Common applications include high visibility protection for wires, cables, hoses, springs and chains.

The wide range of available colors and sizes allows easy and systematic color coding in complex wiring and cabling schemes.

FLEXO PET is braided from 10 mil PolyEthylene Terephthalate (PET) monofilament yarns. The material has a wide operating temperature range, is resistant to chemical degradation, UV radiation, and abrasion.

PET cuts easily and cleanly with a hot knife and once installed, will beautify and protect any wire, hose or cable application.

Since 1963, **TECHFLEX** has been engineering and manufacturing a wide range of expandable braided sleeving products for everything from biomedical and avionic research and development to wire, hose and cable beautification and protection solutions for hot rod enthusiasts. Our experience with this broad market, as well our wide selection of general purpose and high-tech specialty products, has made **TECHFLEX** the first name in braided expandable sleeving solutions.



Variations in systems and monitors may result in inaccurate color rendition. If color is critical, please request a sample

- **UL Recognized Component**
- **Conforms to FMVSS 302**
- **High Tensile Strength**
- **Cut & Abrasion Resistant**
- **Chemically Inert**
- **Halogen Free**
- **19 Standard Colors**
- **UV Resistant**
- **Maintains Properties Across Wide Temperature Range**
- **Cost Effective**
- **Easy to Install**



TECHFLEX Inc.
Expandable Braided Sleeving


29 Brookfield Drive
Sparta, New Jersey 07871
800 323-5140 • Fax: 973 300-9409
www.techflex.com • E-mail: techflex@techflex.com

300 East 16th Street Suite 306
Greeley, CO 80631
970 352-2355 • Fax: 970 352-3828

Material Type

TECHFLEXExpandable Sleeving

Grade

PET

Size	Min	Max	A * Length	B (OD)	C (ID)	Weight /1000'	Ends	Carriers
1/8"	3/32"	1/4"	1000'	.175"	.125"	1.6 lbs.	1	32
1/4	1/8	7/16	1000	.30	.25	2.4	1	48
3/8	3/16	5/8	500	.425	.375	5.7	3	36
1/2	1/4	3/4	500	.55	.50	7.7	3	48
3/4	1/2	1-1/4	250	.80	.75	12	3	72
1-1/4	3/4	1-3/4	250	1.30	1.25	16	3	96
1-1/2	1	2-1/2	200	1.55	1.50	19.6	4	96
1-3/4	1-1/4	2-3/4	200	1.80	1.75	27	4	120
2	1-1/2	3-1/2	200	2.05	2.0	33	4	120
2-1/2	1-3/4	4-1/2	200	2.55	2.5	38	6	120
3	2-1/2	4-3/4	100	3.05	3.0	40	5	144

Bulk Spools Available: Lengths vary according to size. Custom Cut lengths available**Colors Available:** Black, Clear, Red, Blue, Yellow, Green, Orange, Gray, Neon Red, Purple
Neon Blue, Neon Green, Neon Yellow, Neon Pink, Beige, White, Carbon, Nitrox, Patriot

* Lengths may not be continuous

Material **PET**

Polyethylene Terephthalate

Monofilament Thickness

.010"☐ Heat Treated☐ Rounded

File# LR 66-145



File# E 107 055

**TECHFLEX**Inc.29 Brookfield Drive • P.O. Box 119 • Sparta, NJ 07871
1.800.323.5140 • 973.300.9242 • 973.300.9409 fax
www.techflex.com

PolyEthylene Terephthalate (PET)

Drawing Number

TF001PET-WD

Approved

Date

MATERIAL SPECIFICATIONS - FLEXO PET

CHEMICAL RESISTANCES		Testing Method
1 - No Effect 2 - Little Effect 3 - Moderate Effect 4 - Greater Effect 5 - Severe Effect		
Aromatic Solvents	2	N/A
Aliphatic Solvents	1	N/A
Chlorinated Solvents	3	N/A
Weak Bases	1	N/A
Salts	1	N/A
Strong Bases	2	N/A
Salt Water	1	O-S-1926
Hydraulic Fluid	1	MIL-H-5606
Lube Oil	1	MIL-L-7808
De-Ice Fluid	1	MIL-A-8243
Strong Acids	3	N/A
Strong Oxidants	2	N/A
Esters Keytones	1	N/A
UV Light	1	N/A
Petroleum	1	N/A
Fungus	1	ASTM G-21*

* MIL-1-744, MIL-STD 810/508
MIL-E-5272, MIL-1-1631

STRENGTH & ABRASION	
Tensile Strength	85000
Abrasion Resistance	High
Tenacity gms/denier	4.5
Typical Elongation	Break 15
	3g/denier 5
Specific Gravity	1.38

FLAMMABILITY	
Moisture Absorbtion	0.08
Smoke D-Max	56
Toxicity Index	4.2
Flammability Rating	

OUTGASSING	
Outgassing	Moderate
Oxygen Index	21
Specific Gravity g/cc	1.38
Halogen Free	Yes

TEMPERATURES		
Continuous Operating	C	F
Maximum	125	257
Minimum	-75	-103
Melt	230	446