

# Technical Data



Performance you can trust

## Wire Rope Spray

**High performance, de-watering wire rope lubricant in aerosol form.**

**ROCOL WIRE ROPE SPRAY penetrates rapidly to the core of the wire rope even when applied in wet conditions. It is used successfully on hoists, drag lines, cranes and ships in areas where salt water, effluent or hostile weather conditions prevail.**

### Features

- Temperature range –30°C to 100°C
- De-watering - can be applied to wet ropes
- Withstands extreme wet /corrosive conditions
- Excellent internal & external wear & corrosion protection
- High performance - ensures extended relubrication intervals
- Thin film resists dust and dirt build up
- Wire ropes are cleaner to handle and inspect

### Directions for Use

- Shake can well before use
- Hold upright and spray from a convenient distance
- Apply a complete film over the rope surface
- For best results apply to clean, dry ropes

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67  
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

**ROCOL** A division of **ITW** Ltd



BS EN ISO 9001  
Certificate No. FM 12448



BS EN ISO 14001  
Certificate No. EMS 67596



OHSAS 18001  
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers.  
There are many factors outside our control or knowledge which affect the use and performance  
of our products, for which reason it is given without responsibility.

# Technical Data



Performance you can trust

## Wire Rope Spray

<b>Appearance</b>	Grey/green fluid
<b>Base type</b>	Severely refined mineral oil
<b>Thickener</b>	Organically modified clay
<b>Solids</b>	Blend of molybdenum disulphide & high load white solids
<b>Solvent</b>	Hydrocarbon
<b>Propellant</b>	LPG (Hydrocarbon)
<b>Temperature range</b>	-30°C to 100°C
<b>Base fluid viscosity at 40°C</b>	465cSt
<b>Approximate coverage</b>	
<b>25mm dia (1") wire rope</b>	Approx 20 - 30m per aerosol
<b>Storage</b>	Storage temperature should be kept below 50°C. Storage area should be: out of direct sunlight.
<b>Pack size – part code</b>	400ml aerosol – p/c 20015

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67  
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001  
Certificate No. FM 12448



BS EN ISO 14001  
Certificate No. EMS 67596



OHSAS 18001  
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers.  
There are many factors outside our control or knowledge which affect the use and performance  
of our products, for which reason it is given without responsibility.