



Wiha TorqueControl Index

	Description	Page
	TorqueControl Fix Handle	36
	TorqueVario Handle	36
	TorqueVario Handle (Newton Meter Scale)	36
	TorqueControl Sets	38-39
	Standard Blades Slotted, Phillips, Torx®, TorxPlus®, Hex	37
	TorqueControl Adapters	40
	Insulated TorqueVario	40
	Insulated Blades	40
	ESD Safe TorqueVario Handle	41
	ESD Safe Blades	41
	ESD Safe Set TorqueVario	41
	T-handle Torque	42
	T-handle Torque Blades	42

TorqueVario-S ESD was developed for use in anti-static environments and TorqueVario-S provides safety when working with electrical components. All Wiha TorqueVario-S models have an integrated window scale that displays the torque value - a completely new design, which eliminates false readings. The torque value is continuously adjustable by using the provided adjustment tool (TorqueSetter) this prevents the setting from being altered unintentionally.

“easy” Torque

Economically
priced

Pre-set, fixed torque value
+/- 10%, easy to handle,
robust design



[Uses 285 interchangeable
blades on page 37](#)

Wiha Easy Torque Handles



291 Easy Torque Screwdriver Handle

Easy Torque value pre-set. Release accuracy +/- 10%. Internal mechanism slips when torque value has been attained. Light weight, comfortable handle for good power transfer.

Item No.	Pre-Sets Inch/lbs.	Nm	 mm	 Inch	 lbs.	pkg.
291 02	4.4	0.5	103	4.1	.19	1
291 04	5.3	0.6	103	4.1	.19	1
291 06	8.0	0.9	103	4.1	.19	1
291 08	9.7	1.1	103	4.1	.19	1
291 10	10.6	1.2	103	4.1	.19	1
291 12	12.4	1.4	103	4.1	.19	1
291 14	17.7	2.0	103	4.1	.19	1
291 16	22.1	2.5	103	4.1	.19	1
291 18	26.6	3.0	103	4.1	.19	1

* No Calibration Certificates

