







SECTION A-A

mat'l. code		surface	tolerance	projection	product family
ISDI302		ISDI302	ISDI302	ISDI302	MOD JACK
l	tr	ec	n	dr	date
M	T00202	MM	07/04/00	angle	0°
N	N04-0102	YS	11/23/04	angle	0°
P	N06-0039	DT	3/10/06	0°±2'	0°
R	N08-0097	SI	MM	09/25/08	chr
S	ELX-N-010800	SI	MM	3/14/12	en
T	ELX-N-15908	Henry	09/23/13	chr	
sheet revision		T		appd	JENN TSAO
index	sheet	1	2		

8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG
P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY
awg no	awg no	awg no	awg no	awg no	awg no
90598	90598	90598	90598	90598	90598
size	size	size	size	size	size
A4	A4	A4	A4	A4	A4
type	type	type	type	type	type
Product	Product	Product	Product	Product	Product
Customer	Customer	Customer	Customer	Customer	Customer
Drawing	Drawing	Drawing	Drawing	Drawing	Drawing


PRODUCT NO.	POSITIONS LOADED	CONTACT PLATING	MOUNTING EARS
90598-001-001LF	ALL	5u" Au + high performance lubricant	Y
-002-002LF	2,3,4,5,6,7	5u" Au + high performance lubricant	Y
-003-003LF	ALL	5u" Au + high performance lubricant	Y
-004-004LF	ALL	50u" / 1.27u GXT	Y
-005-005LF	1,2,7,8	5u" Au + high performance lubricant	Y
-006-006LF	ALL	5u" Au + high performance lubricant	N
-007-007LF	ALL	50u" / 1.27u GXT	N
-008-008LF	ALL	5u" Au + high performance lubricant	N
-009-009LF	2-7	5u" Au + high performance lubricant	N
-010-010LF	2-7	5u" Au + high performance lubricant	N
-011-011LF	3,4,5,6	50u" / 1.27u GXT	N
-012-012LF	ALL	15u" / 0.37u GXT	N
-013-013LF	ALL	6u" / 0.15u GXT	Y
-014-014LF	ALL	15u" / 0.37u GXT	Y
-015-015LF	ALL	30u" / 0.76u GXT	Y

PRODUCT NO.	POSITIONS LOADED	CONTACT PLATING	MOUNTING EARS
90598-101-101LF	ALL	5u" Au + high performance lubricant	Y
-102-102LF	2,3,4,5,6,7	5u" Au + high performance lubricant	Y
-103-103LF	ALL	5u" Au + high performance lubricant	Y
-104-104LF	ALL	50u" / 1.27u Au	Y
-105-105LF	1,2,7,8	5u" Au + high performance lubricant	Y
-106-106LF	ALL	5u" Au + high performance lubricant	N


LEAD FREE PRODUCT NO.

NOTES :

- 1 P/NO WITH DASH 0XX -NOMIAL WAVE SOLDERING APPLICATION.
P/NO WITH DASH 1XX -1R REFLOW APPLICATION.
PACKAGING SPEC. BUS-14-164.
- 2 SCRATCH MARKS ACCEPTABLE ON THESE SURFACES.
JACK IS FOR 1,57/062 THICK PCB.
- 3 SHOULD THE JACK NEED TO BE DISMOUNTED FROM THE PCB, PLS REMOVE JACK AS PER RECOMMENDED METHOD HEREIN. (DETAIL A) NIPPING THE LEGS OF THE PEG TOGETHER IS DISALLOWED, OTHERWISE LEG BREAKAGE MAY OCCUR.
THESE DIMENSIONS ARE TAKEN FROM THE TOP OF THE PEG.
- 4 MOUNTING EARS OPTIONAL. REFER TO TABLE
- 5 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- 6 MOUNTING EARS OPTIONAL. REFER TO TABLE
- 7 THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD
- 8 IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- 9 EQUIVALENT THICKNESS Au AND GXT PLATING HAVE SAME FUNCTION AND THEY ARE ALTERNATIVE BY THE CUSTOEMR .



DIRECTION OF DISMOUNT



JACK DISMOUNT METHOD

DETAIL A
NOTE 5

mat'l. code	surface	tolerance	projection	product family
ISD1302	ISD1001	ISD406	ISD1001	MOD JACK
l'trecln n'dr date	tolerances unless otherwise specified			
M T00202 MW 07/04/00	angle 0°	0.X±0.3		
N N04-0102 YS 11/23/04	0°±2'	0.XX±0.15		
P N06-0039 DT 3/10/06		0.XXX±0.05		
R N08-0097 SI MW 09/25/08	CL FENG 01/08/97			
S ELX-N-010801 SI MW 3/14/12	engr TONY CHIEN 01/08/97			
T ELX-N-15908 Henry 09/23/13	chr TONY CHIEN 01/08/97			
sheet revision	appd JENN TSAO 01/08/97			
index sheet				

8 POS VERT. SNAP PEG	8 POS VERT. SNAP PEG
P.C.B. III MOD JACK ASSY	P.C.B. III MOD JACK ASSY
awg no	sheet 2 of 2
90598	A4
type	Product Customer Drawing