




DIMENSIONS mm (inches)



PART NUMBER		8609		71		7		5	
row a	PIN OUT	1	32	2	64	3	96	4	64
rows a-b		1	32	2	64	3	96	4	64
rows a-b-c		1	32	2	64	3	96	4	64
rows a-c		1	32	2	64	3	96	4	64
NUMBER OF CONTACTS		13		4		5		6	
TERMINATION		L = 2.75 ± 0.15 (0.108)		A = $\phi 0.6 \pm 0.08$		B = $\phi 0.8 \pm 0.3$		13	
PERFORMANCE CLASS		DIN 41612 class 3		DIN 41612 class 2		DIN 41612 class 1		4	
TERMINATION TYPE		TIN LEAD		LEAD FREE		- 251E1		- ANLF	

PCB DRILLING



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C-8609-0000A

European Views

www.fciconnect.com		surface ISO 1302		tolerance std ISO 406 ISO 1101		projection A3		mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED		ANGULAR		LINEAR		size		Scale	
Dr ROUILLARD		2000/11/20		0.X		±0.1		1.5	
Eng TARON		2000/11/20		0.XX		±0.1			
Chr LEGARE		2000/11/20		0.XXX		±0.1			
Appr LEGARE		2000/11/20		Product family		DIN 8609		Spec ref -	
FCI		RIGHT ANGLE MALE - STYLE C		title		C-8609-0850		Rev. D	
catalog no		SEE TABLE		customer		sheet 1 of 1			

SPECIFICATION 251 = specific marking : only date code
 or SPECIFICATION AN=