


# IRF9410PbF

HEXFET® Power MOSFET

- Generation V Technology
- Ultra Low On-Resistance
- N-Channel MOSFET
- Surface Mount
- Very Low Gate Charge and Switching Losses
- Fully Avalanche Rated
- Lead-Free



$$V_{DS} = 30V$$


$$R_{DS(on)} = 0.030\Omega$$

## Description

Fifth Generation HEXFETs from International Rectifier utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the fast switching speed and ruggedized device design that HEXFET Power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.

The SO-8 has been modified through a customized leadframe for enhanced thermal characteristics and multiple-die capability making it ideal in a variety of power applications. With these improvements, multiple devices can be used in an application with dramatically reduced board space. The package is designed for vapor phase, infra red, or wave soldering techniques.

Recommended upgrade: IRF7403 or IRF7413  
Lower profile/smaller equivalent: IRF7603



## Absolute Maximum Ratings ( $T_A = 25^\circ\text{C}$ Unless Otherwise Noted)

|                                              | Symbol         | Maximum                         | Units            |
|----------------------------------------------|----------------|---------------------------------|------------------|
| Drain-Source Voltage                         | $V_{DS}$       | 30                              | V                |
| Gate-Source Voltage                          | $V_{GS}$       | $\pm 20$                        |                  |
| Continuous Drain Current ⑤                   | $I_D$          | $T_A = 25^\circ\text{C}$<br>7.0 | A                |
|                                              |                | $T_A = 70^\circ\text{C}$<br>5.8 |                  |
| Pulsed Drain Current                         | $I_{DM}$       | 37                              |                  |
| Continuous Source Current (Diode Conduction) | $I_S$          | 2.8                             |                  |
| Maximum Power Dissipation ⑤                  | $P_D$          | $T_A = 25^\circ\text{C}$<br>2.5 | W                |
|                                              |                | $T_A = 70^\circ\text{C}$<br>1.6 |                  |
| Single Pulse Avalanche Energy ②              | $E_{AS}$       | 70                              | mJ               |
| Avalanche Current                            | $I_{AR}$       | 4.2                             | A                |
| Repetitive Avalanche Energy                  | $E_{AR}$       | 0.25                            | mJ               |
| Peak Diode Recovery dv/dt ③                  | dv/dt          | 5.0                             | V/ ns            |
| Junction and Storage Temperature Range       | $T_J, T_{STG}$ | -55 to + 150                    | $^\circ\text{C}$ |

## Thermal Resistance Ratings

| Parameter                     | Symbol          | Limit | Units              |
|-------------------------------|-----------------|-------|--------------------|
| Maximum Junction-to-Ambient ⑤ | $R_{\theta JA}$ | 50    | $^\circ\text{C/W}$ |


# IRF9410PbF

International  
IR Rectifier

## Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)


|                                 | Parameter                            | Min. | Typ.  | Max.  | Units    | Conditions                                           |
|---------------------------------|--------------------------------------|------|-------|-------|----------|------------------------------------------------------|
| $V_{(BR)DSS}$                   | Drain-to-Source Breakdown Voltage    | 30   | —     | —     | V        | $V_{GS} = 0V, I_D = 250\mu A$                        |
| $\Delta V_{(BR)DSS}/\Delta T_J$ | Breakdown Voltage Temp. Coefficient  | —    | 0.024 | —     | V/°C     | Reference to $25^\circ\text{C}$ , $I_D = 1\text{mA}$ |
| $R_{DS(on)}$                    | Static Drain-to-Source On-Resistance | —    | 0.024 | 0.030 | $\Omega$ | $V_{GS} = 10V, I_D = 7.0A$ ④                         |
|                                 |                                      | —    | 0.032 | 0.040 |          | $V_{GS} = 5.0V, I_D = 4.0A$ ④                        |
|                                 |                                      | —    | 0.037 | 0.050 |          | $V_{GS} = 4.5V, I_D = 3.5A$ ④                        |
| $V_{GS(th)}$                    | Gate Threshold Voltage               | 1.0  | —     | —     | V        | $V_{DS} = V_{GS}, I_D = 250\mu A$                    |
| $g_{fs}$                        | Forward Transconductance             | —    | 14    | —     | S        | $V_{DS} = 15V, I_D = 7.0A$                           |
| $I_{DSS}$                       | Drain-to-Source Leakage Current      | —    | —     | 2.0   | $\mu A$  | $V_{DS} = 24V, V_{GS} = 0V$                          |
|                                 |                                      | —    | —     | 25    |          | $V_{DS} = 24V, V_{GS} = 0V, T_J = 55^\circ\text{C}$  |
| $I_{GSS}$                       | Gate-to-Source Forward Leakage       | —    | —     | 100   | nA       | $V_{GS} = 20V$                                       |
|                                 | Gate-to-Source Reverse Leakage       | —    | —     | -100  |          | $V_{GS} = -20V$                                      |
| $Q_g$                           | Total Gate Charge                    | —    | 18    | 27    | nC       | $I_D = 2.0A$                                         |
| $Q_{gs}$                        | Gate-to-Source Charge                | —    | 2.4   | 3.6   |          | $V_{DS} = 15V$                                       |
| $Q_{gd}$                        | Gate-to-Drain ("Miller") Charge      | —    | 4.9   | 7.4   |          | $V_{GS} = 10V$ , See Fig. 10 ④                       |
| $t_{d(on)}$                     | Turn-On Delay Time                   | —    | 7.3   | 15    | ns       | $V_{DD} = 25V$                                       |
| $t_r$                           | Rise Time                            | —    | 8.3   | 17    |          | $I_D = 1.0A$                                         |
| $t_{d(off)}$                    | Turn-Off Delay Time                  | —    | 23    | 46    |          | $R_G = 6.0\Omega, V_{GS} = 10V$                      |
| $t_f$                           | Fall Time                            | —    | 17    | 34    |          | $R_D = 25\Omega$ ④                                   |
| $C_{iss}$                       | Input Capacitance                    | —    | 550   | —     | pF       | $V_{GS} = 0V$                                        |
| $C_{oss}$                       | Output Capacitance                   | —    | 260   | —     |          | $V_{DS} = 25V$                                       |
| $C_{rss}$                       | Reverse Transfer Capacitance         | —    | 100   | —     |          | $f = 1.0\text{MHz}$ , See Fig. 9                     |

## Source-Drain Ratings and Characteristics


|          | Parameter                              | Min. | Typ. | Max. | Units | Conditions                                                                                                                                           |
|----------|----------------------------------------|------|------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| $I_S$    | Continuous Source Current (Body Diode) | —    | —    | 2.8  | A     | MOSFET symbol showing the integral reverse p-n junction diode.  |
| $I_{SM}$ | Pulsed Source Current (Body Diode) ①   | —    | —    | 37   |       |                                                                                                                                                      |
| $V_{SD}$ | Diode Forward Voltage                  | —    | 0.78 | 1.0  | V     | $T_J = 25^\circ\text{C}, I_S = 2.0A, V_{GS} = 0V$ ③                                                                                                  |
| $t_{rr}$ | Reverse Recovery Time                  | —    | 40   | 80   | ns    | $T_J = 25^\circ\text{C}, I_F = 2.0A$                                                                                                                 |
| $Q_{rr}$ | Reverse Recovery Charge                | —    | 63   | 130  | nC    | $di/dt = 100A/\mu s$ ③                                                                                                                               |

### Notes:


- ① Repetitive rating; pulse width limited by max. junction temperature. ( See fig. 11 )
- ② Starting  $T_J = 25^\circ\text{C}$ ,  $L = 6.6\text{mH}$   
 $R_G = 25\Omega, I_{AS} = 4.6A$ .
- ③  $I_{SD} \leq 4.6A, di/dt \leq 120A/\mu s, V_{DD} \leq V_{(BR)DSS}, T_J \leq 150^\circ\text{C}$
- ④ Pulse width  $\leq 300\mu s$ ; duty cycle  $\leq 2\%$ .
- ⑤ Surface mounted on FR-4 board,  $t \leq 10\text{sec}$ .




**Fig 1.** Typical Output Characteristics




**Fig 2.** Typical Output Characteristics




**Fig 3.** Typical Transfer Characteristics




**Fig 4.** Typical Source-Drain Diode Forward Voltage




**Fig 5.** Normalized On-Resistance Vs. Temperature






**Fig 6.** Typical On-Resistance Vs. Drain Current



**Fig 7.** Typical On-Resistance Vs. Gate Voltage



**Fig 8.** Maximum Avalanche Energy Vs. Drain Current




# IRF9410PbF


International  
**IR** Rectifier

## SO-8 Package Outline

Dimensions are shown in millimeters (inches)




| DIM | INCHES     |       | MILLIMETERS |      |
|-----|------------|-------|-------------|------|
|     | MIN        | MAX   | MIN         | MAX  |
| A   | .0532      | .0688 | 1.35        | 1.75 |
| A1  | .0040      | .0098 | 0.10        | 0.25 |
| b   | .013       | .020  | 0.33        | 0.51 |
| c   | .0075      | .0098 | 0.19        | 0.25 |
| D   | .189       | .1968 | 4.80        | 5.00 |
| E   | .1497      | .1574 | 3.80        | 4.00 |
| e   | .050 BASIC |       | 1.27 BASIC  |      |
| e1  | .025 BASIC |       | 0.635 BASIC |      |
| H   | .2284      | .2440 | 5.80        | 6.20 |
| K   | .0099      | .0196 | 0.25        | 0.50 |
| L   | .016       | .050  | 0.40        | 1.27 |
| y   | 0°         | 8°    | 0°          | 8°   |



### NOTES:


1. DIMENSIONING & TOLERANCING PER ASME Y14.5M-1994.
2. CONTROLLING DIMENSION: MILLIMETER
3. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
4. OUTLINE CONFORMS TO JEDEC OUTLINE MS-012AA.
- ⑤ DIMENSION DOES NOT INCLUDE MOLD PROTRUSIONS. MOLD PROTRUSIONS NOT TO EXCEED 0.15 [0.006].
- ⑥ DIMENSION DOES NOT INCLUDE MOLD PROTRUSIONS. MOLD PROTRUSIONS NOT TO EXCEED 0.25 [0.010].
- ⑦ DIMENSION IS THE LENGTH OF LEAD FOR SOLDERING TO A SUBSTRATE.

### FOOTPRINT




## SO-8 Part Marking

EXAMPLE: THIS IS AN IRF7101 (MOSFET)




## SO-8 Tape and Reel

Dimensions are shown in millimeters (inches)



NOTES:

1. CONTROLLING DIMENSION : MILLIMETER.
2. ALL DIMENSIONS ARE SHOWN IN MILLIMETERS(INCHES).
3. OUTLINE CONFORMS TO EIA-481 & EIA-541.



NOTES :

1. CONTROLLING DIMENSION : MILLIMETER.
2. OUTLINE CONFORMS TO EIA-481 & EIA-541.

Data and specifications subject to change without notice.  
This product has been designed and qualified for the Consumer market.  
Qualifications Standards can be found on IR's Web site.

International  
**IR** Rectifier

**IR WORLD HEADQUARTERS:** 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105  
TAC Fax: (310) 252-7903

Visit us at [www.irf.com](http://www.irf.com) for sales contact information.09/04