


## 14 STAGE BINARY COUNTER

- HIGH SPEED :  
 $f_{MAX} = 70 \text{ MHz (TYP.) at } V_{CC} = 6V$
- LOW POWER DISSIPATION:  
 $I_{CC} = 4\mu A(\text{MAX.}) \text{ at } T_A = 25^\circ C$
- HIGH NOISE IMMUNITY:  
 $V_{NIH} = V_{NIL} = 28 \% V_{CC} (\text{MIN.})$
- SYMMETRICAL OUTPUT IMPEDANCE:  
 $|I_{OH}| = I_{OL} = 4mA (\text{MIN})$
- BALANCED PROPAGATION DELAYS:  
 $t_{PLH} \cong t_{PHL}$
- WIDE OPERATING VOLTAGE RANGE:  
 $V_{CC} (\text{OPR}) = 2V \text{ to } 6V$
- PIN AND FUNCTION COMPATIBLE WITH  
 74 SERIES 4020



### ORDER CODES

| PACKAGE | TUBE         | T & R           |
|---------|--------------|-----------------|
| DIP     | M74HC4020B1R |                 |
| SOP     | M74HC4020M1R | M74HC4020RM13TR |
| TSSOP   |              | M74HC4020TTR    |

### DESCRIPTION

The M74HC4020 is an high speed CMOS 14 STAGE BINARY COUNTER fabricated with silicon gate C<sup>2</sup>MOS technology.


A clear input is used to reset the counter to the all low level state. A high level on CLEAR accomplishes the reset function. A negative transition on the CLOCK input increments the counter by one.

For M74HC4020 twelve kind of divided output are provided; 1st and 4th stage to 14th stage.


The maximum division available at last stage is  $1/16384 \times f_{IN}$  at clock.

All inputs are equipped with protection circuits against static discharge and transient excess voltage.

### PIN CONNECTION AND IEC LOGIC SYMBOLS



INPUT AND OUTPUT EQUIVALENT CIRCUIT




PIN DESCRIPTION

| PIN No                                 | SYMBOL        | NAME AND FUNCTION                         |
|----------------------------------------|---------------|-------------------------------------------|
| 9, 7, 6, 5, 3, 2, 4, 13, 12, 14, 15, 1 | Q1, Q4 to Q14 | Parallel Outputs                          |
| 10                                     | CLOCK         | Clock Input (LOW to HIGH, Edge Triggered) |
| 11                                     | CLEAR         | Reset Inputs                              |
| 8                                      | GND           | Ground (0V)                               |
| 16                                     | Vcc           | Positive Supply Voltage                   |

TRUTH TABLE

| CLOCK | CLEAR | OUTPUT STATE          |
|-------|-------|-----------------------|
| X     | H     | ALL OUTPUTS = "L"     |
|       | L     | NO CHANGE             |
|       | L     | ADVANCE TO NEXT STATE |

LOGIC DIAGRAM



This logic diagram has not be used to estimate propagation delays



**ABSOLUTE MAXIMUM RATINGS**

| Symbol                | Parameter                     | Value                  | Unit |
|-----------------------|-------------------------------|------------------------|------|
| $V_{CC}$              | Supply Voltage                | -0.5 to +7             | V    |
| $V_I$                 | DC Input Voltage              | -0.5 to $V_{CC} + 0.5$ | V    |
| $V_O$                 | DC Output Voltage             | -0.5 to $V_{CC} + 0.5$ | V    |
| $I_{IK}$              | DC Input Diode Current        | $\pm 20$               | mA   |
| $I_{OK}$              | DC Output Diode Current       | $\pm 20$               | mA   |
| $I_O$                 | DC Output Current             | $\pm 25$               | mA   |
| $I_{CC}$ or $I_{GND}$ | DC $V_{CC}$ or Ground Current | $\pm 50$               | mA   |
| $P_D$                 | Power Dissipation             | 500(*)                 | mW   |
| $T_{stg}$             | Storage Temperature           | -65 to +150            | °C   |
| $T_L$                 | Lead Temperature (10 sec)     | 300                    | °C   |

Absolute Maximum Ratings are those values beyond which damage to the device may occur. Functional operation under these conditions is not implied

(\*) 500mW at 65 °C; derate to 300mW by 10mW/°C from 65°C to 85°C

**RECOMMENDED OPERATING CONDITIONS**

| Symbol                          | Parameter                |                        | Value                | Unit |
|---------------------------------|--------------------------|------------------------|----------------------|------|
| V <sub>CC</sub>                 | Supply Voltage           |                        | 2 to 6               | V    |
| V <sub>I</sub>                  | Input Voltage            |                        | 0 to V <sub>CC</sub> | V    |
| V <sub>O</sub>                  | Output Voltage           |                        | 0 to V <sub>CC</sub> | V    |
| T <sub>op</sub>                 | Operating Temperature    |                        | -55 to 125           | °C   |
| t <sub>r</sub> , t <sub>f</sub> | Input Rise and Fall Time | V <sub>CC</sub> = 2.0V | 0 to 1000            | ns   |
|                                 |                          | V <sub>CC</sub> = 4.5V | 0 to 500             | ns   |
|                                 |                          | V <sub>CC</sub> = 6.0V | 0 to 400             | ns   |

## DC SPECIFICATIONS

| Symbol          | Parameter                 | Test Condition         |                                         | Value                 |      |       |             |      |              |      | Unit |  |
|-----------------|---------------------------|------------------------|-----------------------------------------|-----------------------|------|-------|-------------|------|--------------|------|------|--|
|                 |                           | V <sub>CC</sub><br>(V) |                                         | T <sub>A</sub> = 25°C |      |       | -40 to 85°C |      | -55 to 125°C |      |      |  |
|                 |                           |                        |                                         | Min.                  | Typ. | Max.  | Min.        | Max. | Min.         | Max. |      |  |
| V <sub>IH</sub> | High Level Input Voltage  | 2.0                    |                                         | 1.5                   |      |       | 1.5         |      | 1.5          |      | V    |  |
|                 |                           | 4.5                    |                                         | 3.15                  |      |       | 3.15        |      | 3.15         |      |      |  |
|                 |                           | 6.0                    |                                         | 4.2                   |      |       | 4.2         |      | 4.2          |      |      |  |
| V <sub>IL</sub> | Low Level Input Voltage   | 2.0                    |                                         |                       |      | 0.5   |             | 0.5  |              | 0.5  | V    |  |
|                 |                           | 4.5                    |                                         |                       |      | 1.35  |             | 1.35 |              | 1.35 |      |  |
|                 |                           | 6.0                    |                                         |                       |      | 1.8   |             | 1.8  |              | 1.8  |      |  |
| V <sub>OH</sub> | High Level Output Voltage | 2.0                    | I <sub>O</sub> =-20 μA                  | 1.9                   | 2.0  |       | 1.9         |      | 1.9          |      | V    |  |
|                 |                           | 4.5                    | I <sub>O</sub> =-20 μA                  | 4.4                   | 4.5  |       | 4.4         |      | 4.4          |      |      |  |
|                 |                           | 6.0                    | I <sub>O</sub> =-20 μA                  | 5.9                   | 6.0  |       | 5.9         |      | 5.9          |      |      |  |
|                 |                           | 4.5                    | I <sub>O</sub> =-4.0 mA                 | 4.18                  | 4.31 |       | 4.13        |      | 4.10         |      |      |  |
|                 |                           | 6.0                    | I <sub>O</sub> =-5.2 mA                 | 5.68                  | 5.8  |       | 5.63        |      | 5.60         |      |      |  |
| V <sub>OL</sub> | Low Level Output Voltage  | 2.0                    | I <sub>O</sub> =20 μA                   |                       | 0.0  | 0.1   |             | 0.1  |              | 0.1  | V    |  |
|                 |                           | 4.5                    | I <sub>O</sub> =20 μA                   |                       | 0.0  | 0.1   |             | 0.1  |              | 0.1  |      |  |
|                 |                           | 6.0                    | I <sub>O</sub> =20 μA                   |                       | 0.0  | 0.1   |             | 0.1  |              | 0.1  |      |  |
|                 |                           | 4.5                    | I <sub>O</sub> =4.0 mA                  |                       | 0.17 | 0.26  |             | 0.33 |              | 0.40 |      |  |
|                 |                           | 6.0                    | I <sub>O</sub> =5.2 mA                  |                       | 0.18 | 0.26  |             | 0.33 |              | 0.40 |      |  |
| I <sub>I</sub>  | Input Leakage Current     | 6.0                    | V <sub>I</sub> = V <sub>CC</sub> or GND |                       |      | ± 0.1 |             | ± 1  |              | ± 1  | μA   |  |
| I <sub>CC</sub> | Quiescent Supply Current  | 6.0                    | V <sub>I</sub> = V <sub>CC</sub> or GND |                       |      | 4     |             | 40   |              | 80   | μA   |  |

**AC ELECTRICAL CHARACTERISTICS** ( $C_L = 50 \text{ pF}$ , Input  $t_r = t_f = 6 \text{ ns}$ )


| Symbol                                 | Parameter                                                      | Test Condition         |  | Value                 |      |      |             |      |              | Unit |      |
|----------------------------------------|----------------------------------------------------------------|------------------------|--|-----------------------|------|------|-------------|------|--------------|------|------|
|                                        |                                                                | V <sub>CC</sub><br>(V) |  | T <sub>A</sub> = 25°C |      |      | -40 to 85°C |      | -55 to 125°C |      |      |
|                                        |                                                                |                        |  | Min.                  | Typ. | Max. | Min.        | Max. | Min.         |      | Max. |
| t <sub>TLH</sub> t <sub>THL</sub>      | Output Transition Time                                         | 2.0                    |  |                       | 30   | 75   |             | 95   |              | 110  | ns   |
|                                        |                                                                | 4.5                    |  |                       | 8    | 15   |             | 19   |              | 22   |      |
|                                        |                                                                | 6.0                    |  |                       | 7    | 13   |             | 16   |              | 19   |      |
| t <sub>PLH</sub> t <sub>PHL</sub>      | Propagation Delay Time<br>(Q <sub>n</sub> - Q <sub>n+1</sub> ) | 2.0                    |  |                       | 20   | 50   |             | 65   |              | 75   | ns   |
|                                        |                                                                | 4.5                    |  |                       | 5    | 10   |             | 13   |              | 15   |      |
|                                        |                                                                | 6.0                    |  |                       | 4    | 9    |             | 11   |              | 13   |      |
| t <sub>PLH</sub> t <sub>PHL</sub>      | Propagation Delay Time<br>(CLOCK Q1)                           | 2.0                    |  |                       | 76   | 145  |             | 180  |              | 220  | ns   |
|                                        |                                                                | 4.5                    |  |                       | 21   | 29   |             | 36   |              | 44   |      |
|                                        |                                                                | 6.0                    |  |                       | 18   | 25   |             | 31   |              | 38   |      |
| t <sub>PHL</sub>                       | Propagation Delay Time<br>(CLEAR - Q <sub>n</sub> )            | 2.0                    |  |                       | 60   | 140  |             | 175  |              | 210  | ns   |
|                                        |                                                                | 4.5                    |  |                       | 18   | 28   |             | 35   |              | 42   |      |
|                                        |                                                                | 6.0                    |  |                       | 15   | 24   |             | 30   |              | 36   |      |
| f <sub>MAX</sub>                       | Maximum Clock Frequency                                        | 2.0                    |  | 6.0                   | 15   |      | 4.8         |      | 4            |      | MHz  |
|                                        |                                                                | 4.5                    |  | 30                    | 65   |      | 24          |      | 20           |      |      |
|                                        |                                                                | 6.0                    |  | 35                    | 70   |      | 28          |      | 24           |      |      |
| t <sub>W(H)</sub><br>t <sub>W(L)</sub> | Minimum Pulse Width (CLOCK)                                    | 2.0                    |  |                       | 40   | 75   |             | 95   |              | 110  | ns   |
|                                        |                                                                | 4.5                    |  |                       | 8    | 15   |             | 19   |              | 22   |      |
|                                        |                                                                | 6.0                    |  |                       | 7    | 13   |             | 16   |              | 19   |      |
| t <sub>W(H)</sub>                      | Minimum Pulse Width (CLEAR)                                    | 2.0                    |  |                       | 32   | 75   |             | 95   |              | 110  | ns   |
|                                        |                                                                | 4.5                    |  |                       | 8    | 15   |             | 19   |              | 22   |      |
|                                        |                                                                | 6.0                    |  |                       | 7    | 13   |             | 16   |              | 19   |      |
| t <sub>REM</sub>                       | Minimum Removal Time                                           | 2.0                    |  |                       |      | 0    |             | 0    |              | 0    | ns   |
|                                        |                                                                | 4.5                    |  |                       |      | 0    |             | 0    |              | 0    |      |
|                                        |                                                                | 6.0                    |  |                       |      | 0    |             | 0    |              | 0    |      |

**CAPACITIVE CHARACTERISTICS**

| Symbol          | Parameter                              | Test Condition         |  | Value                 |      |      |             |      |              | Unit |      |
|-----------------|----------------------------------------|------------------------|--|-----------------------|------|------|-------------|------|--------------|------|------|
|                 |                                        | V <sub>CC</sub><br>(V) |  | T <sub>A</sub> = 25°C |      |      | -40 to 85°C |      | -55 to 125°C |      |      |
|                 |                                        |                        |  | Min.                  | Typ. | Max. | Min.        | Max. | Min.         |      | Max. |
| C <sub>IN</sub> | Input Capacitance                      | 5.0                    |  |                       | 5    | 10   |             | 10   |              | 10   | pF   |
| C <sub>PD</sub> | Power Dissipation Capacitance (note 1) | 5.0                    |  |                       | 34   |      |             |      |              |      | pF   |


1)  $C_{PD}$  is defined as the value of the IC's internal equivalent capacitance which is calculated from the operating current consumption without load. (Refer to Test Circuit). Average operating current can be obtained by the following equation.  $I_{CC(oper)} = C_{PD} \times V_{CC} \times f_{IN} + I_{CC}/2$  (per FLIP/FLOP)



## TEST CIRCUIT



$C_L = 50\text{pF}$  or equivalent (includes jig and probe capacitance)  
 $R_T = Z_{OUT}$  of pulse generator (typically  $50\Omega$ )


**WAVEFORM 1: MINIMUM PULSE WIDTH (CLEAR) AND REMOVAL TIME (CLEAR TO  $\overline{\text{CLOCK}}$ )**  
 ( $f=1\text{MHz}$ ; 50% duty cycle)



**WAVEFORM 2 : PROPAGATION DELAY TIME** ( $f=1\text{MHz}$ ; 50% duty cycle)**WAVEFORM 3 : PROPAGATION DELAY TIME, MINIMUM PULSE WIDTH (CLOCK)** ( $f=1\text{MHz}$ ; 50% duty cycle)

## Plastic DIP-16 (0.25) MECHANICAL DATA


| DIM. | mm.  |       |      | inch  |       |       |
|------|------|-------|------|-------|-------|-------|
|      | MIN. | TYP   | MAX. | MIN.  | TYP.  | MAX.  |
| a1   | 0.51 |       |      | 0.020 |       |       |
| B    | 0.77 |       | 1.65 | 0.030 |       | 0.065 |
| b    |      | 0.5   |      |       | 0.020 |       |
| b1   |      | 0.25  |      |       | 0.010 |       |
| D    |      |       | 20   |       |       | 0.787 |
| E    |      | 8.5   |      |       | 0.335 |       |
| e    |      | 2.54  |      |       | 0.100 |       |
| e3   |      | 17.78 |      |       | 0.700 |       |
| F    |      |       | 7.1  |       |       | 0.280 |
| I    |      |       | 5.1  |       |       | 0.201 |
| L    |      | 3.3   |      |       | 0.130 |       |
| Z    |      |       | 1.27 |       |       | 0.050 |



P001C

## SO-16 MECHANICAL DATA


| DIM. | mm.        |      |      | inch  |       |       |
|------|------------|------|------|-------|-------|-------|
|      | MIN.       | TYP  | MAX. | MIN.  | TYP.  | MAX.  |
| A    |            |      | 1.75 |       |       | 0.068 |
| a1   | 0.1        |      | 0.2  | 0.003 |       | 0.007 |
| a2   |            |      | 1.65 |       |       | 0.064 |
| b    | 0.35       |      | 0.46 | 0.013 |       | 0.018 |
| b1   | 0.19       |      | 0.25 | 0.007 |       | 0.010 |
| C    |            | 0.5  |      |       | 0.019 |       |
| c1   | 45° (typ.) |      |      |       |       |       |
| D    | 9.8        |      | 10   | 0.385 |       | 0.393 |
| E    | 5.8        |      | 6.2  | 0.228 |       | 0.244 |
| e    |            | 1.27 |      |       | 0.050 |       |
| e3   |            | 8.89 |      |       | 0.350 |       |
| F    | 3.8        |      | 4.0  | 0.149 |       | 0.157 |
| G    | 4.6        |      | 5.3  | 0.181 |       | 0.208 |
| L    | 0.5        |      | 1.27 | 0.019 |       | 0.050 |
| M    |            |      | 0.62 |       |       | 0.024 |
| S    | 8° (max.)  |      |      |       |       |       |



PO13H

## TSSOP16 MECHANICAL DATA

| DIM. | mm.  |          |      | inch  |            |        |
|------|------|----------|------|-------|------------|--------|
|      | MIN. | TYP      | MAX. | MIN.  | TYP.       | MAX.   |
| A    |      |          | 1.2  |       |            | 0.047  |
| A1   | 0.05 |          | 0.15 | 0.002 | 0.004      | 0.006  |
| A2   | 0.8  | 1        | 1.05 | 0.031 | 0.039      | 0.041  |
| b    | 0.19 |          | 0.30 | 0.007 |            | 0.012  |
| c    | 0.09 |          | 0.20 | 0.004 |            | 0.0089 |
| D    | 4.9  | 5        | 5.1  | 0.193 | 0.197      | 0.201  |
| E    | 6.2  | 6.4      | 6.6  | 0.244 | 0.252      | 0.260  |
| E1   | 4.3  | 4.4      | 4.48 | 0.169 | 0.173      | 0.176  |
| e    |      | 0.65 BSC |      |       | 0.0256 BSC |        |
| K    | 0°   |          | 8°   | 0°    |            | 8°     |
| L    | 0.45 | 0.60     | 0.75 | 0.018 | 0.024      | 0.030  |



0080338D

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

© The ST logo is a registered trademark of STMicroelectronics

© 2001 STMicroelectronics - Printed in Italy - All Rights Reserved  
STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - China - Finland - France - Germany - Hong Kong - India - Italy - Japan - Malaysia - Malta - Morocco  
Singapore - Spain - Sweden - Switzerland - United Kingdom

© <http://www.st.com>

