



Terminal blocks

to **Type 382** and **Type 190**




- ASP044** page 45
- ASP064** page 45
- Type 113** page 88
- Type 114** page 88
- Type 369** page 87

Accessories

for **Type 382** and **Type 190**
Coding set
 720293 page 204

Note for Type 190

Packaging for automated processing is available on demand. Please do not hesitate to contact us.




Type 382

Header, centerline 3.81 mm / 0.150 inches, horizontal mounting, square contact pins 0.8 mm / 0.031 inches, closed ends, codable

Technical Data

V / A	300 / 8		
	130 V / 2.5 kV / 11 A		
Insulation co-ordination according to EN 60664-1	Clearance and creepage distances min. 3.01 mm		
Insulating material class	CTI 600		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	200	500	500
Rated test voltage	2.5	4	2.5
Protection category according to IEC 529	IP00		
Solder pin dimension	0.8 x 0.8 mm		
Recommended pc board hole dia.	Ø 1.3 mm		
Solder pin length	3.5 mm		
Pole size	2 - 24		
Color	black		

Dimensions in mm 1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 5.2 \text{ mm} / 0.205 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 382

centerline 3.81 mm / 0.150 inches

P/N 313821

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24


Type 190

Header, centerline 3.81 mm / 0.150 inches, horizontal mounting, designed for THR, optional Tape on Reel packaging for automated processing, square contact pins 0.8 mm / 0.031 inches, closed ends, codable

Technical Data

V / A	300 / 8		
	130 V / 2.5 kV / 10 A		
Insulation co-ordination according to EN 60664-1	Clearance and creepage distances min. 3.01 mm		
Insulating material class	CTI 600		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	200	500	500
Rated test voltage	2.5	4	2.5
Protection category according to IEC 529	IP00		
Solder pin dimension	0.8 x 0.8 mm		
Recommended pc board hole dia.	Ø 1.3 mm		
Solder pin length	3.5 mm		
Pole size	2 - 12		
Color	black		

Dimensions in mm 1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 5.2 \text{ mm} / 0.205 \text{ inches}$

Part numbers (P/N)

(information: page 110)

Complete the part number by adding the pole size.

Type 190

centerline 3.81 mm / 0.150 inches

P/N 311901

	02	03	04	05	06	07	08
09	10	11	12				