



Features

- Single-Turn / Cermet / Industrial / Open Frame
- Stable cermet element offers infinite resolution
- Very low profile
- Seven standard pin styles
- Thumb and screwdriver adjustment

- RoHS compliant* version available
- For trimmer applications/processing guidelines, [click here](#)

3352 - 3/8 " Round Trimpot® Trimming Potentiometer

Electrical Characteristics

Standard Resistance Range 10 to 2 megohms
(see standard resistance table)
Resistance Tolerance $\pm 20\%$ std.
(tighter tolerance available)
Absolute Minimum Resistance 2 ohms max.
Contact Resistance Variation 1.0 % or 1 ohm max.
(whichever is greater)
Adjustability
Voltage $\pm 0.05\%$
Resistance $\pm 0.25\%$
Resolution Infinite
Dielectric Strength
Sea Level 500 vac
80,000 Feet 350 vac
Adjustment Angle 205° nom.

Environmental Characteristics

Power Rating (250 volts max.)
85 °C 0.50 watt
125 °C 0 watt
Temperature Range ... -55°C to $+125^\circ\text{C}$
Temperature Coefficient
 ± 100 ppm/°C 2K & up
 ± 150 ppm/°C Below 2K
Humidity MIL-STD-202 Method 103
96 hours
(2 % Δ TR, 10 Megohms IR)
Vibration 30 G (2 % Δ TR; 2 % Δ VR)
Shock 100 G (2 % Δ TR; 2 % Δ VR)
Load Life.. 1,000 hours 0.5 watt @ 85 °C
(3 % Δ TR)
Rotational Life 200 cycles
(10 % Δ TR)


Physical Characteristics

Mechanical Angle 250° nom.
Torque 3.0 oz-in. max.
Stop Strength 8 oz -in. min.
Terminals Solderable pins
Weight 0.01 oz.
Marking Manufacturer's
trademark, resistance value
and model number.
Date code on packaging.
Wiper 50 % (Actual TR) $\pm 10\%$
Standard Packaging 100 pcs. per bag
Adjustment Tool H-90

Aqueous cleaning not recommended.


Product Dimensions

3352




3352E



Top Adjust



3352P



3352T



How To Order


3352 W - 1 - 103 LF

Model _____
Style _____
Standard or Modified
Product Indicator _____
-1 = Standard Product
Resistance Code _____
Terminations _____
LF = 100 % Tin-plated (RoHS compliant)
Blank = 90 % Tin / 10 % Lead-plated
(Standard)


Consult factory for other available options.

3352H


Side Adjust




3352K



3352V



3352W



DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

TOLERANCES: $\pm \frac{0.25}{(.010)}$ EXCEPT WHERE NOTED

Standard Resistance Table

Resistance (Ohms)	Resistance Code
10	100
20	200
50	500
100	101
200	201
500	501
1,000	102
2,000	202
5,000	502
10,000	103
20,000	203
25,000	253
50,000	503
100,000	104
200,000	204
250,000	254
500,000	504
1,000,000	105
2,000,000	205

Popular values listed in boldface. Special resistances available.

REV. 08/10

*RoHS Directive 2002/95/EC Jan 27 2003 including Annex.

"Trimpot" is a registered trademark of Bourns, Inc.

Specifications are subject to change without notice.

Customers should verify actual device performance in their specific applications.