


MATERIALS	
BODY	BRASS NICKEL PLATED
CONTACT	GOLD PLATED
INSULATOR	PTFE
COUPLING NUT	BRASS NICKEL PLATED



SPECIFICATIONS

FREQUENCY RANGE: DC TO 18 GHz
 ATTENUATION: 30 dB
 IMPEDANCE: 50 OHMS
 ACCURACY: ± 1.5 dB
 VSWR:

DC - 4 GHz	1.15:1 MAX
4 GHz - 8 GHz	1.20:1 MAX
8 GHz - 12.4 GHz	1.25:1 MAX
12.4 GHz - 18 GHz	1.35:1 MAX

AVG. POWER HANDLING CAPABILITY: 2 WATTS



PASTERNAK ENTERPRISES, INC.

P.O. BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE7004-30

DES. N ATTENUATOR, MALE TO FEMALE, 30 dB
 FREQUENCY RANGE: DC TO 18 GHz

REV. A **FSCM NO. 53919**

CAD FILE 030408

SCALE N/A

SIZE A 147

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.