






HOLD DOWN TYPE

mat'l. code				surface 58		tolerance		projection		product family											
—				ISO 1302		ISO 406 ISO 101				PCI_EXPRESS											
ltr	ecn no	dr	date	tolerances unless otherwise specified								title									
J	ELX-DG-14311	WL	2013/03/21	angles	linear	.X±.3			PCI_EXPRESS_CARD_EDGE_GEN3												
K	ELX-DG-16269	ST	2013/11/13			.XX±.20			ASSEMBLY(SMT)												
L	ELX-DG-21161-1	ST	2015/05/27			XXX±.10			scale 1												
M	ELX-DG-24164	ZH	2016/06/01	dr	STONE_LI		2015/05/27				dwg no				sheet 1 of 6				size		
N	ELX-DG-25671-1	ZH	2016/12/19	engr	STONE_LI		2015/05/27				10061913				A4						
P	ELX-DG-27937	ZH	2017/09/12	chr	/		/														
				appd	PM_ZHENG		2015/05/27				type								CUSTOMER Drawing		
sheet index		revision		P																	
		sheet																			



I/O PANEL DIRECTION
PRIMARY (COMPONENT) SIDE

I/O PANEL DIRECTION
SECONDARY (SOLDER) SIDE

#	POS	REF.	N	DIM "G"	DIM "F"	"F"
36	6			8.15	6.00	B17
64	20			22.15	20.00	B31
98	37			39.15	37.00	B48
164	70			72.15	70.00	B81

ADD-IN CARD EDGE-FINGER DIMENSIONS

mat'l. code				surface 58		tolerance		projection		product family			
-				ISO 1302		ISO 406		ISO 101		PCI_EXPRESS			
ltr		ecn no		dr		date		tolerances unless otherwise specified		title			
								.X±.2		PCI_EXPRESS_CARD_EDGE_GEN3			
								.XX±.13		ASSEMBLY(SMT)			
								XXX±.05		scale 2			
								scale 2		dwg no		sheet 2 of 6	
								scale 2		10061913		A4	
								scale 2		type		CUSTOMER Drawing	
sheet index		revision		P									
		sheet											




RECOMMENDED PCB LAYOUT, PAD TYPE


DIMENSIONS								
POSITION	A	B $\begin{smallmatrix} +0.15 \\ -0.05 \end{smallmatrix}$	C ± 0.20	D ± 0.23	E ± 0.20	H ± 0.10	J	K ± 0.10
36	6.00	7.65	9.15	25.00	27.00	28.00	6.00	9.15
64	20.00	21.65	23.15	39.00	41.00	42.00	20.00	23.15
98	37.00	38.65	40.15	56.00	58.00	59.00	37.00	40.15
164	70.00	71.65	73.15	89.00	91.00	92.00	70.00	73.15

POSTION OF CAP





POSTION OF DUMMY CARD



POSTION OF CUSTOMIZED CAP(30X12)



mat'l. code				surface 58	tolerance	projection	product family			
-				ISO 1302	ISO 406	ISO 101	PCI_EXPRESS			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
				angles	linear	MM	PCI_EXPRESS_CARD_EDGE_GEN3			
				0°±2°	XXX±.05	scale 2	ASSEMBLY(SMT)			
				dr	STONE_LI	2015/05/27	dwg no		sheet 3 of 6	size
				engr	STONE_LI	2015/05/27	10061913			A4
				chr	/	/	type			
				appd	PM_ZHENG	2015/05/27	CUSTOMER Drawing			
sheet index	revision	P								
	sheet									



TAPE AND REEL
PACKING
RECOMMENDED FOR
36PINS ONLY

DIMENSIONS					
POSITIONS	A	B	C	D REF.	E REF.
36 (10061913-xxxALF)	44.00	40.40	20.20	44.5	50.5
36	56.00	52.60	26.30	56.4	60.4
64	56.00	52.60	26.30	56.4	60.4
98	88.00	79.60	39.80	88.4	92.4

mat'l. code				surface 58		tolerance		projection		product family									
—				ISO 1302		ISO 406 ISO 101				PCI_EXPRESS									
ltr	ecn no	dr	date	tolerances unless otherwise specified						title									
				angles		linear				PCI_EXPRESS_CARD_EDGE_GEN3 ASSEMBLY(SMT)									
				0°±2°				MM											
				dr	STONE_LI	2015/05/27		scale 1		dwg no									
				engr	STONE_LI	2015/05/27				sheet 5 of 6									
				chr	/	/				size									
				appd	PM_ZHENG	2015/05/27				A4									
sheet index		revision sheet		P						type CUSTOMER Drawing									

I For PCI EXPRESS SMT TYPE 36P ONLY.

2. Material :


- 2.1 Reel :
 - 2.1.1 Plastic hub : High Impact Polystyrene
 - 2.1.2 Cover tape : PE
 - 2.1.3 Carrier tape : ABS
- 2.2 Waterproof bag : PE
- 2.3 Desiccative : Silica Gel
- 2.4 Carton : Corrugated paper
- 2.5 Baffle : E.P.E
- 2.6 Angle paperboard : Corrugated paper

3. Dimension :

- 3.1 Reel :
 - 3.1.1 Plastic hub : $\varnothing 330 \times T50.5$ mm
 - 3.1.2 Cover tape : $5690(L) \times 37.4(W)$ mm
 - 3.1.3 Carrier tape : $5640(L) \times 44(W)$ mm
- 3.2 Waterproof bag : $600(H) \times 465(W) \times 0.06(T)$ mm
- 3.3 Desiccative : 25 gram / Package
- 3.4 Carton : $380(L) \times 380(W) \times 300(H)$ mm
- 3.5 Baffle (1): $370(L) \times 370(W) \times 15(H)$ mm
- 3.6 Baffle (2): $355(L) \times 252(W) \times 15(H)$ mm
- 3.7 Angle paperboard : $252(H)$

4. Quantity :

- 4.1 250 Pcs / Reel
- 4.2 1250 Pcs / Carton



mat'l. code				surface 58	tolerance	projection	product family									
—				ISO 1302	ISO 406	ISO 101	PCI_EXPRESS									
ltr	ecn no	dr	date	tolerances unless otherwise specified			title									
				angles			PCI_EXPRESS_CARD_EDGE_GEN3 ASSEMBLY(SMT)									
				linear												
				0°±2°		scale 1										
				dr	STONE_LI	2015/05/27										
				engr	STONE_LI	2015/05/27										
				chr	/	/										
				appd	PM_ZHENG	2015/05/27										
sheet index	revision	P					dwg no									
	sheet						sheet 6 of 6									
							size									
							10061913									
							A4									
							type									
							CUSTOMER Drawing									