















T3-1/4 (9mm) Miniature Based LED Lamps

Miniature Packages		Replaces Incandescent	Part Number	Electrical-Optical Characteristics (Ta = 25°C)			Angle of Illumination	Special Features
				Voltage V typ	Current mA typ	Intensity mcd		
660nm Ultra Red GaAlAs/GaAs  BF321	T3-1/4 (9mm) Miniature Bayonet 	6MB, 44, 47, 755	BF321-0UR-006B	5/6V	20	115	120°	Center Contact Polarity B = Bipolar AC/DC A = AC only Replace BF321 With B321 for Narrow Beam (15°) 1.6K mcd/52 Ft.Cd @ 20mA
		12MB, 756	BF321-0UR-014B	12/14V	20	115		
		24MB,	BF321-0UR-024B	24V	20	115		
		313,757,1819,1829	BF321-0UR-028B	28V	20	115		
		48MB	BF321-0UR-048B	48V	12	65		
		60MB,1835	BF321-0UR-060B	60V	12	65		
		120MB, NE51H	BF321-0UR-120A	120VAC	10	50		
660nm Ultra Red GaAlAs/GaAs  BF304	T3-1/4 (9mm) Miniature Bayonet LED Cluster 	6MB, 44, 47, 755	BF304-0UR-006B	5/6V	80	460	120°	Center Contact Polarity B = Bipolar AC/DC A = AC only Replace BF304 With B304 for Narrow Beam (15°) 6.4K mcd/208 Ft.Cd @ 20mA
		12MB, 756	BF304-0UR-014B	12/14V	40	460		
		24MB,	BF304-0UR-024B	24V	20	460		
		313,757,1819,1829	BF304-0UR-028B	28V	20	460		
		48MB	BF304-0UR-048B	48V	12	260		
		60MB,1835	BF304-0UR-060B	60V	12	260		
		120MB, NE51H	BF304-0UR-120A	120VAC	10	200		
660nm Ultra Red GaAlAs/GaAs  BF3126/ BF3127	T3-1/4 (9mm) Miniature Bayonet LED Cluster 	6MB, 44, 47, 755	BF3126-0UR-006B	5/6V	120	600	120°	Center Contact Polarity B = Bipolar AC/DC A = AC only Replace BF3126/3127 With B3126/3127 for Narrow Beam (65°) 1.3K mcd/210 Ft.Cd @ 20mA
		12MB, 756	BF3126-0UR-014B	12/14V	40	600		
		24MB,	BF3127-0UR-024B	24V	20	700		
		313,757,1819,1829	BF3127-0UR-028B	28V	20	700		
		48MB	BF3127-0UR-048B	48V	12	230		
		60MB,1835	BF3127-0UR-060B	60V	12	230		
		120MB, NE51H	BF3127-0UR-120A	120VAC	10	160		
612nm Super Orange InGaAlP  BF321	T3-1/4 (9mm) Miniature Bayonet 	6MB, 44, 47, 755	BF321-0UO-006B	5/6V	20	130	120°	Center Contact Polarity B = Bipolar AC/DC A = AC only Replace BF321 With B321 for Narrow Beam (15°) 3.5 K mcd @ 20mA
		12MB, 756	BF321-0UO-014B	12/14V	20	130		
		24MB,	BF321-0UO-024B	24V	20	130		
		313,757,1819,1829	BF321-0UO-028B	28V	20	130		
		48MB	BF321-0UO-048B	48V	12	78		
		60MB,1835	BF321-0UO-060B	60V	12	78		
		120MB, NE51H	BF321-0UO-120A	120VAC	10	65		
612nm Super Orange InGaAlP  BF304	T3-1/4 (9mm) Miniature Bayonet LED Cluster 	6MB, 44, 47, 755	BF304-0UO-006B	5/6V	80	520	120°	Center Contact Polarity B = Bipolar AC/DC A = AC only Replace BF304 With B304 for Narrow Beam (15°) 14 K mcd @ 20mA
		12MB, 756	BF304-0UO-014B	12/14V	40	520		
		24MB,	BF304-0UO-024B	24V	20	520		
		313,757,1819,1829	BF304-0UO-028B	28V	20	520		
		48MB	BF304-0UO-048B	48V	12	312		
		60MB,1835	BF304-0UO-060B	60V	12	312		
		120MB, NE51H	BF304-0UO-120A	120VAC	10	260		
612nm Super Orange InGaAlP  BF3126/ BF3127	T3-1/4 (9mm) Miniature Bayonet LED Cluster 	6MB, 44, 47, 755	BF3126-0UO-006B	5/6V	120	510	120°	Center Contact Polarity B = Bipolar AC/DC A = AC only Replace BF3126/3127 With B3126/3127 for Medium Beam (50°) 2.45 K mcd @ 20mA
		12MB, 756	BF3126-0UO-014B	12/14V	40	510		
		24MB,	BF3127-0UO-024B	24V	20	595		
		313,757,1819,1829	BF3127-0UO-028B	28V	20	595		
		48MB	BF3127-0UO-048B	48V	12	357		
		60MB,1835	BF3127-0UO-060B	60V	12	357		
		120MB, NE51H	BF3127-0UO-120A	120VAC	10	298		
			BF3127-0UO-130B	130V	8	238		

All dimensions in inches. For millimeters multiply by 25.4

Log # 122H Rev 10-2000