


VICOR CONFIDENTIAL

THIS DOCUMENT AND THE DATA DISCLOSED
HEREIN OR HERewith IS NOT TO BE REPRODUCED,
USED, OR DISCLOSED IN WHOLE OR IN PART
TO ANYONE WITHOUT PERMISSION OF VICOR CORP.


REV.	DESCRIPTION	DATE	APPROVED
1	RELEASED PER E064265	02/02/06	ECF



- NOTES:
- 1.) TIME CURRENT CHARACTERISTICS: CARRY 100% OF RATING FOR 4.0 HRS. MINIMUM, OPEN OF 200% OF RATING IN 10 SECONDS MAXIMUM. (NON-TIME DELAY).
 - 2.) AGENCY APPROVALS:
PCB, PCC, PCD, PDE, PCF, PCH & PCI. UL RECOGNIZED: FILE E19180.
GUIDE JDYX2. (PCC APPROVAL PENDING)
CSA CERTIFIED: FILE 42731, CLASS 1421-01.
PCG CERTIFICATION PENDING.
 - 3.) RATINGS 2.5 AMPS, 250 V.
 - 4.) COLD RESISTANCE DATA: (10% RATED CURRENT) NOMINAL VALUE 2.5 A - .10Ω.
 - 5.) RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST REVISION.

MARKING:

MFG. ID/PF CODE

DRAWN BY <i>P.E.IENI</i>	DATE <i>10/26/05</i>			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES- TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ±1/64 .XX= ±.01 ±1° .XXX=±.005		<i>FUSE 2.5A 250V</i> <i>BUSS PC-TRON</i>		
THIRD ANGLE PROJECTION 	SIZE B	FSCM NO. 67131	DWG NO 30772	REV 1
DO NOT SCALE DRAWING	SCALE NONE	SHEET 1 OF 1		