




- 2 PHOSPHOR BRONZE
- 3 LCP, UL94V-0
- 4 FINISH:
CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF
TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON
TELCORDIA GR-1217-CORE; APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA: 0.5µm MIN BRIGHT TIN-LEAD OVER BASE PLATING.
- 5 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 6 REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 7 APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD
- 8 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 9 CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995

LOC		DIST		REVISONS			
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED PER ECO-12-006972	23AUG2012	KH	JE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±0.13
±0.05
±
-

±
±
±0.05
±
-

MATERIAL
HOUSING: 3

CONTACTS: 2

DWN
R. TREA
20FEB2007

CHK
R. PATTERSON
20FEB2007

APVD
R. PATTERSON
20FEB2007

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME
HEADER ASSEMBLY, 30 POSITION,
FEED THROUGH, 6 ROW,
BACKPLANE CONNECTOR, Z-PACK HS3

SIZE
A1

CAGE CODE
00779

DRAWING NO
120998

RESTRICTED TO

SCALE
5:1

SHEET
1

OF
1

REV
C

120998-1

AMP
PART NUMBER

TE Connectivity

TE