

Direct Mount Auto Switch

Series D-M9□

Multiple Mounting Options


1. Band mounting



2. Rail mounting



3. Groove mounting



4. Tie-rod mounting



Locations in North America

Atlanta	Indianapolis [M]	Richmond
Austin	Los Angeles [M]	Rochester
Boston	Milwaukee	San Francisco
Charlotte	Minneapolis	St. Louis
Chicago	Montreal	Tampa
Cincinnati	Nashville	Toronto [M]
Cleveland	New Jersey	Vancouver
Dallas	Phoenix	Windsor
Detroit	Portland	

[M] = Manufacturing

Locations Worldwide!

The Americas

Argentina	Bolivia	Brazil	Canada
Chile	Mexico	U.S.A.	Venezuela

Europe

Austria	Bulgaria	Croatia	Czech
Denmark	Estonia	Finland	France
Germany	Hungary	Ireland	Italy
Latvia	Lithuania	Netherlands	Norway
Poland	Romania	Russia	Slovakia
Slovenia	Sweden	Spain/Portugal	
Switzerland	U.K.		

Asia

China	Hong Kong	India	Japan
Malaysia	Philippines	South Korea	Singapore
Taiwan	Thailand		

Oceania

Australia	New Zealand
-----------	-------------



SMC Corporation of America
3011 N. Franklin Road
Indianapolis IN 46226

1-800-762-7621(1-800-SMC-SMC1)
www.smcusa.com

SMC Pneumatics (Canada) Ltd.
6768 Financial Drive Mississauga
Ontario L5N 7J6 Canada

(905) 812-0400
www.smcpcneumatics.ca

© 2005 SMC Corporation of America, All Rights Reserved.

All reasonable efforts to ensure the accuracy of the information detailed in this catalog were made at the time of publishing. However, SMC can in no way warrant the information herein contained as specifications are subject to change without notice.

DEC05-CP25M-LA



Auto Switch




Series D-□□□

Direct Mount Auto Switch

Series **D-M9**□


Replaces D-F9□



Brighter Indicator Light

Twice the brightness


Control point brightness is improved for all viewing angles.



More Flexible Lead Wire

4 times the flexibility

Flexible lead wire is available as standard.



Optional Pre-wired Connector




Increased Range of Load Current

2.5 to 40mA (2-wire)

Conventional types
D-F9B
5 to 40mA

New types
D-M9B
2.5 to 40mA

Two Types of Electrical Entry



Mounting Bracket Part Numbers


For D-M9□ Auto Switches

Switch Mounting Method	Series	Bore Size (mm)	Adaptor Piece Part No.	Switch Mounting Bracket Part No.
Band Mounting	NCDJ2 CDJ2	6	BJ3-1	BJ2-006
		10		BJ2-010
		16		BJ2-016
	CDM2	20		BM2-020
		25		BM2-025
		32		BM2-032
		40		BM2-040
	CD85	10		BJ2-010
		16		BJ2-016
		20		BM2-020
		25		BM2-025
	NCDG1 CDG1	20		BMA2-020
		25		BMA2-025
		32		BMA2-032
		40		BMA2-040
		50		BMA2-050
		63		BMA2-063
Rail Mounting	NCDQ2 CDQ2	12-25	BQ2-012	BQ-1
		32-50		BQ-2
Groove Mounting	MGP MGQ	12-100	BMG2-012	—
Tie-Rod Mounting	CDA2 CDNA CDLA	40, 50	—	BA7-040
		63		BA7-063
		80, 100		BA7-080
	MDB C95SD	32, 40	—	BMB5-032
		50, 63		BA7-040
		80, 100		BA7-063

ALSO AVAILABLE


Trimmer Auto Switch Series D-□7K/D-R□K

OUT1 and OUT2 are adjustable separately.




Band Mounting

- 1) Adaptor piece part number is BJ3-1 (blue shaded parts).
- 2) Select switch mounting bracket part number from table to the left.
- 3) Perpendicular electrical entry type (D-M9□V) cannot be used.




Rail Mounting

- 1) Adaptor piece part number is BQ2-012 (blue shaded part).
- 2) Select switch mounting bracket part number from table to the left.




Groove Mounting

- 1) Adaptor piece part number is BMG2-012.
- 2) Adaptor piece is required for mounting D-M9□ auto switch into a square groove.



Tie-Rod Mounting

- 1) Select switch mounting bracket part number from table to the left.



Optional 2-color indication

Optimum operating position seen at a glance.

- Simplifies the initial auto switch mounting.
Easy to find the optimum operating position.
- Detects unintentional movement or tampering of auto switch position.
Avoids problems related to detection failure.

