


© 1968 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING. APPROVED PER GOVT CONTRACT NO.

REVISIONS

SYM	DESCRIPTION	DATE	APPD
0	RELEASED, WAS CUST. 5168-790 m.s.	5-27-8	
0-1	REVISED 2217 m.s.	9-26-67	
02	.031±.016 WAS .031, TOL. BLOC A ±.005 ECU 1797 72	1-1-77	PAW
A	F. L. R. D. AD4171 JRG	11-21-77	B
B	OK-1 ECN 0034-92	2-9-83	RHC



OBSOLETE

MOD. I	86181-2	.360	.025	.140	.070	.090
MOD. III	86181-1	.265	.020	.090	.030	.080
KEY FOR	PART NO.	A	B	C	D	E

AMP INFO

LOC	AD B 39
-----	---------

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES TOLERANCES ON

FRACTIONS	DECIMALS	ANGLES
± .005	± .005	± .005

MATERIAL
NYLON

HEAT TREAT
H

COLOR
NATURAL

SIGNATURE	DATE
DR <i>Rumold</i>	5-6-68
DSGN ENGR <i>C. Snyder</i>	5/28/68
APPD <i>W. Freese</i>	5-31-68

DSGN APPD	OTHER APPD
-----------	------------



AMP INCORPORATED
HARRISBURG, PENNSYLVANIA

NAME

KEYING PLUG

CODE IDENT NO	SIZE	NUMBER			
00779	A	86181			
SCALE	10-1	WT	CALC	ACTUAL	SHEET