

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG 2006

C

COPYRIGHT 2009

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR


DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

LOGO &
DATE CODE




NOTES:

1. MATERIAL:

HOUSING: THERMOPLASTIC WITH 30% GF, UL 94V-0, COLOR: BLACK.
CONTACTS: PHOSPHOR BRONZE, THICKNESS=0.25mm.
SHIELD: BRASS, THICKNESS=0.30mm.

2. FINISH:

CONTACT: 0.762 μ m [30 μ "] MIN. GOLD PLATED ON CONTACT AREA.
3.048 μ m [120 μ "] MIN. BRIGHT-TIN ON SOLDER TAIL, WITH
ENTIRE CONTACT UNDERPLATED 1.27 μ m [50 μ "] MIN. NICKEL.
SHIELD: 0.762 μ m [30 μ "] MIN. NICKEL OVER 0.762 μ m [30 μ "] MIN.

3. REFLOW SOLDER CAPABLE TO 260°C PER TE TEST SPEC.
109-201, CONDITION B.ALL CONTACTS
AND PEGSRECOMMEND P.C.B LAYOUT (THICKNESS=1.6mm)
(CONDUCTIVE SIDE) TOLERANCE ± 0.05


2-1734082-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	$\pm -$
1 PLC	± 0.35
2 PLC	± 0.25
3 PLC	± 0.15
4 PLC	$\pm -$
ANGLES	$\pm 3^\circ$

FINISH

SEE NOTE

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

USB CON, RCPT, ASS'Y, R/A SMT, A TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779 C=1734082

SCALE

SHEET

2 OF 4

REV B3

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG 2006

C

COPYRIGHT 2009

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION





DATE

DWN

APVD

SEE SHEET 1.

PULL OUT DIRECTION



300	5	1500	5.36	2.73	1-1734082-2
					1-1734082-1
					1734082-2
					1734082-1
PCS/ REEL	REELS/ BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

MATERIAL

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

USB CON, RCPT, ASS'Y, R/A SMT, A TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734082

SCALE

SHEET

3 OF 4

REV B3

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG 2006

C

COPYRIGHT 2009

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION



DATE

DWN

APVD


SEE SHEET 1.

PULL OUT DIRECTION



OBSOLETE

SHIPPING BOX

 $\phi 330(13")$

37.1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$

FINISH

MATERIAL



TE Connectivity

NAME

USB CON, RCPT, ASS'Y, R/A SMT, A TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734082

SCALE

SHEET

4 OF 4

REV

B3