






V1 FILAMENT:
5.2-5.5 VDC
FILAMENT CURRENT:
45 +/- 10 mA DC
V2 ELECTRODE SOURCE:
24-26 V DC TYP.
ELECTRODE CURRENT:
14 +/- 3.0 mA DC
BALLAST RESISTOR:
1K TYP.
ELECTRODE RUNNING VOLTAGE:
10 +/- 3.0 V DC
TOTAL LAMP WATTAGE:
.40 TYP.
INTENSITY
3000 Cd/m2 MIN.
LIFE HOURS:
*15,000

*TO 50% OUTPUT INTENSITY



JKL PART NO.: BGF717-22

			METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE MINIATURE HOT CATHODE FLUORESCENT LAMP (ACORN)					
B	RELEASED TO CAD	5/9/01		DRAWN BY	APP'V'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.	BGF717-22	
A	LIFE HRS-LEAD LENGTH	11/9/99	L. WENGSTROM	F.D.	5/9/01	A	55335				
	RELEASED	7/2/99	- CAD DRAWING -			SCALE	RELEASED DATE	REVISION DATE	REV. NO.	SHEET	
REV. NO.	DESCRIPTION/ECO NUMBER	APP'V'D DATE	MANUAL REVISIONS NOT PERMITTED			NONE	7/2/99	5/9/01	B	1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BGF717-22](#)