

MATERIALS AND FINISHES:







BODY, CRIMP TUBE: BRASS
PLATED NICKEL

CENTER CONTACT: PHOSPHOR BRONZE
PLATED GOLD

INSULATOR: TEFLON

OUTER CONTACT: BERYLLIUM COPPER
PLATED NICKEL

SMB PLUG
INTERFACE



RECOMMENDED STRIPPING DIMENSIONS

PART # 73404-0710

MIL-STD-348A, FIG. 311-2	INTERFACE
SPECIFICATION	DESCRIPTION

CHG: BODY WAS
ZINC

EC NO: URF2011-0692
DRWN: JWIENER 2011/06/13
CHKD: SSS 2011/06/13
APPR: JWIENER 2011/06/13

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .005	± .0005
1 PLACE	± .005	± .0005

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
SSS	2001/11/10
CHECKED BY	DATE
TEF	2001/11/10
APPROVED BY	DATE
GMH	2001/11/10

MATERIAL NO.
734040710

SIZE
C

SCALE
DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

SMB PLUG STR RG-316
50 OHMS, EWR-1503
SMB-PC

MOLEX INCORPORATED

DOCUMENT NO.
SD-73404-071

SHEET NO.
1 OF 1