



2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			F	REVISED PER E.O. PI6998	08DEC2000	SP	RDR
			G	REVISED PER E.O. PI9555	11JUL2007	JA	RDR
			H	REVISED PER E.O. P20396	25JUN2010	JA	RDR
			J	REVISED PER ECO-15-007761	289MAY2015	RL	DM



SECTION A-A
WIRE BARREL

SECTION B-B
INSULATION BARREL

- 3 MATERIAL: .012 [0.30] THICK COPPER ALLOY
2. WIRE RANGE: 18 AWG TO 14 AWG [0.75-2.0 mm²]
INSULATION RANGE: $\varnothing .075$ -.140 [$\varnothing$ 1.91-3.56]
- 1 APPLIES ONLY TO SELECTIVE GOLD 1060-16-0144.
INDICATED DIMENSION SHOWS GOLD PLATED AREA.

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES[mm]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm .025$ [0.64] 4 PLC $\pm$ ANGLES $\pm$
MATERIAL 3	FINISH SEE TABLE

DWN	M. BLUM	04NOV1999
CHK	A. ROLINSKI	08DEC2000
APVD	R. REED	08DEC2000
PRODUCT SPEC		
0425-015-0000		
APPLICATION SPEC		
114-151000		
WEIGHT	0.33 g	
Customer Drawing		

TE INTERNAL PN		DEUTSCH PN	PLATING
1060-16-0122		1060-16-0122	NICKEL
1060-16-0144		1060-16-0144	SELECTIVE GOLD
1060-16-0177		1060-16-0177	TIN
TE Connectivity			
NAME STAMPED CONTACT PIN SIZE 16			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	4AFU8	C=1060-16-01XX	-
SCALE 6:1		SHEET 1 OF 1	REV J