


DO NOT SCALE

DIMENSIONS IN mm

METRIC


THIRD ANGLE

PROJECTION




NOTES:

- 1 FOR USE ON STANDARD APPLICATORS.(RIGHT-LEFT FEED)
- 2 FOR USE ON MINIATURE APPLICATORS.(LEFT-RIGHT FEED)
- 3 FOR USE ON MINIATURE APPLICATORS, AMP O-MATOR APPLICATION.(LEFT-RIGHT FEED)
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI






SECTION B-B



SECTION A-A

WIRE RANGE :
0,5-1,0mm ² AWG
INSULATION RANGE :
1,8-3,3mm DIA.



4	OBSOLETE	2	SEL. GOLD	BRASS	-8=163300=1
	OBSOLETE	3	PRE-TINPLATED	BRASS	1=163300=5
		2	PRE-TINPLATED	PHOSPHOR BR.	163300-8
		2	UNPLATED	PHOSPHOR BR.	163300-7
		2	PRE-TINPLATED	BRASS	163300-6
		2	UNPLATED	BRASS	163300-5
4	OBSOLETE	1	PRE-TINPLATED	PHOSPHOR BR.	163300=4
		1	UNPLATED	PHOSPHOR BR.	163300-3
		1	PRE-TINPLATED	BRASS	163300-2
		1	UNPLATED	BRASS	163300-1
		PLATING	PLATING	MATERIAL	PARTNUMBER

—	—	—	—	—	CUSTOMER DRAWING		FOR REFERENCE ONLY WILL NOT BE UPDATED					
—	—	—	—	—	© COPYRIGHT — BY							
—	—	—	—	—	ALL INTERNATIONAL RIGHTS RESERVED.							
—	—	—	—	—	THIS DRAWING IS UNPUBLISHED							
—	—	—	—	—	RELEASED FOR PUBLICATION —,19—							
—	—	—	—	—	TE Connectivity							
—	—	—	—	—								
J2	REVISED PER ECO-11-005294		RK	HMR	13APR11	NAME SOCKET MATE-N-LOK.						
LTR.	REVISION RECORD		DR.	CHK.	DATE							
DR.: J.V.D.HEIJDEN.		CHK.: A.BIJNEN.		APP.: L.V.SOEST.		DWG.No.			REV.LTR.	SHEET	A3	
DATE: 10-04-92		DATE: —		DATE: —		163300			J2	1 OF 1		