

## Crimpmate Range - RSV 1.6

The rectangular connector system RSV 1.6 in 5.00 mm pitch guarantees the highest proven contact reliability during strong vibration. Without any screws: When the connector is plugged in, the pin headers and socket blocks lock together and can only be separated when the release levers are activated.

To achieve the high density of connections required, the RSV 1.6 has been designed utilising crimp technology. This connection technique permits the components to be pre-assembled in large batches. Thus, the crimpmate range saves space and combines safe contacts and swift installation.

Two crimp contact systems are available for use with the RSV 1.6: GB/GS - is the low cost "fit-for-use" system. CB/CS - is the high-spec, high vibration resistant, high mating cycles option.



### Product features overview:

- vibration-resistant due to a high-quality contact system
- integrated fixing flanges for the printed circuit board headers
- locking latches ensure a secure connection of the socket block to the pin header
- multi-row capability provides a high connection density
- protection against incorrect insertion
- large selection of accessories

## Crimpmate Range - RSV 1.6



### Pin headers RSV 1.6 LS



| Technical Data | VDE | UL   | CSA |
|----------------|-----|------|-----|
| Rated voltage  | V   | 250* | 300 |
| Rated current  | A   | 10   | 10  |

\*Overvoltage category III / Pollution severity 3  
Additional technical data see page 232

Solder pin length 3.2 mm 4.5 mm  
tin-plated version



| Poles | Type            | Cat. No.   | Cat. No.   | Qty. |
|-------|-----------------|------------|------------|------|
| 4     | RSV 1.6 LS4 SN  | 1440500000 | 1413500000 | 100  |
| 6     | RSV 1.6 LS6 SN  | 1441500000 | 1414500000 | 50   |
| 9     | RSV 1.6 LS9 SN  | 1442500000 | 1415500000 | 50   |
| 12    | RSV 1.6 LS12 SN | 1443500000 | 1416500000 | 25   |
| 18    | RSV 1.6 LS18 SN | 1444500000 | 1417500000 | 25   |
| 24    | RSV 1.6 LS24 SN | 1445500000 | 1418500000 | 20   |
| 36    | RSV 1.6 LS36 SN | 1446500000 | 1419500000 | 10   |

Solder pin length 3.2 mm 4.5 mm  
gold-plated version

| Poles | Type            | Cat. No.   | Cat. No.   | Qty. |
|-------|-----------------|------------|------------|------|
| 4     | RSV 1.6 LS4 AU  | 1440400000 | 1413400000 | 100  |
| 6     | RSV 1.6 LS6 AU  | 1441400000 | 1414400000 | 50   |
| 9     | RSV 1.6 LS9 AU  | 1442400000 | 1415400000 | 50   |
| 12    | RSV 1.6 LS12 AU | 1443400000 | 1416400000 | 25   |
| 18    | RSV 1.6 LS18 AU | 1444400000 | 1417400000 | 25   |
| 24    | RSV 1.6 LS24 AU | 1445400000 | 1418400000 | 20   |
| 36    | RSV 1.6 LS36 AU | 1446400000 | 1419400000 | 10   |

| Accessories   | Page                  |
|---------------|-----------------------|
| Fixing        | integrated in product |
| Marking       | –                     |
| Coding        | 198                   |
| Miscellaneous | –                     |

### Pin headers RSV 1.6 LSF



| Technical Data | VDE | UL   | CSA |
|----------------|-----|------|-----|
| Rated voltage  | V   | 250* | 300 |
| Rated current  | A   | 10   | 10  |

\*Overvoltage category III / Pollution severity 3  
Additional technical data see page 232

Solder pin length 3.2 mm 4.5 mm  
tin-plated version



| Poles | Type             | Cat. No.   | Cat. No.   | Qty. |
|-------|------------------|------------|------------|------|
| 4     | RSV 1.6 LSF4 SN  | 1440900000 | 1413900000 | 100  |
| 6     | RSV 1.6 LSF6 SN  | 1441900000 | 1414900000 | 50   |
| 9     | RSV 1.6 LSF9 SN  | 1442900000 | 1415900000 | 50   |
| 12    | RSV 1.6 LSF12 SN | 1443900000 | 1416900000 | 25   |
| 18    | RSV 1.6 LSF18 SN | 1444900000 | 1417900000 | 25   |
| 24    | RSV 1.6 LSF24 SN | 1445900000 | 1418900000 | 20   |
| 36    | RSV 1.6 LSF36 SN | 1446900000 | 1419900000 | 10   |

Solder pin length 3.2 mm 4.5 mm  
gold-plated version

| Poles | Type             | Cat. No.   | Cat. No.   | Qty. |
|-------|------------------|------------|------------|------|
| 4     | RSV 1.6 LSF4 AU  | 1440800000 | 1413800000 | 100  |
| 6     | RSV 1.6 LSF6 AU  | 1441800000 | 1414800000 | 50   |
| 9     | RSV 1.6 LSF9 AU  | 1442800000 | 1415800000 | 50   |
| 12    | RSV 1.6 LSF12 AU | 1443800000 | 1416800000 | 25   |
| 18    | RSV 1.6 LSF18 AU | 1444800000 | 1417800000 | 25   |
| 24    | RSV 1.6 LSF24 AU | 1445800000 | 1418800000 | 20   |
| 36    | RSV 1.6 LSF36 AU | 1446800000 | 1419800000 | 10   |

| Accessories   | Page                  |
|---------------|-----------------------|
| Fixing        | integrated in product |
| Marking       | –                     |
| Coding        | 198                   |
| Miscellaneous | –                     |

### Socket blocks RSV 1.6 LB



| Technical Data | VDE | UL   | CSA |
|----------------|-----|------|-----|
| Rated voltage  | V   | 250* | 300 |
| Rated current  | A   | 10   | 10  |

\*Overvoltage category III / Pollution severity 3  
Additional technical data see page 232

Solder pin length 3.2 mm 4.5 mm  
tin-plated version








| Poles | Type            | Cat. No.   | Cat. No.   | Qty. |
|-------|-----------------|------------|------------|------|
| 4     | RSV 1.6 LB4 SN  | 1440300000 | 1413300000 | 100  |
| 6     | RSV 1.6 LB6 SN  | 1441300000 | 1414300000 | 50   |
| 9     | RSV 1.6 LB9 SN  | 1442300000 | 1415300000 | 50   |
| 12    | RSV 1.6 LB12 SN | 1443300000 | 1416300000 | 25   |
| 18    | RSV 1.6 LB18 SN | 1444300000 | 1417300000 | 25   |
| 24    | RSV 1.6 LB24 SN | 1445300000 | 1418300000 | 20   |
| 36    | RSV 1.6 LB36 SN | 1446300000 | 1419300000 | 10   |

Solder pin length 3.2 mm 4.5 mm  
gold-plated version

| Poles | Type            | Cat. No.   | Cat. No.   | Qty. |
|-------|-----------------|------------|------------|------|
| 4     | RSV 1.6 LB4 AU  | 1440200000 | 1413200000 | 100  |
| 6     | RSV 1.6 LB6 AU  | 1441200000 | 1414200000 | 50   |
| 9     | RSV 1.6 LB9 AU  | 1442200000 | 1415200000 | 50   |
| 12    | RSV 1.6 LB12 AU | 1443200000 | 1416200000 | 25   |
| 18    | RSV 1.6 LB18 AU | 1444200000 | 1417200000 | 25   |
| 24    | RSV 1.6 LB24 AU | 1445200000 | 1418200000 | 20   |
| 36    | RSV 1.6 LB36 AU | 1446200000 | 1419200000 | 10   |

| Accessories   | Page                  |
|---------------|-----------------------|
| Fixing        | integrated in product |
| Marking       | –                     |
| Coding        | 198                   |
| Miscellaneous | –                     |

## Pin headers RSV 1.6S



| Technical Data |   | VDE  | UL  | CSA |
|----------------|---|------|-----|-----|
| Rated voltage  | V | 250* | 300 | 300 |
| Rated current  | A | 10   | 10  | 13  |

\*Overvoltage category III / Pollution severity 3  
Additional technical data see page 232

| Technical Data             |                      | VDE  | UL  | CSA |
|----------------------------|----------------------|------|-----|-----|
| <b>Rated voltage</b>       | V                    | 320* | 600 | 600 |
| <b>Rated current</b>       | A                    | 13   | 10  | 13  |
| <b>Clamping range max.</b> | mm <sup>2</sup> /AWG | 2.5  | 12  | 12  |

\*Overvoltage category III / Pollution severity 3  
Additional technical data see page 232

| Technical Data      |                      | VDE  | UL  | CSA |
|---------------------|----------------------|------|-----|-----|
| Rated voltage       | V                    | 320* | 600 | 600 |
| Rated current       | A                    | 13   | 10  | 13  |
| Clamping range max. | mm <sup>2</sup> /AWG | 2.5  | 12  | 12  |

\*Overvoltage category III / Pollution severity 3  
Additional technical data see page 232

**Solder pin length**  
tin-plated version

3.2 mm      4.5 mm



**Colour**

| Poles | Type             | Cat. No.   | Cat. No.   | Qty. |
|-------|------------------|------------|------------|------|
| 4     | RSV 1.6 LBF4 SN  | 1440700000 | 1413700000 | 100  |
| 6     | RSV 1.6 LBF6 SN  | 1441700000 | 1414700000 | 50   |
| 9     | RSV 1.6 LBF9 SN  | 1442700000 | 1415700000 | 50   |
| 12    | RSV 1.6 LBF12 SN | 1443700000 | 1416700000 | 25   |
| 18    | RSV 1.6 LBF18 SN | 1444700000 | 1417700000 | 25   |
| 24    | RSV 1.6 LBF24 SN | 1445700000 | 1418700000 | 20   |
| 36    | RSV 1.6 LBF36 SN | 1446700000 | 1419700000 | 10   |

**Colour**



| Poles | Type        | Cat. No.          | Qty. |
|-------|-------------|-------------------|------|
| 4     | RSV 1.6 B4  | <b>1413000000</b> | 25   |
| 6     | RSV 1.6 B6  | <b>1414000000</b> | 25   |
| 9     | RSV 1.6 B9  | <b>1415000000</b> | 25   |
| 12    | RSV 1.6 B12 | <b>1416000000</b> | 25   |
| 18    | RSV 1.6 B18 | <b>1417000000</b> | 25   |
| 24    | RSV 1.6 B24 | <b>1418000000</b> | 20   |
| 36    | RSV 1.6 B36 | <b>1419000000</b> | 10   |

**Colour**



| Poles | Type        | Cat. No.          | Qty. |
|-------|-------------|-------------------|------|
| 4     | RSV 1.6 S4  | <b>1413100000</b> | 25   |
| 6     | RSV 1.6 S6  | <b>1414100000</b> | 25   |
| 9     | RSV 1.6 S9  | <b>1415100000</b> | 25   |
| 12    | RSV 1.6 S12 | <b>1416100000</b> | 25   |
| 18    | RSV 1.6 S18 | <b>1417100000</b> | 25   |
| 24    | RSV 1.6 S24 | <b>1418100000</b> | 20   |
| 36    | RSV 1.6 S36 | <b>1419100000</b> | 10   |

**Suitable contact systems listed on next double page.**

**Suitable contact systems listed on next double page.**

**Solder pin length**  
**gold-plated version**

3.2 mm      4.5 mm



**Colour**


| Poles | Type             | Cat. No.   | Cat. No.   | Qty. |
|-------|------------------|------------|------------|------|
| 4     | RSV 1.6 LBF4 AU  | 1440600000 | 1413600000 | 100  |
| 6     | RSV 1.6 LBF6 AU  | 1441800000 | 1414600000 | 50   |
| 9     | RSV 1.6 LBF9 AU  | 1442600000 | 1415600000 | 50   |
| 12    | RSV 1.6 LBF12 AU | 1443600000 | 1416600000 | 25   |
| 18    | RSV 1.6 LBF18 AU | 1444600000 | 1417600000 | 25   |
| 24    | RSV 1.6 LBF24 AU | 1445600000 | 1418600000 | 20   |
| 36    | RSV 1.6 LBF36 AU | 1446600000 | 1419600000 | 10   |

| Accessories   | Page                  |
|---------------|-----------------------|
| Fixing        | integrated in product |
| Marking       | —                     |
| Coding        | 198                   |
| Miscellaneous | —                     |

| Accessories   | Page                  |
|---------------|-----------------------|
| Fixing        | integrated in product |
| Marking       | –                     |
| Coding        | 198                   |
| Miscellaneous | 203, 206, 207         |

| Accessories   | Page                  |
|---------------|-----------------------|
| Fixing        | integrated in product |
| Marking       | –                     |
| Coding        | 198                   |
| Miscellaneous | 203, 206, 207         |


## Contact system GS/GB



- low cost and reliable contacts
- up to 100 mating cycles (gold-plated version)
- up to 50 mating cycles (tin-plated version)



## Contact system CS/CB



- proven crimp contact design with four defined contact points
- locking latch in upper steel spring for non-slip contact fit
- up to 500 mating cycles (gold-plated version)
- up to 100 mating cycles (tin-plated version)



## Crimp contacts GS/GB

The contact system GS/GB must not be combined with the CS/CB system!

| Cable cross-section mm <sup>2</sup> | AWG     | Insulation diameter mm | Type   |
|-------------------------------------|---------|------------------------|--------|
| 0.32...0.5                          | 22...20 | 2.0...2.5              | Pin    |
|                                     |         |                        | Socket |
| 0.75...1.5                          | 18...16 | 2.0...3.5              | Pin    |
|                                     |         |                        | Socket |

Single contacts  
tin-plated version

| Description        | Cat. No.          | Qty. |
|--------------------|-------------------|------|
| GS 1.6E 22-20 SnPb | <b>1629870000</b> | 250  |
| GB 1.6E 22-20 SnPb | <b>1629790000</b> | 250  |
| GS 1.6E 18-16 SnPb | <b>1629860000</b> | 250  |
| GB 1.6E 18-16 SnPb | <b>1629780000</b> | 250  |

Bandolier  
tin-plated version

| Description        | Cat. No.          | Qty. |
|--------------------|-------------------|------|
| GS 1.6R 22-20 SnPb | <b>1629890000</b> | 4500 |
| GB 1.6R 22-20 SnPb | <b>1629810000</b> | 4500 |
| GS 1.6R 18-16 SnPb | <b>1629880000</b> | 4500 |
| GB 1.6R 18-16 SnPb | <b>1629800000</b> | 4500 |

| Cable cross-section mm <sup>2</sup> | AWG     | Insulation diameter mm | Type   |
|-------------------------------------|---------|------------------------|--------|
| 0.32...0.5                          | 22...20 | 2.0...2.5              | Pin    |
|                                     |         |                        | Socket |
| 0.75...1.5                          | 18...16 | 2.0...3.5              | Pin    |
|                                     |         |                        | Socket |

Single contacts  
gold-plated version

| Description           | Cat. No.          | Qty. |
|-----------------------|-------------------|------|
| GS 1.6E 22-20 AU 0.75 | <b>1629830000</b> | 250  |
| GB 1.6E 22-20 AU 0.75 | <b>1629750000</b> | 250  |
| GS 1.6E 18-16 AU 0.75 | <b>1629820000</b> | 250  |
| GB 1.6E 18-16 AU 0.75 | <b>1629740000</b> | 250  |

Bandolier  
gold-plated version

| Description           | Cat. No.          | Qty. |
|-----------------------|-------------------|------|
| GS 1.6R 22-20 AU 0.75 | <b>1629850000</b> | 4500 |
| GB 1.6R 22-20 AU 0.75 | <b>1629770000</b> | 4500 |
| GS 1.6R 18-16 AU 0.75 | <b>1629840000</b> | 4500 |
| GB 1.6R 18-16 AU 0.75 | <b>1629760000</b> | 4500 |

## Crimp contacts CS/CB

The contact system CS/CB must not be combined with the GS/GB contact system!

| Cable cross-section mm <sup>2</sup> | AWG     | Insulation diameter mm | Type           |
|-------------------------------------|---------|------------------------|----------------|
| 0.14...0.25                         | 26...24 | 0.8...1.4              | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 0.34...0.5                          | 22...20 | 1.1...1.8              | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 0.34...0.5                          | 22...20 | 2.0...2.5              | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 0.75...1.5                          | 18...16 | 2.0 ...2.5             | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 0.75...1.5                          | 18...16 | 2.0 ...3.5             | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 2.5                                 | 14...12 | 2.8 ...3.5             | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 2.5                                 | 14...12 | 2.8 ...4.2             | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |

Single contacts  
tin-plated version

| Description            | Cat. No.           | Qty. |
|------------------------|--------------------|------|
| CS 1.6E 26-24 SN I1.4  | <b>1421600000</b>  | 250  |
| CSL 1.6E 26-24 SN I1.4 | <b>1421700000*</b> | 250  |
| CB 1.6E 26-24 SN I1.4  | <b>1421900000</b>  | 250  |
| CS 1.6E 22-20 SN I1.8  | <b>1423600000</b>  | 250  |
| CSL 1.6E 22-20 SN I1.8 | <b>1423700000*</b> | 250  |
| CB 1.6E 22-20 SN I1.8  | <b>1423900000</b>  | 250  |
| CS 1.6E 22-20 SN I2.5  | <b>1425600000</b>  | 250  |
| CSL 1.6E 22-20 SN I2.5 | <b>1425700000*</b> | 250  |
| CB 1.6E 22-20 SN I2.5  | <b>1425900000</b>  | 250  |
| CS 1.6E 18-16 SN I2.5  | <b>1427600000</b>  | 250  |
| CSL 1.6E 18-16 SN I2.5 | <b>1427700000*</b> | 250  |
| CB 1.6E 18-16 SN I2.5  | <b>1427900000</b>  | 250  |
| CS 1.6E 18-16 SN I3.5  | <b>1582270000</b>  | 250  |
| CSL 1.6E 18-16 SN I3.5 | <b>1582350000*</b> | 250  |
| CB 1.6E 18-16 SN I3.5  | <b>1582430000</b>  | 250  |
| CS 1.6E 14-12 SN I3.5  | <b>1429600000</b>  | 250  |
| CSL 1.6E 14-12 SN I3.5 | <b>1429700000*</b> | 250  |
| CB 1.6E 14-12 SN I3.5  | <b>1429900000</b>  | 250  |
| CS 1.6E 14-12 SN I4.2  | <b>1582310000</b>  | 250  |
| CSL 1.6E 14-12 SN I4.2 | <b>1582390000*</b> | 250  |
| CB 1.6E 14-12 SN I4.2  | <b>1582470000</b>  | 250  |

\* The long pins can be used with the standard pins to provide a leading-earth facility.

Bandolier  
tin-plated version

| Description            | Cat. No.           | Qty. |
|------------------------|--------------------|------|
| CS 1.6R 26-24 SN I1.4  | <b>1421500000</b>  | 5000 |
| CSL 1.6R 26-24 SN I1.4 | <b>1565900000*</b> | 5000 |
| CB 1.6R 26-24 SN I1.4  | <b>1421800000</b>  | 5000 |
| CS 1.6R 22-20 SN I1.8  | <b>1423500000</b>  | 5000 |
| CSL 1.6R 22-20 SN I1.8 | <b>1565870000*</b> | 5000 |
| CB 1.6R 22-20 SN I1.8  | <b>1423800000</b>  | 5000 |
| CS 1.6R 22-20 SN I2.5  | <b>1425500000</b>  | 5000 |
| CSL 1.6R 22-20 SN I2.5 | <b>1565840000*</b> | 5000 |
| CB 1.6R 22-20 SN I2.5  | <b>1425800000</b>  | 5000 |
| CS 1.6R 18-16 SN I2.5  | <b>1427500000</b>  | 5000 |
| CSL 1.6R 18-16 SN I2.5 | <b>1565810000*</b> | 5000 |
| CB 1.6R 18-16 SN I2.5  | <b>1427800000</b>  | 5000 |
| CS 1.6R 18-16 SN I3.5  | <b>1582280000</b>  | 3000 |
| CSL 1.6R 18-16 SN I3.5 | <b>1582360000*</b> | 3000 |
| CB 1.6R 18-16 SN I3.5  | <b>1582440000</b>  | 3000 |
| CS 1.6R 14-12 SN I3.5  | <b>1429500000</b>  | 3000 |
| CSL 1.6R 14-12 SN I3.5 | <b>1565780000*</b> | 3000 |
| CB 1.6R 14-12 SN I3.5  | <b>1429800000</b>  | 3000 |
| CS 1.6R 14-12 SN I4.2  | <b>1582320000</b>  | 3000 |
| CSL 1.6R 14-12 SN I4.2 | <b>1582400000*</b> | 3000 |
| CB 1.6R 14-12 SN I4.2  | <b>1582480000</b>  | 3000 |

\* The long pins can be used with the standard pins to provide a leading-earth facility.

Single contacts  
gold-plated version

| Cable cross-section mm <sup>2</sup> | AWG     | Insulation diameter mm | Type           |
|-------------------------------------|---------|------------------------|----------------|
| 0.14...0.25                         | 26...24 | 0.8...1.4              | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 0.34...0.5                          | 22...20 | 1.1...1.8              | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 0.34...0.5                          | 22...20 | 2.0...2.5              | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 0.75...1.5                          | 18...16 | 2.0 ...2.5             | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 0.75...1.5                          | 18...16 | 2.0 ...3.5             | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 2.5                                 | 14...12 | 2.8 ...3.5             | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |
| 2.5                                 | 14...12 | 2.8 ...4.2             | Pin - standard |
|                                     |         |                        | Pin - long     |
|                                     |         |                        | Socket         |

| Description                 | Cat. No.           | Qty. |
|-----------------------------|--------------------|------|
| CS 1.6E 26-24 AU 0.75 I1.4  | <b>1420600000</b>  | 250  |
| CSL 1.6E 26-24 AU 0.75 I1.4 | <b>1420700000*</b> | 250  |
| CB 1.6 26-24 AU 0.75 I1.4   | <b>1420900000</b>  | 250  |
| CS 1.6E 22-20 AU 0.75 I1.8  | <b>1422600000</b>  | 250  |
| CSL 1.6E 22-20 AU 0.75 I1.8 | <b>1422700000*</b> | 250  |
| CB 1.6E 22-20 AU 0.75 I1.8  | <b>1422900000</b>  | 250  |
| CS 1.6E 22-20 AU 0.75 I2.5  | <b>1424600000</b>  | 250  |
| CSL 1.6E 22-20 AU 0.75 I2.5 | <b>1424700000*</b> | 250  |
| CB 1.6E 22-20 AU 0.75 I2.5  | <b>1424900000</b>  | 250  |
| CS 1.6E 18-16 AU 0.75 I2.5  | <b>1426600000</b>  | 250  |
| CSL 1.6E 18-16 AU 0.75 I2.5 | <b>1426700000*</b> | 250  |
| CB 1.6E 18-16 AU 0.75 I2.5  | <b>1426900000</b>  | 250  |
| CS 1.6E 18-16 AU 0.75 I3.5  | <b>1582250000</b>  | 250  |
| CSL 1.6E 18-16 AU 0.75 I3.5 | <b>1582330000*</b> | 250  |
| CB 1.6E 18-16 AU 0.75 I3.5  | <b>1582410000</b>  | 250  |
| CS 1.6E 14-12 AU 0.75 I3.5  | <b>1428600000</b>  | 250  |
| CSL 1.6E 14-12 AU 0.75 I3.5 | <b>1428700000*</b> | 250  |
| CB 1.6E 14-12 AU 0.75 I3.5  | <b>1428900000</b>  | 250  |
| CS 1.6E 14-12 AU 0.75 I4.2  | <b>1582290000</b>  | 250  |
| CSL 1.6E 14-12 AU 0.75 I4.2 | <b>1582370000*</b> | 250  |
| CB 1.6E 14-12 AU 0.75 I4.2  | <b>1582450000</b>  | 250  |

\* The long pins can be used with the standard pins to provide a leading-earth facility.

Bandolier  
gold-plated version

| Description                 | Cat. No.           | Qty. |
|-----------------------------|--------------------|------|
| CS 1.6R 26-24 AU 0.75 I1.4  | <b>1420500000</b>  | 5000 |
| CSL 1.6R 26-24 AU 0.75 I1.4 | <b>1565880000*</b> | 5000 |
| CB 1.6R 26-24 AU 0.75 I1.4  | <b>1420800000</b>  | 5000 |
| CS 1.6R 22-20 AU 0.75 I1.8  | <b>1422500000</b>  | 5000 |
| CSL 1.6R 22-20 AU 0.75 I1.8 | <b>1565850000*</b> | 5000 |
| CB 1.6R 22-20 AU 0.75 I1.8  | <b>1422800000</b>  | 5000 |
| CS 1.6R 22-20 AU 0.75 I2.5  | <b>1424500000</b>  | 5000 |
| CSL 1.6R 22-20 AU 0.75 I2.5 | <b>1565820000*</b> | 5000 |
| CB 1.6R 22-20 AU 0.75 I2.5  | <b>1424800000</b>  | 5000 |
| CS 1.6R 18-16 AU 0.75 I2.5  | <b>1426500000</b>  | 5000 |
| CSL 1.6R 18-16 AU 0.75 I2.5 | <b>1565790000*</b> | 5000 |
| CB 1.6R 18-16 AU 0.75 I2.5  | <b>1426800000</b>  | 5000 |
| CS 1.6R 18-16 AU 0.75 I3.5  | <b>1582260000</b>  | 3000 |
| CSL 1.6R 18-16 AU 0.75 I3.5 | <b>1582340000*</b> | 3000 |
| CB 1.6R 18-16 AU 0.75 I3.5  | <b>1582420000</b>  | 3000 |
| CS 1.6R 14-12 AU 0.75 I3.5  | <b>1428500000</b>  | 3000 |
| CSL 1.6R 14-12 AU 0.75 I3.5 | <b>1565760000*</b> | 3000 |
| CB 1.6R 14-12 AU 0.75 I3.5  | <b>1428800000</b>  | 3000 |
| CS 1.6R 14-12 AU 0.75 I4.2  | <b>1582300000</b>  | 3000 |
| CSL 1.6R 14-12 AU 0.75 I4.2 | <b>1582380000*</b> | 3000 |
| CB 1.6R 14-12 AU 0.75 I4.2  | <b>1582460000</b>  | 3000 |

\* The long pins can be used with the standard pins to provide a leading-earth facility.

