

SOT89 PNP SILICON PLANAR MEDIUM POWER TRANSISTOR


ISSUE 4 – JUNE 1996



BSR30

COMPLEMENTARY TYPE – BSR40

PARTMARKING DETAIL – BR1



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	-70	V
Collector-Emitter Voltage	V_{CEO}	-60	V
Emitter-Base Voltage	V_{EBO}	-5	V
Peak Pulse Current	I_{CM}	-2	A
Continuous Collector Current	I_C	-1	A
Power Dissipation at $T_{amb}=25^{\circ}C$	P_{tot}	1	W
Operating and Storage Temperature Range	T_j, T_{stg}	-65 to +150	$^{\circ}C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$ unless otherwise stated).

PARAMETER	SYMBOL	MIN.	MAX.	UNIT	CONDITIONS.
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	-70		V	$I_C = -100\mu A$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	-60		V	$I_C = -10mA$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	-5		V	$I_E = -10\mu A$
Collector Cut-Off Current	I_{CBO}		-100 -50	nA μA	$V_{CB} = -60V$ $V_{CB} = -60V, T_{amb} = 125^{\circ}C$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$		-0.25 -0.5	V V	$I_C = -150mA, I_B = -15mA$ $I_C = -500mA, I_B = -50mA$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$		-1.0 -1.2	V V	$I_C = -150mA, I_B = -15mA$ $I_C = -500mA, I_B = -50mA$
Static Forward Current Transfer Ratio	h_{FE}	10 40 30	120		$I_C = -100\mu A, V_{CE} = -5V$ $I_C = -100mA, V_{CE} = -5V$ $I_C = -500mA, V_{CE} = -5V$
Collector Capacitance	C_c		20	pF	$V_{CB} = -10V, f = 1MHz$
Emitter Capacitance	C_e		120	pF	$V_{EB} = -0.5V, f = 1MHz$
Transition Frequency	f_T	100		MHz	$I_C = -50mA, V_{CE} = -10V$ $f = 35MHz$
Turn-On Time	T_{on}		500	ns	$V_{CC} = -20V, I_C = -100mA$ $I_{B1} = -I_{B2} = -5mA$
Turn-Off Time	T_{off}		650	ns	

*Measured under pulsed conditions. Pulse width=300 μs . Duty cycle $\leq 2\%$
For typical characteristics graphs see FMMT551 datasheet.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diodes Incorporated:](#)

[BSR30TA](#)