

RF AMPLIFIER

MODEL *TM9114*

Available as: TM9114, 4 Pin TO-8 (T4)
 TN9114, 4 Pin Surface Mount (SM3)
 FP9114, 4 Pin Flatpack (FP4)
 BX9114, Connectorized Housing (H1)

Features

- High Gain: 20 dB Typical
- Medium Output Power: +6.5 dBm Typical
- Operating Temp. - 55 °C to +85 °C
- Environmental Screening Available

Specifications

CHARACTERISTIC	TYPICAL Ta= 25 °C	MIN/MAX Ta = -55 °C to +85 °C
Frequency	10 - 1500 MHz	10 - 1500 MHz
Gain (dB)	20	18.0 Min.
Power @ 1 dB Comp. (dBm)	+7	+5.0 Min.
Reverse Isolation (dB)	- 32	- 30 Max.
VSWR In	<1.4:1	2.0:1 Max.
Out	<1.4:1	2.0:1 Max.
Noise figure (dB)	<4.0	5.5 Max.
Power Vdc	+12	+12
mA	34	38 Max.

Note: Care should always be taken to effectively ground the case of each unit.


Typical Intermodulation Performance at 25 ° C

Second Order Harmonic Intercept Point +47 (Typ.)
 Second Order Two Tone Intercept Point +42 (Typ.)
 Third Order Two Tone Intercept Point +21 (Typ.)

Maximum Ratings

Ambient Operating Temperature -55°C to + 100 °C
 Storage Temperature -62°C to + 125 °C
 Case Temperature + 125 °C
 DC Voltage + 15 Volts
 Continuous RF Input Power + 6 dBm
 Short Term RF Input Power 50 Milliwatts
 (1 Minute Max.)
 Maximum Peak Power 0.5 Watt
 (3 µsec Max.)

Typical Performance Data



Legend ——— + 25 °C - - - + 85 °C -55 °C

Linear S-Parameters

FREQ. MHz	S11		S21		S12		S22	
	Mag	Deg	Mag	Deg	Mag	Deg	Mag	Deg
10	.02	-38	10.48	-0	.02	0	.08	-170
50	.02	-50	10.26	-9	.02	-5	.08	-172
100	.02	-73	10.18	-18	.02	-7	.09	-171
200	.03	-118	10.12	-36	.02	-0	.10	-171
400	.07	-170	10.04	-72	.02	-4	.15	176
600	.12	150	10.10	-108	.02	-1	.18	151
800	.17	113	10.10	-145	.02	-14	.19	122
1000	.18	81	9.95	178	.02	-20	.16	88
1200	.14	52	9.75	141	.03	-37	.12	47
1400	.04	28	9.91	105	.03	-47	.08	-14
1500	.04	167	10.20	84	.02	-52	.08	-56

Amplifonix

2707 Black Lake Place, Philadelphia, PA 19154

TEL 215-464-4000 • • • • FAX 215-464-4001 3/18/03