

PRODUCT NUMBER

73325-XXXLF

PLATING OPTION

1= GXT 0.76 μm
 3= GOLD 0.76 μm
 5= GOLD 1.27 μm

PACKAGE OPTION

1= TAPE ON REEL
 2= TUBE
 3= TAPE ON REEL
 IN PLASTIC BAG

TERMINAL LOADING

1= FULLY LOADED
 2= POS 1,2,7,8
 3= POS 3,4,5,6

WHEN NEEDED, SUFFIX LETTER "LF"
 INDICATES THE PRODUCT IS RoHS
 COMPATIBLE, SEE NOTE 4.

NOTES:

1- MATERIAL: HOUSING: HIGH TEMP. NYLON, COLOUR BLACK.
 TERMINAL: PHOSPHOR BRONZE.
 2 - PLATING: CONTACT AREA: SEE TABLE.
 SOLDER TAIL : 90/10 SnPb 2 μm MIN.
 WHEN SUFFIX "LF" IS REQUIRED, 2 μm MIN MATTE
 TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
 NO RAW EDGES EXCEPT SOLDER TAIL TIPS

3 - SOLDER TAILS COPLANARITY : 0.1 mm

4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
 2 μm MINIMUM MATTE TIN OVER 1.27 μm
 MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY


- THE HOUSING WILL WITHSTAND EXPOSURE TO
 245°C PEAK TEMPERATURE FOR 30 SECONDS
 MAX IN A CONVECTION, INFRA-RED OR VAPOR
 PHASE OR REFLOW OVEN.

c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-22-008

5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
 TO PROTECT FROM MOISTURE DURING STACKING TIME.








CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code		surface	tolerance	projection	product family
		ISO 1302	ISO 406 ISO 1101		MOD JACK
ltr	ecn no	dr	date	tolerances unless otherwise specified	title
H	F06-0240	DLE	06.07.18	angles	SMT RA JACK
J	F09-0070	LSA	09.07.23	linear	8 POS INSIDE
				±2'	scale 2:1
D	F80620	DLE	98.11.26	dr	D LEGRAND
E	F03020	DLE	03.01.27	enrg	P NIZZI
F	F04-0363	DLE	04.10.18	chr	D LEGRAND
G	F05-0247	DLE	05.09.12	appd	P NZ
sheet	revision	J	E	B	
index	sheet	1	2	3	



PRODUCT NUMBER
SEE SHEET 1

LTR	PART NAME	QTY
1	PRODUCT	230
2	TAPE	1
3	REEL	1
4	COVER TAPE	1



1- IN ACCORDANCE WITH EIA-481 AND IEC 296-3

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MOD—JACK					
ltr	ecn no	dr	date	tolerances unless otherwise specified						title					
D	F80620	DLE	98.11.26	angles		linear		mm 		SMT RA JACK 8 POS. INSIDE					
E	F06—0240	DLE	06.07.18					scale 1:1							
				dr	D LEGRAND		06.07.18				dwg no		sheet 2 of 3		size
				engr	P NIZZI		06.07.18				73325				A3
				chr	D LE		06.07.18								
				appd	P NZ		06.07.18								
sheet index		revision sheet								type CUSTOMER Drawing					

PDM: Rev:J

STATUS Released

Printed: Oct 01, 2010

1

2

A

B

C

D

D

form: A4

1

2

Fciconnect.com



PDM: Rev:J


STATUSReleased

Printed: Oct 01, 2010

Copyright FCI

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface	tolerance		projection		product family	
				ISO 1302	ISO 406	ISO 1101			MOD JACK	
ltr	ecr	no	dr	tolerances unless otherwise specified					title	
A	F04-0363	DLE	04.10.18	angles	±0.13		scale 2:1		SMT RA JACK	
B	F06-0240	DLE	06.07.18	±2°	linear				8 POS INSIDE	
				dr	D	LEGRAND	04.10.18	dwg no		sheet 3 of - size
				engr	P	NIZZI	04.10.18	73325		A4
				chr	D	LEGRAND	04.10.18	type		CUSTOMER Drawing
				appd	P	NZ	04.10.18			
sheet index	revision									
	sheet									



A

B

C

D