

MARKING

 MEDER-Label, Type
 Production code EN60062/
 Factory code

 MEDER-Logo, Typ
 Produktionscode
 EN60062/Fertigungsstätte

Coil Data at 20 °C	Conditions	Min	Typ	Max	Unit
Coil resistance		45	50	55	Ohm
Coil voltage			5		VDC
Rated power			625		mW
Coil current			125		mA
Thermal resistance	max. Relay temperature = operating temperature + self heating		25		K/W
Inductance			44		mH
Pull-In voltage				3,5	VDC
Drop-Out voltage		0,75			VDC

Contact data 69	Conditions	Min	Typ	Max	Unit
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			50	W
Switching voltage	DC or Peak AC			10.000	V
Switching current	DC or Peak AC			3	A
Carry current	DC or Peak AC			5	A
Contact resistance static	Measured with 40% overdrive Start Value			150	mOhm
Insulation resistance	RH <45 %, 100 V test voltage	10			TOhm
Breakdown voltage	according to IEC 255-5	15			kV DC
Operate time incl. bounce	measured with 40% overdrive			3	ms
Release time	measured with no coil excitation			1,5	ms
Capacitance	@ 10 kHz across open switch		0,2		pF

Special Product Data	Conditions	Min	Typ	Max	Unit
Number of contacts			1		
Contact - form			A - NO		
Dielectric Strength Coil/Contact	according to IEC 255-5	15			kV DC
Insulation resistance Coil/Contact	RH <45%, 100 VDC test voltage	10			TOhm
Capacity Coil/Contact	@ 10 kHz		1,1		pF
Case colour			nature		
Housing material			Crastin, SK 645FR, rated 94V-0, 140 °C, E.I. Dupont		
Connection pins			FeNi-alloy tin plated		
Magnetic Shield			no		
Reach / RoHS conformity			yes		



Products for tomorrow...

Europe: +49 / 7731 8399 0

| Email: info@meder.com

USA: +1 / 508 295 0771

| Email: salesusa@meder.com

Asia: +852 / 2955 1682

| Email: salesasia@meder.com

Item No.:

1905169114

Item:

H05-1A69

Environmental data	Conditions	Min	Typ	Max	Unit
Shock	1/2 sine wave duration 11ms			50	g
Vibration	from 10 - 2000 Hz			20	g
Operating temperature		-20		70	°C
Storage temperature		-20		90	°C
Soldering temperature	wave soldering max. 5 sec.			260	°C
Washability		fully sealed			

General data	Conditions	Min	Typ	Max	Unit
Total weight			25		g
Packaging		Styrofoam tray ESD per 10 piece			

Modifications in the sense of technical progress are reserved

Designed at: 07.03.06

Designed by: WKOVACS

Approval at: 26.05.08

Approval by: KOLBRICH

Last Change at: 11.11.09

Last Change by: SERVICES_EUROPE

Approval at: 25.11.09

Approval by: KOLBRICH

Version: 05