





DO NOT
SCALE FROM
THIS PRINT

FIG 1
THRU HOLE OPTION
(XFWS-08-XX-T-S SHOWN)
SEE NOTE 9



- NOTES:
- 1. Ⓢ REPRESENTS A CRITICAL DIMENSION.
 - 2. MINIMUM PUSHOUT FORCE: 3 lbs.
 - 3. MAXIMUM ALLOWABLE BOW: .003[.08] IN/IN AFTER ASSEMBLY.
 - 4. HEIGHT VARIATION BETWEEN ANY 2 PINS: .005[.13] MAX.
 - 5. -----
 - 6. -----
 - 7. MAXIMUM ALLOWABLE FLASH: .020[.51].
 - 8. MAXIMUM PIN ROTATION IN BODY: 2 DEGREES.
 - 9. THRU HOLE AND RIGHT ANGLE PARTS TO BE BULK PACKAGED.
 - 10. -VS PARTS TO BE PACKAGED AS:
POSITIONS -02 AND -03: LAYER PACKAGED,
POSITIONS -04 THRU -20: TUBE PACKAGED.
 - 11. TAILS ARE TO BE SHEARED TO PROPER LENGTH.
 - 12. T-1S8-XX MUST BE FLIPPED IN THE OPPOSITE WAY AS THE SELECTIVE PINS TO REDUCE THE NUMBER OF BAND MARKS IN THE POST AREA.

TABLE 1 : THRU HOLE OPTION				
STYLE	TERMINAL	"A" OVERALL HEIGHT	"B" POST HEIGHT	"C" TAIL DIM.
-01	T-1S8-01-TX	.750 [19.05]	.470 [11.94]	.180 [4.57]
-02	T-1S8-02-TX	.800 [20.32]	.520 [13.21]	.180 [4.57]
-04	T-1S8-04-TX	1.090 [27.69]	.829 [21.06]	.161 [4.10]
-05	T-1S8-01-TX	.430 [10.92]	.150 [3.81]	.180 [4.57]
-06	T-1S8-05-TX	1.350 [34.29]	1.070 [27.18]	.180 [4.57]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.3] ±2°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 1.5:1
INSULATOR:
HFSW: VECTRA E130i, COLOR: NATURAL
FWS: VALOX 420 SEO, COLR: BLACK
TERMINAL: PHOS BRONZE

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.045 [1.14] SQ POST POWER BLOCK ASSEMBLY, .200 [5.08]

DWG. NO. XFWS-XX-XX-XX-S-XX-X

BY: T. WERNE 9/27/2000 SHEET 1 OF 2

FIG 2

-VS: VERTICAL SURFACE MOUNT OPTION

-01 & -02 LEAD STYLES ONLY
(HFSW-08-01-TX-S-VS SHOWN)

[DIFFERENT AS SHOWN, OTHERWISE SAME AS THRU HOLE]




TABLE 2: -VS OPTION

TERMINAL	"B" POST HEIGHT	"C" TAIL DIM. (AFTER BEND)	"F" TAIL DIM (BEFORE BEND)
T-1S8-01-TX	0.422 [10.72]	.340 [8.64]	.228 [5.79]
T-1S8-02-TX	0.482 [12.24]	.330 [8.38]	.218 [5.54]

FIG 3

-RA: RIGHT ANGLE (POST) OPTION

-02 & -04 STYLES ONLY
(XFWS-XX-XX-TX-S-RA SHOWN)
SEE NOTE 9

[DIFFERENT AS SHOWN, OTHERWISE SAME AS THRU HOLE]






TABLE 3: -RA OPTION

STYLE	TERMINAL	"B" IN-PROCESS POST	"C" TAIL DIM.	"D" PROFILE	"E" FINAL POST
-02	T-1S8-02-TX	.520 [13.21]	.180 [4.57]	.100 [2.54]	.318 [8.08]
-04	T-1S8-04-TX	.829 [21.06]	.156 [3.96]	.195 [4.95]	.544 [13.82]




XFWS-XX-02-XX-XX-S-VS

PACKAGING VIEW

USE PT-XFWS001-VS TUBE
USE TP-13 TUBE PLUG


XFWS-XX-01-XX-XX-S-VS

PACKAGING VIEW

USE PT-XFWS001-VS TUBE
USE TP-13 TUBE PLUG

IN-PROCESS
-VS: VERTICAL SURFACE MOUNT
-RA: RIGHT ANGLE (POST)

"F" ONLY APPLIES TO -VS

F:\DWG\MISC\MKTG\XFWS-XX-XX-XX-S-XX-X-MKT.SLDDRW

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1:0.666667

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:

.045 [1.14] SQ POST POWER BLOCK ASSEMBLY, .200 [5.08]

DWG. NO.

XFWS-XX-XX-XX-S-XX-X

BY: T. WERNE 9/27/2000

SHEET 2 OF 2


-P: PICK & PLACE PAD


FIG 4

"R" = No OF POS x .200[5.08] REF
"S" = ("R" - .450[11.43]) / 2 ±.020[.51]
"T" = POST HEIGHT + .050 [1.27] REF
