

Touch panel - TP 06M - 2985165

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Touch panel with 14.5 cm/5.7" FSTN-display (Resistive industrial touch screen), 320 x 240 pixel(s) (QVGA), 5 grayscales, Arm9™, 200 MHz, 2x USB host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows CE 5.0 and user software: Visu+ / AX OPC Server. (bus system: without)

Your advantages

- ✓ Short startup time
- ✓ Easy installation, low installation depth, and compact design
- ✓ Display available in sizes from 8.9 cm (3.8") to 38.1 cm (15")
- ✓ Visu+ RT and AX OPC server integrated as standard in all devices
- ✓ Energy efficient due to LED backlighting

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	1,575.600 g
Custom tariff number	84714100
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---------------------------------------------------------------------------

Dimensions

Outer dimensions: width, height, depth	203 mm x 147 mm x 5 mm (Dimensions of the front plate)
Installation dimensions: width, height, depth	195 mm x 139 mm x 54 mm

Display

Display	14.5 cm/5.7" FSTN
Screen resolution	320 x 240 Pixel(s) (QVGA)
Touch technology	Resistive industrial touch screen
Backlighting	CCFL
Colors	5 grayscales

Touch panel - TP 06M - 2985165

Technical data

Computer data

Processor	Arm9™, 200 MHz
Operating system	Windows® CE 5.0
User software	Visu+
	AX OPC Server
RAM	64 MB SDRAM
	512 KB SRAM
Mass storage	Flash, 32 MB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x USB host 2.0
Bus system	without

General

Mounting type	Front installation
---------------	--------------------

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Vibration (operation)	DIN EN 60068-2-6
Shock	DIN EN 60068-2-27

Device supply

Power supply unit	24 V DC ±20 %
-------------------	---------------

Standards and Regulations

Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Classifications

eCl@ss

eCl@ss 4.0	27330202
eCl@ss 4.1	27330202
eCl@ss 5.0	27242215
eCl@ss 5.1	27242301
eCl@ss 6.0	27242301
eCl@ss 7.0	27242301

Touch panel - TP 06M - 2985165

Classifications

eCl@ss

eCl@ss 8.0	27242302
eCl@ss 9.0	27330201

ETIM

ETIM 2.0	EC001426
ETIM 3.0	EC001426
ETIM 4.0	EC001426
ETIM 5.0	EC001412

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43211903
UNSPSC 13.2	43201404

Accessories

Accessories

Battery module

Battery / accumulator - HMI BATTERY - 2701383

Lithium battery



Mounting material

Mounting material - HMI WALL MOUNTING KIT - 2701380

HMI mounting kit for panel installation. The mounting kit includes 2 spring clips.



Touch panel - TP 06M - 2985165

Accessories

Mounting material - HMI SCB MOUNTING KIT 4 - 2701384



HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.

Mounting material - HMI SCB MOUNTING KIT 6 - 2701385



HMI mounting kit for installation on a front plate. The mounting kit includes 6 x mounting brackets, 6 x screw threads, and a hexagonal wrench.

Mounting material - HMI SCB MOUNTING KIT 8 - 2701387



HMI mounting kit for installation on a front plate. The mounting kit includes 8 x mounting brackets, 8 x screw threads, and a hexagonal wrench.

Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for analog-resistive HMIs, silver coated. Delivery includes self-adhesive pen holder.

Protective foil

Protective foil - 5,7" DISPLAY PROTECTIVE FOIL - 2701371



Protective film set comprising 10 pieces of film for a 5.7" display. Including a squeegee to apply film and instructions.

Touch panel - TP 06M - 2985165

Accessories

Storage medium

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB
